

Miniature Basic Switch that Offers High Reliability and Security

- Wide variation of best-selling microswitches with switching currents of 10 to 21 A.
- Can be used for interrupting current when doors are opened or closed.
- Available in two types of cases: thermoplastic resin and thermosetting resin.

RoHS Compliant



Model Number Legend



1: SPDT

- 2: SPST-NC
- 3: SPST-NO

V

List of Models

Thermoplastic Case

			Ratings	21A	16A
Actuator	Terminals	Contact form	Maximum operating force (OF)	218	IUA
		SPDT			V-16-1A6
		SPST-NC	3.92N		V-16-2A6
		SPST-NO			V-16-3A6
		SPDT			V-16-1A5
	Solder terminals (A)	SPST-NC	1.96N		V-16-2A5
	(* 5)	SPST-NO			V-16-3A5
		SPDT			
		SPST-NC	0.98N		
		SPST-NO			
		SPDT			V-16-1C26
	Quick-connect terminals (#187) (C2)	SPST-NC	3.92N		V-16-2C26
		SPST-NO			V-16-3C26
Pin plunger		SPDT	1.96N		V-16-1C25
		SPST-NC			V-16-2C25
		SPST-NO			V-16-3C25
		SPDT	0.98N		
		SPST-NC			
		SPST-NO			
		SPDT		V-21-1C6	V-16-1C6
		SPST-NC	3.92N	V-21-2C6	V-16-2C6
		SPST-NO		V-21-3C6	V-16-3C6
	Quick-connect	SPDT			V-16-1C5
	terminals (#250)	SPST-NC	1.96N		V-16-2C5
	(C)	SPST-NO			V-16-3C5
		SPDT			
		SPST-NC	0.98N		
		SPST-NO			

			Ratings	21A	16A
Actuator	Terminals	Contact form	Maximum operating force (OF)	21A	ΙΟΑ
		SPDT			V-161-1A6
	-	SPST-NC	3.92N		V-161-2A6
		SPST-NO			V-161-3A6
	.	SPDT	1.96N		V-161-1A5
	Solder terminals (A)	SPST-NC			V-161-2A5
		SPST-NO			V-161-3A5
		SPDT			
		SPST-NC	0.98N		
		SPST-NO			
		SPDT			V-161-1C26
		SPST-NC	3.92N		V-161-2C26
		SPST-NO			V-161-3C26
Short hinge lever	Quick-connect	SPDT			V-161-1C25
~	terminals (#187)	SPST-NC	1.96N		V-161-2C25
	(C2)	SPST-NO			V-161-3C25
		SPDT			
		SPST-NC	0.98N		
		SPST-NO			
		SPDT		V-211-1C6	V-161-1C6
		SPST-NC	3.92N	V-211-2C6	V-161-2C6
		SPST-NO		V-211-3C6	V-161-3C6
	Quick-connect	SPDT			V-161-1C5
	terminals (#250) (C)	SPST-NC	1.96N		V-161-2C5
		SPST-NO			V-161-3C5
		SPDT	0.98N		
		SPST-NC			
		SPST-NO			
		SPDT	2.45N		V-162-1A6
		SPST-NC			V-162-2A6
		SPST-NO			V-162-3A6
	Solder terminals	SPDT	1.23N		V-162-1A5
	Solder terminals (A)	SPST-NC			V-162-2A5
		SPST-NO			V-162-3A5
		SPDT			
		SPST-NC	0.59N		
		SPST-NO			
		SPDT			V-162-1C26
		SPST-NC	2.45N		V-162-2C26
		SPST-NO			V-162-3C26
Hinge lever	Quick-connect	SPDT			V-162-1C25
~	terminals (#187) (C2)	SPST-NC	1.23N		V-162-2C25
	(02)	SPST-NO			V-162-3C25
		SPDT			
		SPST-NC	0.59N		
		SPST-NO			
		SPDT	_	V-212-1C6	V-162-1C6
		SPST-NC	2.45N	V-212-2C6	V-162-2C6
		SPST-NO		V-212-3C6	V-162-3C6
	Quick-connect	SPDT			V-162-1C5
	terminals (#250) (C)	SPST-NC	1.23N		V-162-2C5
	(0)	SPST-NO			V-162-3C5
		SPDT			
		SPST-NC	0.59N		
		SPST-NO			

			Ratings		
Actuator	Terminals	Contact form	Maximum operating force (OF)	21A	16A
		SPDT			V-163-1A6
		SPST-NC	1.27N		V-163-2A6
		SPST-NO			V-163-3A6
		SPDT			V-163-1A5
	Solder terminals (A)	SPST-NC	0.69N		V-163-2A5
	(74)	SPST-NO			V-163-3A5
		SPDT			
		SPST-NC	0.34N		
		SPST-NO			
		SPDT			V-163-1C26
		SPST-NC	1.27N		V-163-2C26
		SPST-NO	-		V-163-3C26
Long hinge lever	Outists segments	SPDT			V-163-1C25
	Quick-connect terminals (#187)	SPST-NC	0.69N		V-163-2C25
4	(C2)	SPST-NO			V-163-3C25
		SPDT			
		SPST-NC	0.34N		
		SPST-NO			
		SPDT		V-213-1C6	V-163-1C6
		SPST-NC	1.27N	V-213-2C6	V-163-2C6
		SPST-NO		V-213-3C6	V-163-3C6
		SPDT			V-163-1C5
	Quick-connect terminals (#250)	SPST-NC	0.69N		V-163-2C5
	(C)	SPST-NO			V-163-3C5
		SPDT			
		SPST-NC	0.34N 2.45N 1.23N		
		SPST-NC SPST-NO			
		SPDT			 V-164-1A6
		SPST-NC			V-164-2A6
		SPST-NO			V-164-3A6
	Solder terminals	SPDT			V-164-1A5
	(A)	SPST-NC			V-164-2A5
		SPST-NO			V-164-3A5
		SPDT			
		SPST-NC	0.59N		
		SPST-NO			
		SPDT			V-164-1C26
		SPST-NC	2.45N		V-164-2C26
Simulated roller		SPST-NO			V-164-3C26
lever	Quick-connect	SPDT			V-164-1C25
~	terminals (#187) (C2)	SPST-NC	1.23N		V-164-2C25
<u>~</u>	(02)	SPST-NO			V-164-3C25
		SPDT			
		SPST-NC	0.59N		
		SPST-NO			
		SPDT		V-214-1C6	V-164-1C6
		SPST-NC	2.45N	V-214-2C6	V-164-2C6
		SPST-NO		V-214-3C6	V-164-3C6
	Quick-connect	SPDT			V-164-1C5
	terminals (#250)	SPST-NC	1.23N		V-164-2C5
	(C)	SPST-NO			V-164-3C5
		SPDT			
		SPST-NC	0.59N		
		SPST-NO			

			Ratings	21A	16A
Actuator	Terminals	Contact form	Maximum operating force (OF)		
		SPDT	_		V-165-1A6
		SPST-NC	4.71N		V-165-2A6
		SPST-NO			V-165-3A6
	Solder terminals	SPDT	2.35N		V-165-1A5
	(A)	SPST-NC			V-165-2A5
		SPST-NO			V-165-3A5
		SPDT	-		
		SPST-NC	1.18N		
		SPST-NO			
		SPDT	-		V-165-1C26
		SPST-NC	4.71N		V-165-2C26
Short hinge roller		SPST-NO			V-165-3C26
lever	Quick-connect	SPDT	-		V-165-1C25
ଜ	terminals (#187) (C2)	SPST-NC	2.35N		V-165-2C25
<u> </u>	(02)	SPST-NO			V-165-3C25
		SPDT	-		
		SPST-NC	1.18N		
		SPST-NO			
		SPDT	-	V-215-1C6	V-165-1C6
		SPST-NC	4.71N	V-215-2C6	V-165-2C6
	Quick-connect terminals (#250) (C)	SPST-NO		V-215-3C6	V-165-3C6
		SPDT	2.35N		V-165-1C5
		SPST-NC			V-165-2C5
		SPST-NO			V-165-3C5
		SPDT	1.18N		
		SPST-NC			
		SPST-NO			
		SPDT	2.45N		V-166-1A6
		SPST-NC			V-166-2A6
		SPST-NO			V-166-3A6
	Solder terminals	SPDT	1.23N		V-166-1A5
	(A)	SPST-NC			V-166-2A5
		SPST-NO			V-166-3A5
		SPDT			
		SPST-NC	0.59N		
		SPST-NO			
		SPDT			V-166-1C26
		SPST-NC	2.45N		V-166-2C26
Hinge roller lever		SPST-NO			V-166-3C26
	Quick-connect	SPDT	4 0011		V-166-1C25
R	terminals (#187) (C2)	SPST-NC	1.23N		V-166-2C25
<u>.er_e</u> _	()	SPST-NO			V-166-3C25
		SPDT			
		SPST-NC	0.59N		
		SPST-NO			
		SPDT	0.4511	V-216-1C6	V-166-1C6
		SPST-NC	2.45N	V-216-2C6	V-166-2C6
		SPST-NO		V-216-3C6	V-166-3C6
	Quick-connect	SPDT	4.0011		V-166-1C5
	terminals (#250) (C)	SPST-NC	1.23N		V-166-2C5
	(-)	SPST-NO			V-166-3C5
		SPDT	0.501		
		SPST-NC	0.59N		
		SPST-NO			

Thermoset	ting case						
			Ratings	15A	10A	Heat-re	esistive
Actuator	Terminals	Contact form	Maximum operating force (OF)	134	IUA	15A	10A
		SPDT		V-15-1A6		V-15-1A6-T	
		SPST-NC	3.92N	V-15-2A6			
		SPST-NO		V-15-3A6			
		SPDT		V-15-1A5	V-10-1A5	V-15-1A5-T	V-10-1A5-T
	Solder terminals (A)	SPST-NC	1.96N	V-15-2A5	V-10-2A5		
	(74)	SPST-NO		V-15-3A5	V-10-3A5		
		SPDT			V-10-1A4		V-10-1A4-T
		SPST-NC	0.98N		V-10-2A4		V-10-2A4-T
	-	SPST-NO			V-10-3A4		V-10-3A4-T
		SPDT		V-15-1C26		V-15-1C26-T	
		SPST-NC	3.92N	V-15-2C26			
		SPST-NO	-	V-15-3C26			
Dia alua asa	Outists service at	SPDT		V-15-1C25	V-10-1C25	V-15-1C25-T	V-10-1C25-T
Pin plunger	Quick-connect terminals (#187)	SPST-NC	1.96N	V-15-2C25	V-10-2C25		
	(C2)	SPST-NO	-	V-15-3C25	V-10-3C25		
	-	SPDT			V-10-1C24		V-10-1C24-T
	-	SPST-NC	0.98N		V-10-2C24		
	-	SPST-NO			V-10-3C24		
		SPDT		V-15-1C6		V-15-1C6-T	
		SPST-NC	3.92N	V-15-2C6			
	-	SPST-NO		V-15-3C6			
	·	SPDT		V-15-1C5	V-10-1C5	V-15-1C5-T	V-10-1C5-T
	Quick-connect terminals (#250)	SPST-NC	1.96N	V-15-2C5	V-10-2C5		
	(C)	SPST-NO	1.3014	V-15-3C5	V-10-3C5		
		SPDT	0.98N		V-10-1C4		V-10-1C4-T
		SPST-NC			V-10-2C4		
		SPST-NO			V-10-3C4		
		SPDT	3.92N	V-151-1A6		V-151-1A6-T	
		SPST-NC		V-151-2A6			
		SPST-NO		V-151-3A6			
	·	SPDT		V-151-1A5	V-101-1A5	V-151-1A5-T	V-101-1A5-T
	Solder terminals	SPST-NC	1.96N	V-151-2A5	V-101-2A5		
	(A)	SPST-NO		V-151-3A5	V-101-2A5		
		SPDT			V-101-1A4		V-101-1A4-T
		SPST-NC	0.98N		V-101-1A4		V-101-1A4-1
		SPST-NO	0.301		V-101-2A4 V-101-3A4		
		SPDT		V-151-1C26		V-151-1C26-T	
		SPST-NC	3.92N	V-151-2C26			
	-	SPST-NO	5.521	V-151-2026			
0 1 1 1 1	-	SPDT		V-151-3C25	V-101-1C25	V-151-1C25-T	V-101-1C25-T
Short hinge lever	Quick-connect terminals (#187)	SPST-NC	1.96N	V-151-1C25	V-101-1C25		
a	(C2)	SPST-NC SPST-NO	1.301	V-151-2C25 V-151-3C25	V-101-2C25		
		SPST-NO		V-151-3025	V-101-3C25		 V-101-1C24-T
		SPD1 SPST-NC	0.98N		V-101-1C24 V-101-2C24		V-101-1C24-1
		SPST-NC SPST-NO	0.301		V-101-2C24 V-101-3C24		
		SPST-NO		 V-151-1C6	v-101-3C24	 V-151-1C6-T	
		SPD1 SPST-NC	3.92N	V-151-1C6 V-151-2C6		V-131-100-1	
		SPST-NC SPST-NO	J.92IN	V-151-2C6 V-151-3C6			
		SPDT		V-151-3C6 V-151-1C5	 V-101-1C5	 V-151-1C5-T	 V-101-1C5-T
	Quick-connect		1.06N				
	terminals (#250) (C)	SPST-NC	1.96N	V-151-2C5	V-101-2C5		
		SPST-NO		V-151-3C5	V-101-3C5		
		SPDT	0.000		V-101-1C4		V-101-1C4-T
		SPST-NC	0.98N		V-101-2C4		
		SPST-NO			V-101-3C4		

Miniature Basic Switch

V

			Ratings			Heat-re	esistive
Actuator	Terminals	Contact form	Maximum operating force (OF)	15A	10A	15A	10A
		SPDT		V-152-1A6		V-152-1A6-T	
	-	SPST-NC	2.45N	V-152-2A6			
	-	SPST-NO	-	V-152-3A6			
	-	SPDT		V-152-1A5	V-102-1A5	V-152-1A5-T	V-102-1A5-T
	Solder terminals (A)	SPST-NC	1.23N	V-152-2A5	V-102-2A5		
	(~)	SPST-NO	-	V-152-3A5	V-102-3A5		
	-	SPDT			V-102-1A4		V-102-1A4-T
	-	SPST-NC	0.59N		V-102-2A4		
	-	SPST-NO	-		V-102-3A4		
		SPDT		V-152-1C26		V-152-1C26-T	
	-	SPST-NC	2.45N	V-152-2C26			
	-	SPST-NO	-	V-152-3C26			
Hinge lever	Quick-connect	SPDT		V-152-1C25	V-102-1C25	V-152-1C25-T	V-102-1C25-T
	terminals (#187)	SPST-NC	1.23N	V-152-2C25	V-102-2C25		
<u> </u>	(C2)	SPST-NO	-	V-152-3C25	V-102-3C25		
	-	SPDT			V-102-1C24		V-102-1C24-T
	-	SPST-NC	0.59N		V-102-2C24		
	-	SPST-NO	-		V-102-3C24		
		SPDT		V-152-1C6		V-152-1C6-T	
	-	SPST-NC	2.45N	V-152-2C6			
		SPST-NO	-	V-152-3C6			
	Quick-connect	SPDT	1.23N	V-152-1C5	V-102-1C5	V-152-1C5-T	V-102-1C5-T
	terminals (#250)	SPST-NC		V-152-2C5	V-102-2C5		
	(C)	SPST-NO		V-152-3C5	V-102-3C5		
		SPDT	0.59N		V-102-1C4		V-102-1C4-T
		SPST-NC			V-102-2C4		
		SPST-NO			V-102-3C4		
		SPDT	1.27N	V-153-1A6		V-153-1A6-T	
		SPST-NC		V-153-2A6			
		SPST-NO		V-153-3A6			
		SPDT	0.69N	V-153-1A5	V-103-1A5	V-153-1A5-T	V-103-1A5-T
	Solder terminals (A)	SPST-NC		V-153-2A5	V-103-2A5		
	(~)	SPST-NO		V-153-3A5	V-103-3A5		
		SPDT	0.34N		V-103-1A4		V-103-1A4-T
		SPST-NC			V-103-2A4		
		SPST-NO			V-103-3A4		
		SPDT		V-153-1C26		V-153-1C26-T	
	-	SPST-NC	1.27N	V-153-2C26			
		SPST-NO		V-153-3C26			
Long hinge lever	Quick-connect	SPDT		V-153-1C25	V-103-1C25	V-153-1C25-T	V-103-1C25-T
/	terminals (#187)	SPST-NC	0.69N	V-153-2C25	V-103-2C25		
<u>e</u>	(C2)	SPST-NO		V-153-3C25	V-103-3C25		
	-	SPDT			V-103-1C24		V-103-1C24-T
		SPST-NC	0.34N		V-103-2C24		
		SPST-NO			V-103-3C24		
		SPDT		V-153-1C6		V-153-1C6-T	
		SPST-NC	1.27N	V-153-2C6			
		SPST-NO		V-153-3C6			
	Quick-connect	SPDT		V-153-1C5	V-103-1C5	V-153-1C5-T	V-103-1C5-T
	terminals (#250)	SPST-NC	0.69N	V-153-2C5	V-103-2C5		
	(C)	SPST-NO		V-153-3C5	V-103-3C5		
		SPDT			V-103-1C4		V-103-1C4-T
		SPST-NC	0.34N		V-103-2C4		
		SPST-NO			V-103-3C4		

Miniature Basic Switch

			Ratings			Heat-re	esistive
Actuator	Terminals	Contact form	Maximum operating force (OF)	15A	10A	15A	10A
		SPDT		V-154-1A6		V-154-1A6-T	
		SPST-NC	2.45N	V-154-2A6			
5		SPST-NO	-	V-154-3A6			
		SPDT		V-154-1A5	V-104-1A5	V-154-1A5-T	V-104-1A5-T
	Solder terminals	SPST-NC	1.23N	V-154-2A5	V-104-2A5		
	(A)	SPST-NO		V-154-3A5	V-104-3A5		
		SPDT			V-104-1A4		V-104-1A4-T
		SPST-NC	0.59N		V-104-1A4		
		SPST-NO	0.331		V-104-2A4		
		SPDT	0.45%	V-154-1C26		V-154-1C26-T	
		SPST-NC	2.45N	V-154-2C26			
Simulated roller		SPST-NO		V-154-3C26			
lever	Quick-connect	SPDT	-	V-154-1C25	V-104-1C25	V-154-1C25-T	V-104-1C25-T
~	terminals (#187) (C2)	SPST-NC	1.23N	V-154-2C25	V-104-2C25		
<u>a</u>	(02)	SPST-NO		V-154-3C25	V-104-3C25		
		SPDT			V-104-1C24		V-104-1C24-T
		SPST-NC	0.59N		V-104-2C24		
		SPST-NO			V-104-3C24		
		SPDT		V-154-1C6		V-154-1C6-T	
		SPST-NC	2.45N	V-154-2C6			
		SPST-NO		V-154-3C6			
	Quick-connect	SPDT	1.23N	V-154-1C5	V-104-1C5	V-154-1C5-T	V-104-1C5-T
	terminals (#250)	SPST-NC		V-154-2C5	V-104-2C5		
	(C)	SPST-NO		V-154-3C5	V-104-3C5		
		SPDT	0.59N		V-104-1C4		V-104-1C4-T
		SPST-NC			V-104-2C4		
		SPST-NO			V-104-3C4		
		SPDT	C 4.71N	V-155-1A6		V-155-1A6-T	
		SPST-NC		V-155-2A6			
		SPST-NO		V-155-3A6			
		SPDT		V-155-3A6	 V-105-1A5	 V-155-1A5-T	
	Solder terminals		2.35N				V-105-1A5-T
	(A)	SPST-NC		V-155-2A5	V-105-2A5		
		SPST-NO		V-155-3A5	V-105-3A5		
		SPDT			V-105-1A4		V-105-1A4-T
		SPST-NC	1.18N		V-105-2A4		
		SPST-NO			V-105-3A4		
		SPDT		V-155-1C26		V-155-1C26-T	
		SPST-NC	4.71N	V-155-2C26			
Short hinge roller		SPST-NO		V-155-3C26			
lever	Quick-connect	SPDT		V-155-1C25	V-105-1C25	V-155-1C25-T	V-105-1C25-T
୍	terminals (#187)	SPST-NC	2.35N	V-155-2C25	V-105-2C25		
	(C2)	SPST-NO		V-155-3C25	V-105-3C25		
		SPDT			V-105-1C24		V-105-1C24-T
		SPST-NC	1.18N		V-105-2C24		
		SPST-NO			V-105-3C24		
		SPDT		V-155-1C6		V-155-1C6-T	
		SPST-NC	4.71N	V-155-2C6			
		SPST-NO		V-155-3C6			
		SPDT		V-155-1C5	V-105-1C5	V-155-1C5-T	V-105-1C5-T
	Quick-connect terminals (#250)	SPST-NC	2.35N	V-155-1C5	V-105-1C5	v-155-105-1	-105-105-1
	(C)	SPST-NC SPST-NO	2.3511	V-155-2C5	V-105-2C5 V-105-3C5		
		SPDT			V-105-1C4		V-105-1C4-T
		SPST-NC	1.18N		V-105-2C4		
		SPST-NO			V-105-3C4		


Miniature Basic Switch


V

	Astustas Tampinala		Ratings	15A	10A	Heat-re	esistive
Actuator	Terminals	Contact form	Maximum operating force (OF)	15A	IUA	15A	10A
		SPDT		V-156-1A6		V-156-1A6-T	
		SPST-NC	2.45N	V-156-2A6			
		SPST-NO		V-156-3A6			
		SPDT		V-156-1A5	V-106-1A5	V-156-1A5-T	V-106-1A5-T
	Solder terminals (A)	SPST-NC	1.23N	V-156-2A5	V-106-2A5		
	(7	SPST-NO		V-156-3A5	V-106-3A5		
		SPDT			V-106-1A4		V-106-1A4-T
		SPST-NC	0.59N		V-106-2A4		
		SPST-NO			V-106-3A4		
	Quick-connect terminals (#187) (C2)	SPDT		V-156-1C26		V-156-1C26-T	
		SPST-NC	2.45N	V-156-2C26			
		SPST-NO		V-156-3C26			
Hinge roller lever		SPDT	1.23N	V-156-1C25	V-106-1C25	V-156-1C25-T	V-106-1C25-T
R		SPST-NC		V-156-2C25	V-106-2C25		
<u> </u>		SPST-NO		V-156-3C25	V-106-3C25		
		SPDT			V-106-1C24		V-106-1C24-T
		SPST-NC	0.59N		V-106-2C24		
		SPST-NO			V-106-3C24		
		SPDT		V-156-1C6		V-156-1C6-T	
		SPST-NC	2.45N	V-156-2C6			
		SPST-NO		V-156-3C6			
	Quick-connect	SPDT		V-156-1C5	V-106-1C5	V-156-1C5-T	V-106-1C5-T
	terminals (#250)	SPST-NC	1.23N	V-156-2C5	V-106-2C5		
	(C)	SPST-NO		V-156-3C5	V-106-3C5		
		SPDT			V-106-1C4		V-106-1C4-T
		SPST-NC	0.59N		V-106-2C4		
		SPST-NO			V-106-3C4		


Contact form

SPDT









Contact Specifications

Item	Model	V-21	V-16	V-15	V-10	
	Specification	Rivet				
Contact	Material	Silver alloy			Silver	
	Gap (standard value)	1 mm				
Inrush	NC	50 A	40 A	30 A	24 A	
current	NO	max.	max.	max.	max.	
Minimum (reference	applicable load e value)		DC5V	160mA	•	

\overline{V} Ratings

Model	Item Rated voltage	Resistive load
	AC250V	21 A
V-21	DC125V	0.6 A
	DC250V	0.3 A
	AC250V	16 A
V-16	DC125V	0.6 A
	DC250V	0.3 A
	AC250V	15 A
V-15	DC125V	0.6 A
	DC250V	0.3 A
	AC250V	10 A
V-10	DC125V	0.6 A
	DC250V	0.3 A

Note. The above rating values apply under the following test conditions. (1) Ambient temperature: $20\pm2^{\circ}C$

(2) Ambient humidity: 65±5% RH

(3) Operating frequency: 30 operations/min

Characteristics

App	proved	Stand	ards
-----	--------	-------	------

UL (UL1054)/CSA (CSA C22.2 No.55)

Rated voltage	Model	V-21	V-16	V-15	V-10
125 VAC 250 VAC		21A 1/2HP	16A 1/2HP	15A 1/2HP	10A 1/2HP
125 VDC 250 VDC		0.6A 0.3A			

VDE (EN61058-1)

Consult your OMRON sales representative for specific models with VDE approvals.

Rated voltage	Model	V-21	V-16
AC250V		20(4)A	16(4)A

Testing conditions: 5E4 (50,000 operations), for models of V-21: T80 (0 to 80° C), for models of V-16: T105 (0 to 105° C)

Item	Model	V-10 V-15 V-16			V-21		
Permissible operating spe	eed	0.1mm to 1 m/s max. (pin plunger models)					
Permissible operating	Mechanical	600 operations/min max. (pin plunger models)					
frequency	Electrical	60 operations/min					
Insulation resistance			100M Ω min. (at 500 VDC w	vith insulation tester)			
Contact resistance (initial	value)		15mΩ ma	IX.			
	Between terminals of the same polarity		AC1,000V 50/60)Hz 1min			
Dielectric strength *1	Between current-carrying metal parts and ground	AC1,500V 50/60Hz 1min	AC1,500V 50/60Hz 1min	AC2,000V 5	0/60Hz 1min		
	Between each terminals and non-current-carrying metal parts	AC1,500V 50/60Hz 1min AC1,500V 50/60Hz 1min AC2,000V 50/		0/60Hz 1min			
Vibration resistance *2	Malfunction	10 to 55 Hz, 1.5-mm double amplitude					
	Durability	1,000 m/s ² {approx. 100 G} max.					
Shock resistance *2	Malfunction	200 m/s ² {approx. 20G} max. 300 m/s ² {approx. 30 G} max.					
	Mechanical	50,000,000 operations min. (60 operations/min)					
Durability *3	Electrical	300,000 operations min. 100,000 operations min. (30 operations/min) (30 operations/min) Heat resistive: 50,000 Heat resistive: 20,000 operations min operations min (30 operations/min) (30 operations/min)		· · · ·	erations min. tions/min)		
Degree of protection		IEC IP40					
Degree of protection again	inst electric shock	Class I					
Proof tracking index (PTI			175				
Ambient operating temperature		-25 to 105°C (Heat resistive: -25 to 150°C) -25 to 105°C -25 to 80°C			-25 to 80°C		
		(at ambient humidity of 60% max.) (with no icing or condensation)					
Ambient operating humid	ity	85% max. (for 5 to 35°C)					
Weight			Approx. 6.2g (pin plu	nger models)			


Note. The data given above are initial values.

*1. The dielectric strength shown in the table indicates a value for models with a Separator.

*2. For the pin plunger models, the above values apply for use at the free position and total travel position. For the lever models, they apply at the total travel position. Close or open circuit of the contact is shorter than 1 ms.


*3. For testing conditions, consult your OMRON sales representative.

Terminals and Apperance (Unit: mm)



Note. The above is for the SPDT contact specifications. Two terminals will be available for SPST-NO or SPST-NC contact specifications. For terminal positions, refer to Contact form on page 9.

Mounting Holes (Unit: mm)



Dimensions and Operating Characteristics

Thermoplastic Case V-21/-16 Models

The following illustrations and drawings are for quick-connect terminals #250 (terminals C). V models with a switching current of 16 A and 11 A incorporate solder terminals (A) and quick-connect terminals #187 (C2). These models are different from #250 models in terminal size only. Dimensions of solder terminals (A) and quick-connect terminals #187 (C2) are omitted. Please refer to the **"Terminals and Shapes"** on previous page.

The 🗆 is replaced with the code for the terminals. See the "List of Models" for available combinations of shapes.


●Pin plunger V-21-1□6

V-16-1□6

V-16-1□5

V






Operating characteristics	Model	V-21-1⊡6 V-16-1⊡6	V-16-1□5	
OF max.		3.92N	1.96N	
RF min.		0.78N	0.49N	
PT max.		1.2mm		
OT min.		1.0mm		
MD max.		0.4mm		
OP		14.7±0.4mm		

●Short hinge lever V-211-1□6

V-161-1□6 V-161-1□5






Operating characteristics	Model	V-211-1□6 V-161-1□6	V-161-1□5	
OF max.		3.92N	1.96N	
RF min.		0.49N	0.49N	
PT max.		1.6mm		
OT min.		0.8mm		
MD max.		0.6mm		
OP		15.2±0.5mm		

●Hinge lever V-212-1□6 V-162-1□6


V-162-1⊡5






Operating characteristics	Model	V-212-1⊡6 V-162-1⊡6	V-162-1□5	
OF max.		2.45N	1.23N	
RF min.		0.25N	0.14N	
PT max.		4.0mm		
OT min.		1.6mm		
MD max.		1.5mm		
OP		15.2±1.2mm		

Long Hinge Lever Models



Operating characteristics	Model	V-213-1⊡6 V-163-1⊡6	V-163-1□5	
OF max.		1.27N	0.69N	
RF min.		0.12N	0.06N	
PT max.		9.0mm		
OT min.		2.0mm		
MD max.		2.8mm		
OP		15.2 ^{+2.6} _{-3.2} mm		

Note 1. Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions. Note 2. The operating characteristics are for operation in the A direction (\clubsuit).



Note 1. Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.

Note 2. The operating characteristics are for operation in the A direction (\clubsuit).

Thermosetting Case (V-15/V-10 Models) Applicable to both Standard (105°C) and Heat-resistive (150°C) models


The following dimensions and Operating Characteristics are for both "Not specified: Standard (105°C)" and "-T: Heat-resistive (150°C)" models. The following illustrations and drawings are for solder terminals (Terminal A). V models with a switching current of 15A and 10A have quick-connect terminals #187 (C2). These models are different from solder terminal models in terminal size only. Illustrations for quick-connect terminals #187 (C2) are omitted. Please refer to "Terminals and Shapes" on page 8.

The 🗌 is replaced with the code for the terminals.See the "List of Models" for available combinations of shapes.

●Pin plunger V-15-1□6 V-15-1□5




V-10-1□5 V-10-1□4




Operating characteristics	Model	V-15-1□6	V-15-1□5 V-10-1□5	V-10-1□4
OF max.		3.92N	1.96N	0.98N
RF min.		078N	0.49N	0.20N
PT max.		1.2mm		
OT min.		1.0mm		
MD max.		0.4mm		
OP		14.7±0.4mm		

•Short hinge lever

V-151-1□6 V-151-1□5 V-101-1□5 V-101-1□4






t=0.5 *

Operating characteristics	Model	V-151-1□6	V-151-1□5 V-101-1□5	V-101-1□4
OF max.		3.92N	1.96N	0.98N
RF min.		0.49N	0.49N	0.15N
PT max.			1.6mm	
OT min.		0.8mm		
MD max.			0.6mm	
OP		1	15.2±0.5mn	n


●Hinge lever V-152-1□6 V-152-1□5 V-102-1□5







Operating characteristics	Model	V-152-1□6	V-152-1□5 V-102-1□5	V-102-1□4
OF max.		2.45N	1.23N	0.59N
RF min.		0.25N	0.14N	0.06N
PT max.			4.0mm	
OT min.			1.6mm	
MD max.		1.5mm		
OP		1	5.2±1.2mn	n

Long Hinge Lever Models



Operating characteristics	Model	V-153-1□6	V-153-1□5 V-103-1□5	V-103-1□4
OF max.		1.27N	0.69N	0.34N
RF min.		0.12N	0.06N	-
PT max.		9.0	mm	9.0mm
OT min.		2.0	mm	3.2mm
MD max.		2.8	mm	2.8mm
OP		15.2 ⁺²	.6 .2 mm	15.2±2.6
				mm





Note 1. Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions. Note 2. The operating characteristics are for operation in the A direction (\clubsuit).

Precautions

★Please read "Common Precautions" for correct use.

Precautions for Safe Use

Soldering

Connecting to Solder Terminals

Complete the soldering at the iron tip temperature of 250 to 350°C (60W) within 5 seconds, and do not apply any external force for 1 minute after soldering.

Be sure to apply only the minimum required amount of flux.It may result in contact failure once the flux penetrates into the internal part of the Switch.

 Connecting to Quick-connect Terminals #187 Insert the receptacle of quick-connect terminal #187 straight toward the terminal.
 Applying excessive external force horizontally or vertically may

cause deformation of terminals and may damage the housings.

Connecting to Quick-connect Terminals #250

Insert the receptacle of quick-connect terminal #250 straight toward the terminal.

Applying excessive external force horizontally or vertically may cause deformation of terminals and may damage the housings.

Precautions for Correct Use

Mounting

Use M3 mounting screw with plane washers or spring washers to securely mount the Switch.Tighten the screws to a torque of 0.39 to 0.59N·m {4 to 6 kgf·cm}.

Application examples provided in this document are for reference only. In actual applications, confirm equipment functions and safety before using the product.
Consult your OMRON representative before using the product under conditions which are not described in the manual or applying the product to nuclear control systems, railroad systems, aviation systems, vehicles, combustion systems, medical equipment, amusement machines, safety equipment, and other systems or equipment that may have a serious influence on lives and property if used improperly. Make sure that the ratings and performance characteristics of the product provide a margin of safety for the system or equipment, and be sure to provide the system or equipment with double safety mechanisms.

Note: Do not use this document to operate the Unit.

OMRON Corporation Electronic and Mechanical Components Company

Contact: www.omron.com/ecb

Cat. No. B010-E1-14 0615(0207)(O)

16 Downloaded from Arrow.com.