IRFP460B, SiHG460B




Vishay Siliconix

D Series Power MOSFET

PRODUCT SUMMARY					
V_{DS} (V) at T_{J} max.	550				
R _{DS(on)} max. at 25 °C (Ω)	$V_{GS} = 10 V$	0.25			
Q _g max. (nC)	170				
Q _{gs} (nC)	14				
Q _{gd} (nC)	28				
Configuration	Single				







N-Channel MOSFET

FEATURES

- Optimal Design
 - Low Area Specific On-Resistance
 - Low Input Capacitance (Ciss)
 - Reduced Capacitive Switching Losses
 - High Body Diode Ruggedness
 - Avalanche Energy Rated (UIS)
- Optimal Efficiency and Operation
 - Low Cost
 - Simple Gate Drive Circuitry
 - Low Figure-of-Merit (FOM): Ron x Qa
 - Fast Switching

 Material categorization: For definitions of compliance please see www.vishay.com/doc?99912

Note

Lead (Pb)-containing terminations are not RoHS-compliant. Exemptions may apply.

APPLICATIONS

- Consumer Electronics
 - Displays (LCD or Plasma TV)
- Server and Telecom Power Supplies
- SMPS
- Industrial
 - Welding
 - Induction Heating
- Motor Drives Battery Chargers
- SMPS
 - Power Factor Correction (PFC)

ORDERING INFORMATION	
Package	TO-247AC
Lead (Pb)-free	IRFP460BPbF
Lead (Pb)-free and Halogen-free	SiHG460B-GE3

ABSOLUTE MAXIMUM RATINGS ($T_c = 25 \degree C$, unless otherwise noted)							
PARAMETER	SYMBOL	LIMIT	UNIT				
Drain-Source Voltage		V _{DS}	500				
Gate-Source Voltage		V _{GS}	± 20	V			
Gate-Source Voltage AC (f > 1 Hz)			30				
Continuous Drain Current (T _J = 150 °C)	V_{GS} at 10 V $\frac{T_C = 25 \degree C}{T_C = 100 \degree C}$	- I _D -	20				
	V_{GS} at 10 V $T_C = 100 \text{ °C}$		13	А			
Pulsed Drain Current ^a		I _{DM}	62				
Linear Derating Factor			2.2	W/°C			
Single Pulse Avalanche Energy ^b		E _{AS}	281	mJ			
Maximum Power Dissipation		PD	278	W			
Operating Junction and Storage Temperature Range		T _J , T _{stg}	- 55 to + 150	°C			
Drain-Source Voltage Slope	T _J = 125 °C	dV/dt	24	V/ns			
Reverse Diode dV/dt ^d		uv/dl	0.36	v/ns			
Soldering Recommendations (Peak Temperature)	for 10 s		300 ^c	°C			

Notes

a. Repetitive rating; pulse width limited by maximum junction temperature. 5 A.

b.
$$V_{DD} = 50$$
 V, starting $I_J = 25$ °C, L = 10 mH, $R_g = 25 \Omega$, $I_{AS} = 7.0$

c. 1.6 mm from case.

d. $I_{SD} \leq I_D$, starting $T_J = 25 \ ^{\circ}C$.

S12-0812-Rev. B, 16-Apr-12



HALOGEN

FREE

Available



Vishay Siliconix

PARAMETER	SYMBOL	TYP.	M	AX.	UNIT		
Maximum Junction-to-Ambient	R _{thJA}	-	4	0			
Maximum Junction-to-Case (Drain)	R _{thJC}	-	0.	45			
		1					
SPECIFICATIONS ($T_J = 25 \ ^{\circ}C$, u	inless otherwi	ise noted)					
PARAMETER	SYMBOL	TES	T CONDITIONS	MIN.	TYP.	MAX.	UNIT
Static						•	•
Drain-Source Breakdown Voltage	V _{DS}	V _{GS} =	= 0 V, I _D = 250 μA	500	-	-	V
V _{DS} Temperature Coefficient	$\Delta V_{DS}/T_{J}$	Reference	to 25 °C, $I_D = 250 \ \mu A$	-	0.56	-	V/°C
Gate-Source Threshold Voltage (N)	V _{GS(th)}	V _{DS} =	$V_{DS} = V_{GS}, I_D = 250 \ \mu A$		-	4	V
Gate-Source Leakage	I _{GSS}		V _{GS} = ± 20 V		-	± 100	nA
	I		= 500 V, V _{GS} = 0 V	-	-	1	
Zero Gate Voltage Drain Current	IDSS	V _{DS} = 400 V	$V_{\rm ,}V_{\rm GS}$ = 0 V, T _J = 125 °	C -	-	10	μA
Drain-Source On-State Resistance	R _{DS(on)}	V _{GS} = 10 V	I _D = 10 A	-	0.2	0.25	Ω
Forward Transconductance	9 _{fs}	-	= 50 V, I _D = 10 A	-	12	-	S
Dynamic				•		•	
Input Capacitance	C _{iss}	$V_{GS} = 0 V,$ $V_{DS} = 100 V,$ f = 1 MHz		-	3094	-	pF
Output Capacitance	C _{oss}			-	152	-	
Reverse Transfer Capacitance	C _{rss}			-	13	-	
Effective output capacitance, energy related ^a	C _{o(er)}	V _{GS} = 0 V, V _{DS} = 0 V to 400 V		-	131	-	
Effective output capacitance, time related ^b	C _{o(tr)}			-	189	-	
Total Gate Charge	Qg			-	85	170	
Gate-Source Charge	Q _{gs}	$V_{GS} = 10 V$	$V_{GS} = 10 \text{ V}$ $I_D = 10 \text{ A}, \text{ V}_{DS} = 400 \text{ V}$		14	-	nC
Gate-Drain Charge	Q _{gd}				28	-	
Turn-On Delay Time	t _{d(on)}			-	24	50	
Rise Time	t _r	Van -	V _{DD} = 400 V, I _D = 10 A,		31	62	ns
Turn-Off Delay Time	t _{d(off)}	$V_{DD} = 400 \text{ V}, \text{ ID} = 10 \text{ A},$ $V_{GS} = 10 \text{ V}, \text{ R}_{g} = 9.1 \Omega$		-	117	176	
Fall Time	t _f			-	56	112	
Gate Input Resistance	R _g	f = 1 MHz, open drain		-	1.8	-	Ω
Drain-Source Body Diode Characteristic	cs						
Continuous Source-Drain Diode Current	۱ _S	MOSFET symbol showing the integral reverse p - n junction diode		-	-	20	A
Pulsed Diode Forward Current	I _{SM}			-	-	80	
Diode Forward Voltage	V _{SD}	T _J = 25 °C, I _S = 10 A, V _{GS} = 0 V		-	-	1.2	V
Reverse Recovery Time	t _{rr}	$T_{J} = 25 \text{ °C}, I_{F} = I_{S} = 10 \text{ A},$ dI/dt = 100 A/ μ s, V _R = 20 V		-	437	-	ns
Reverse Recovery Charge	Q _{rr}			-	5.9	-	μC
Reverse Recovery Current	I _{RRM}			-	25	-	A

Notes

a. $C_{oss(er)}$ is a fixed capacitance that gives the same energy as C_{oss} while V_{DS} is rising from 0 % to 80 % V_{DS} .

b. $C_{oss(tr)}$ is a fixed capacitance that gives the same charging time as C_{oss} while V_{DS} is rising from 0 % to 80 % V_{DS} .



Vishay Siliconix

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Fig. 1 - Typical Output Characteristics





Fig. 2 - Typical Output Characteristics








Fig. 4 - Normalized On-Resistance vs. Temperature




Fig. 5 - Typical Capacitance vs. Drain-to-Source Voltage




Fig. 6 - Typical Gate Charge vs. Gate-to-Source Voltage

S12-0812-Rev. B, 16-Apr-12

Document Number: 91502

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000








Fig. 7 - Typical Source-Drain Diode Forward Voltage








Fig. 9 - Maximum Drain Current vs. Case Temperature




Fig. 10 - Temperature vs. Drain-to-Source Voltage




Fig. 11 - Normalized Thermal Transient Impedance, Junction-to-Case

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

Vishay Siliconix






Fig. 12 - Switching Time Test Circuit




Fig. 13 - Switching Time Waveforms




Fig. 14 - Unclamped Inductive Test Circuit




Fig. 15 - Unclamped Inductive Waveforms




Fig. 16 - Basic Gate Charge Waveform




Fig. 17 - Gate Charge Test Circuit

5

IRFP460B, SiHG460B

Vishay Siliconix

IRFP460B, SiHG460B





Peak Diode Recovery dV/dt Test Circuit




Fig. 18 - For N-Channel

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?91502.

Vishay Siliconix





TO-247AC (High Voltage)

ECN: X13-0103-Rev. D, 01-Jul-13 DWG: 5971

Notes

1. Dimensioning and tolerancing per ASME Y14.5M-1994.

2. Contour of slot optional.

 Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body.

4. Thermal pad contour optional with dimensions D1 and E1.

5. Lead finish uncontrolled in L1.

6. Ø P to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154").

7. Outline conforms to JEDEC outline TO-247 with exception of dimension c.

8. Xian and Mingxin actually photo.





Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay: IRFP460BPBF SIHG460B-GE3