COMPLIANT

HALOGEN

FREE



Vishay General Semiconductor

Surface Mount Ultrafast Plastic Rectifier



SMB (DO-214AA)

PRIMARY CHARACTERISTICS					
I _{F(AV)}	2.0 A				
V _{RRM}	100 V, 150 V, 200 V				
I _{FSM}	50 A				
t _{rr}	20 ns				
V _F at I _F = 2.0 A	0.76 V				
T _J max.	150 °C				
Package	SMB (DO-214AA)				
Circuit configuration	Single				

FEATURES

- · Oxide planar chip junction
- · Ultrafast recovery time
- · Low forward voltage, low power losses
- High forward surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Material categorization: for definitions of compliance please see www.vishav.com/doc?99912

TYPICAL APPLICATIONS

For use in low voltage, high frequency rectifier of switching power supplies, freewheeling diodes, DC/DC converters or polarity protection application.

MECHANICAL DATA

Case: SMB (DO-214AA)

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade Base P/N-M3 - halogen-free, RoHS-compliant, and commercial grade

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 and M3 suffix meet JESD 201 class 2 whisker test

Polarity: color band denotes cathode end

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)						
PARAMETER	SYMBOL	U2B	U2C	U2D	UNIT	
Device marking code		U2B	U2C	U2D		
Maximum repetitive peak reverse voltage	V_{RRM}	100	150	200	V	
Maximum average forward rectified current (fig. 1)	I _{F(AV)}	2.0			Α	
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	50			А	
Operating junction and storage temperature range	T _J , T _{STG}	-55 to +150			°C	



Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)							
PARAMETER	TEST CONDITIONS		SYMBOL	TYP.	MAX.	UNIT	
Instantaneous forward voltage	I _F = 2 A	T _A = 25 °C	V _F ⁽¹⁾	0.86	0.90	V	
		T _A = 100 °C		0.76	0.83		
Reverse current	Rated V _B	T _A = 25 °C	I _R ⁽²⁾	ı	10	μА	
	Haled V _R	T _A = 100 °C		180	350		
Reverse recovery time	$I_F = 0.5 \text{ A}, I_R = 1.0 \text{ A},$ $I_{rr} = 0.25 \text{ A}$	T _A = 25 °C	t _{rr}	-	20	ns	
	$I_F = 2.0 \text{ A}, \text{ dI/dt} = 50 \text{ A/}\mu\text{s}, \ V_R = 30 \text{ V}, I_{rr} = 0.1 I_{RM}$	T _A = 25 °C		27	-		
		T _A = 100 °C		35	-		
Storage charge	$I_F = 2.0 \text{ A}, \text{ dI/dt} = 50 \text{ A/}\mu\text{s}, \ V_R = 30 \text{ V}, I_{rr} = 0.1 I_{RM}$	T _A = 25 °C	Q _{rr}	9	-	- nC	
		T _A = 100 °C		19	-		
Typical junction capacitance	4.0 V, 1 MHz		CJ	16	-	pF	

Notes

 $^{(1)}\,$ Pulse test: 300 μs pulse width, 1 % duty cycle

(2) Pulse test: Pulse width ≤ 40 ms

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	OL U2B U2C U2D		UNIT	
Typical thermal registeres	R _{0JA} (1)	105		°C/W	
Typical thermal resistance	R _{0JM} (1)	18			

Note

 $^{(1)}$ Free air, mounted on recommended copper pad area. Thermal resistance $R_{\theta JA}$ - junction to ambient, $R_{\theta JM}$ - junction to mount

ORDERING INFORMATION (Example)					
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE	
U2D-E3/52T	0.099	52T	750	7" diameter plastic tape and reel	
U2D-E3/5BT	0.099	5BT	3200	13" diameter plastic tape and reel	
U2D-M3/52T	0.099	52T	750	7" diameter plastic tape and reel	
U2D-M3/5BT	0.099	5BT	3200	13" diameter plastic tape and reel	

RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)




Fig. 1 - Maximum Forward Current Derating Curve




Fig. 2 - Forward Power Loss Characteristics



Vishay General Semiconductor




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 4 - Typical Reverse Characteristics




Fig. 5 - Typical Junction Capacitance






Fig. 6 - Typical Transient Thermal Impedance

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)







Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

U2B-E3/5BT U2B-E3/52T U2C-E3/5BT U2C-E3/52T U2D-E3/5BT U2D-E3/52T