

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1703510003](#)
Status: **Active**
Overview: [EXTreme Guardian System](#)
Description: EXTreme Guardian Crimp Receptacle Housing, 2 Circuit, 11.00mm Pitch, 6 AWG

Documents:

[3D Model](#) [Product Specification PS-46819-001-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Crimp Housings
 Series [170351](#)
 Application Wire-to-Board, Wire-to-Wire
 Overview [EXTreme Guardian System](#)
 Product Name EXTreme Guardian
 UPC 884982970038

Physical

Circuits (maximum) 2
 Color - Resin Black
 Flammability 94V-0
 Gender Receptacle
 Glow-Wire Capable No
 Keying to Mating Part None
 Material - Resin Polyester
 Net Weight 6.920/g
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 11.00mm
 Temperature Range - Operating -40° to +105°C

Electrical

Current - Maximum per Contact 80.0A


Solder Process Data

Lead-free Process Capability N/A

Material Info

Reference - Drawing Numbers

Product Specification PS-46819-001-001
 Sales Drawing SD-170351-0002-001



EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2021)4569-DC (8
 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[170351](#) Series

Use With

[46819](#) High Power Terminal

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[170351-0003](#)