

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2041020209](#)
Status: **Active**
Overview: [VersaBlade Wire-to-Wire Connector System](#)
Description: [VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Friction Lock, Natural, Glow-Wire Capable](#)

Documents:

3D Model	Application Specification 351500000ASKOR-000 (PDF)
Drawing (PDF)	Packaging Specification 2041020609-001 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification 2041020609-000 (PDF)	Brochure (PDF)
Application Specification 351500000ASENG-000 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	204102
Application	Power, Wire-to-Wire
Overview	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
UPC	191128970778

Physical

Circuits (maximum)	2
Color - Resin	Natural
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PET/PC
Net Weight	1.594/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	8.00mm
Pitch - Termination Interface	8.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +110°C

Material Info

Reference - Drawing Numbers

Application Specification	351500000AS_ENG-000, 351500000AS_KOR-000
Packaging Specification	2041020609-001
Product Specification	2041020609-000
Sales Drawing	2041020209-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[204102 Series](#)

Mates With

VersaBlade Multi-Module 4-2 Receptacle Housing [2041020609](#)

Use With

VersaBlade Crimp Terminals [35746](#)

VersaBlade TPA [359650290](#) , [359650292](#)
, [359650293](#) , [495470392](#) (Upper),
[495480390](#) (Lower)