




**RoHS
Compliant
Drawing For
Reference Only**



規格書 Specifications

額定負荷 Ratings	DC 30V 0.5 A
絶縁電阻 Insulation Resistance	DC 250V 60 Sec. 100 mΩ Min
抗電強度 Dielectric Voltage	AC 500V (50-60Hz) 60 Sec. Min
操作力 Operating Force (gf)	挿入力 (Insertion Force) 3 ~ 20N 抜出力 (Extraction Force) 3 ~ 20N
負荷壽命 Operating Life With Load	5,000 次 Cycles

Model No.	DS-225A(SL)	DS-225B(SL)
Pin	φ2.5	φ2.0

TOLERANCESE UNIESS OTHERWISE SPEC

UNDER	1.5 mm	±0.10
	1.5 - 10.0mm	±0.20
OVER	10.0 mm	± 0.25

NO	PART	MATERIAL	Q'TY	REMARKS
6	Cover	Phenol	1	Black / Yellow
5	Case	PBT	1	Black
4	Plug Pin	Brass Strip	1	Ag Plated Over Ni Plated
3	Terminal	Brass Strip	1	Ag Plated Over Ni Plated
2	Contact Terminal	Manganese Steel	1	Ni Plated
1	Pin Terminal	Brass Strip	1	Ag Plated Over Ni Plated

Technical requirement :

1. This product should meet EU RoHS related requirement.
2. The surface of plastic part should be without any crackle such as burr,lack,and so on phenomenon.
3. The surface of metal part should be without any defect such as scour,nick,oxidation and plating problem.
4. The electronic performance should be the same as spec.

DCI DRAGON CITY INDUSTRIES LIMITED

Item Name	DC POWER JACK	Tolerance :
Item No.	DS-225(SL)	Unit : mm

Design	K.W Law	Remark	Scale
Drawing	W.K Yeung	Remark	Material
Check	K.L Wong	Remark	Drawing No. A512141345
Approval	K.W Chan	Remark	Sheet