



## D26411

### 1800W Standard Heatgun

#### Selling Proposition

- Durable design with added protection for the heating element
- Light weight ergonomics and compact design for increased comfort and application use
- Two air flows to maximise control in most applications
- Large stable support stand to ensure safety in stationary applications
- Two cone attachments as standard to increase the users versatility for specific applications

#### Standard Equipment

- Cone nozzle
- Fish tail surface nozzle

#### Warranty Specifications

- 1 Year Free Service Contract
- 1 year full warranty
- 30 Day No Risk Satisfaction Guarantee

Specifications	
Power Input	1800 Watts
Operating Temperature	50-400 / 50-600 °C
Air Flow	250 / 450 l/min
´Gewicht	0.80 kg
Länge	253 mm
Height	210 mm
Hand/Arm Vibration	0.86 m/s <sup>2</sup>
Uncertainty K 1 (Vibration)	1.5 m/s <sup>2</sup>