Product datasheet Characteristics

ABL6TS06J

voltage transformer - 230..400 V - 1 x 12 V - 63 VA



Price* : 50.00 GBP



Main

| Range of product | Phaseo Optimum | 9 |
|---------------------------------------|---|----------|
| Product or component type | Safety and isolation transformer | |
| Rated power in VA | 63 VA | ¥ |
| Input voltage | 230 V AC single phase, terminal(s): N-L1 400 V AC phase to phase, terminal(s): L1-L2 | , |
| Output voltage | 12 V AC | |
| Secondary winding | Single | <u> </u> |
| Protective cover | Without | |
| Ambient air temperature for operation | -2050 °C | |
| | | |

Complementary

| Complementary | |
|------------------------------------|---|
| Input voltage limits | 207253 V 360440 V |
| Network frequency limits | 4763 Hz |
| Input voltage tolerance | +/- 15 V |
| Efficiency | 84 % |
| Power dissipation in W | 12 W |
| Output sustained overvoltage | 9 % (no load, hot state) |
| Maximum voltage drop at rated load | 1.3 % |
| No load losses | 5.3 W |
| Short-circuit voltage | 0,0963 |
| Output protection type | Against overload, protection technology: external Against overvoltage, protection technology: external Against short-circuits, protection technology: external |
| Connections - terminals | For input connection: screw type terminals, connection capacity: 5 x 4 mm² AWG 11 For input ground connection: screw type terminals, connection capacity: 1 x 4 mm² AWG 11 For output connection: screw type terminals, connection capacity: 2 x 4 mm² AWG 11 |
| Marking | CE |

| Fixing mode | By 4 screws diameter: 4.8 mm on vertical panel, operating position: horizontal By 4 screws diameter: 4.8 mm on vertical panel, operating position: vertical By clips (with mounting plate) on 35 mm symmetrical DIN rail By 4 screws diameter: 4.8 mm on horizontal panel with derating to 90 % |
|-----------------------------|---|
| Operating altitude | 3000 m |
| Electrical insulation class | Class B |
| Width | 78 mm |
| Height | 90 mm |
| Depth | 80 mm |
| Net weight | 1.6 kg |

Environment

| Product certifications | UR EAC |
|-------------------------------------|--|
| Standards | UL 506 |
| IP degree of protection | IP20 |
| Environmental characteristic | EMC conforming to EN 62041 Safety conforming to EN 61558-1 Safety conforming to EN 61558-2-6 |
| Protective treatment | TC |
| Ambient air temperature for storage | -4080 °C |
| Overvoltage category | Class I conforming to VDE 0106-1 |
| Dielectric strength | 2000 V between winding and ground 4000 V between primary and secondary |
| | |

Offer Sustainability

| Sustainable offer status | Green Premium product | |
|--|--|--|
| REACh Regulation | REACh Declaration | |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration | |
| Mercury free | Yes | |
| RoHS exemption information | Yes | |
| China RoHS Regulation | China RoHS declaration | |
| Environmental Disclosure Product Environmental Profile | | |
| Circularity Profile | No need of specific recycling operations End of Life Information | |


Contractual warranty

| Contractadi Warranty | ontractal warranty | | | |
|----------------------|--------------------|--|--|--|
| Warranty | 18 months | | | |

Product datasheet Dimensions Drawings

ABL6TS06J

Dimensions



Dimensions in mm

| а | b | С | G | J | Ø |
|----|----|----|----|----|-----|
| 78 | 90 | 80 | 56 | 56 | 4.8 |


Dimensions in in.

| а | b | С | G | J | Ø |
|------|------|------|------|------|------|
| 3.07 | 3.54 | 3.15 | 2.20 | 2.20 | 0.19 |

Product datasheet Connections and Schema

ABL6TS06J


Internal Scheme




Product datasheet Connections and Schema

ABL6TS06J

Primary Voltage Wiring





Product datasheet Connections and Schema

ABL6TS06J

Secondary Voltage Wiring

