UL Recognised Wirewound Resistors





ULW Series

- UL1412 recognised fusible resistor *
- Failsafe mains fusing at 120 / 240Vrms
- Inrush and surge withstanding
- UL94-V0 flameproof coating
- Surface mount ZI-form option



All Pb-free parts comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)

Electrical Data

		ULW2 / ULWP2R	ULW3	ULW4	ULW5			
Power rating at 25°C	watts	2	3	4	5			
5 second overload rating at 25°C	watts	10	10 15 20 25					
Inrush / surge performance			See Pulse Performance graphs					
Resistance range	ohms	1R0 to 100R						
TCR	ppm/°C		±200					
Isolation voltage	volts	250	250 350 500					
Resistance tolerance	%		5					
UL recognised standard values	ohms	An	Any value in the range 1R0 to 100R is recognised. E24 preferred					
Thermal impedance	°C/watt	110 82 62 54						
Ambient temperature range	°C	-55 to +155						

Note - no limiting element voltage applies; maximum continuous voltage is V(P.R)

Physical Data

	Dimensions (mm) and weight (g)									
Type	L Max	D Max	f min	d nom	PCB mount centres	Min bend radius	Wt. Nom	~		
ULW2	9.0	3.8	19.8		12.7		0.5	√ d ——		
ULW3	14.5	5.8	24.6	0.8	20.3	1.2	1.1	D		f
ULW4	13	5.6	22.8	0.0	18.9		1.0	I	L	1 '
ULW5	16.5	7.2	23.6		22.9		1.8			

Construction

A high purity ceramic rod is assembled with interference fit end caps to which are welded the terminations. The surge withstanding resistive element is wound on the rod and welded to the caps. Flameproof fusible cement coating is applied prior to marking with indelible ink. The components are then leadformed if required and packed.

Marking

ULW2, ULWP2R & ULW3 resistors are marked with five colour bands. The first four indicate value and tolerance in conformance with IEC62. The fifth yellow band denotes defined fusibility. ULW4 and ULW5 resistors are legend marked with type, value and tolerance.

General Note

BI Technologies IRC Welwyn

^{*} UL file number E234469.

UL Recognised Wirewound Resistors



ULW Series

Terminations

Material: Hot tin dipped copper wire

Strength: The terminations meet the requirements of IEC 68.2.21

Solderability: The terminations meet the requirements of IEC 115-1 Clause 4.17.3.2

Solvent Resistance

The body protection and marking are resistant to all normal industrial cleaning solvents suitable for printed circuits.

Flammability


The resistor coating will not burn or emit incandescent particles under any condition of applied temperature or power overload.


Performance Data

		Maximum*	Typical
Load at rated power (1000 hours @ 25°C)	ΔR%	5	3
Short term overload (5 x Pr for 5 seconds)	ΔR%	5	1
Pulse (see Pulse Performance graphs)	ΔR%	5	2
Climatic	ΔR%	5	2
Long term damp heat (56 days)	ΔR%	5	1
Climatic category		55/20	0/56
Temperature rapid change	ΔR%	5	1
Dry heat (1000 hours @ 200°C)	ΔR%	5	3
Vibration	ΔR%	5	1
Robustness & solder heat	ΔR%	5	1

^{*} Addition of 0.01Ω applies

Thermal Performance






General Note

UL Recognised Wirewound Resistors






Pulse Performance



Fusing Performance




UL Recognised Wirewound Resistors






Fusing Performance

ULW3 & ULW4 Fusing Characteristic



ULW5 Fusing Characteristic



Notes:

- 1. Typical fusing times are around 1/3 of the maximum figures.
- After fusing the resistance value is >100 times the initial nominal value, provided the initial power is at least 20 x rated power.
- 3. Suitable for fusing at voltages up to 264Vrms.

UL Recognised Wirewound Resistors






Application Notes

- 1. If the resistors are to dissipate full rated power, it is recommended that the terminations should not be soldered closer than 4mm from the body.
- 2. Due to operating temperature limits imposed by some PCB materials, derating may be necessary. An estimate of the temperature rise to be expected can be calculated using the thermal impedance figures given under Electrical Data.
- 3. For the purposes of UL approval, the following points should be observed:
 - 3.1 To protect against fire under all conditions of overload, a positive clearance of at least
 - 13mm should be provided between the body of the resistor and any combustible materials.
 - 3.2 A positive clearance of 13mm should be provided between the resistor body or terminations and uninsulated parts of opposite polarity or uninsulated dead metal parts.
 - 3.3 Limited Short Circuit testing should be performed in the complete appliance.
- 4. ULW resistors can also be supplied with radial, goalpost or lancet pre-formed leads see https://www.ttelectronics.com/TTElectronics/media/ProductFiles/Resistors/ApplicationNotes/TN008-resistors-Leadform-Capability.pdf. ULW2, ULW3, ULW4 and ULW5 are available in ZI-form SMD format packed in blister tape - see https://www.ttelectronics.com/TTElectronics/media/ProductFiles/Resistors/Datasheets/ZI-form.pdf

Hairpin	Goalpost	Lancet	ZI-form

Also a 2W and 3W radial taped version is available as shown below

Radial Taped Dimensions (mm)								
Dimension	Notation	ULWP2R	ULW3R					
Component body length	L	10.0 Max	14.5 Max					
Component body diameter	D	4.0 Max	5.8 Max					
Terminal lead diameter	d	1 8.0	Nom					
Component pitch	Р	12.7±0.5	12.7±1.0					
Hole pitch	Po	12.7±0.2	12.7±0.3					
	P1	3.85±0.3	3.85±0.7					
Component to hole offset	P2	5.85±0.5	6.35±1.3					
Lead pitch	F	5.0 +0.75 -0.34	5.0±1.0					
Width of backing strip	W	18.0±0.3	18.0±1.0					
Position of hole	W1	9.0±0.25	9.0±0.5					
Diameter of hole	Do	4.0±0.3						
Height to lead form	form Ho 16.0±0		17.0±1.0					
Height from lead form	Ho1	17.0 Max 23.0 Ma						
Height to resistor	Ho2	18.0 Min						
Width of adhesive tape	W0	15.0±0.5						
Length of protrusion	I	<2.5						
	K1	2.0±0.3						
	K2	3.0±0.5						
Form dimensions	К3	1.5±	0.25					
	K4	1.0±	±0.2					
	K5		2.0 Min					



General Note


UL Recognised Wirewound Resistors



ULW Series

Packaging

The standard packaging for ULW is taped. The critical dimensions are shown in Figure 1. The component wires will not protrude beyond the outside edge of the tapes. Taped product is then packed into ammo boxes for ULW2, 3 and 4 or onto reels for ULW5. Alternative packaging is available by request. The standard packaging for ULWP2R is tape and reel. Pre-formed radial, goalpost & lancet resistors are supplied loose packed in plastic bags or boxes. ZI-form SMD are packed in blister tape.



Note 1: Cumulative tolerance over 10 pitches is ±2mm

Ordering Procedure

Example: ULW2-33RJA25 (ULW2, 33 ohms ±5%, Pb-free)



1	2	3	4	5			
Туре	Leadforming	Value	Tolerance	Packing			
ULW2	Optional code	3/4 characters	J = ±5%	A25	ULW2	Ammo pack, 2500/box	
ULW3		R = ohms		A1	ULW3, ULW4	Ammo pack, 1000/box	
ULW4			-	T075	ULW5	Tape & reel, 750/reel	
ULW5			'				

Example: ULWP2R-33RJT15 (ULWP2R radially formed & taped, 33 ohms ±5%, Pb-free)



1	2	3	4		5		
Туре	Leadforming	Value	Tolerance	e Packing			
ULWP2	R = Radial taped	3/4 characters R = ohms	J = ±5%	T15	ULWP2R	Tape & reel	1500/reel
ULW3				A2	ULW3R	Ammo pack	2000/box
	•			T1	OLVVSK	Tape & reel	1000/reel

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TT Electronics:

ULW2-100R0JA25 ULW2-22R0JA25 ULW2-24R0JA25 ULW2-27R0JA25 ULW2-30R0JA25 ULW2-33R0JA25 ULW2-36R0JA25 ULW2-39R0JA25 ULW2-43R0JA25 ULW2-47R0JA25 ULW2-51R0JA25 ULW2-56R0JA25 ULW2-62R0JA25 ULW2-68R0JA25 ULW2-75R0JA25 ULW2-82R0JA25 ULW2-91R0JA25 ULW3-100R0JA1 ULW3-10R0JA1 ULW3-15R0JA1 ULW3-18R0JA1 ULW3-20R0JA1 ULW3-22R0JA1 ULW3-24R0JA1 ULW3-27R0JA1 ULW3-30R0JA1 ULW3-33R0JA1 ULW3-36R0JA1 ULW3-39R0JA1 ULW3-43R0JA1 ULW3-47R0JA1 ULW3-51R0JA1 ULW3-56R0JA1 ULW3-62R0JA1 ULW3-68R0JA1 ULW3-75R0JA1 ULW3-82R0JA1 ULW3-91R0JA1 ULW5-15R0JA1 ULW5-18R0JA1 ULW5-20R0JA1 ULW5-22R0JA1 ULW5-24R0JA1 ULW5-27R0JA1 ULW5-30R0JA1 ULW5-33R0JA1 ULW5-36R0JA1 ULW5-39R0JA1 ULW5-43R0JA1 ULW5-47R0JA1 ULW5-51R0JA1 ULW5-56R0JA1 ULW5-62R0JA1 ULW5-68R0JA1 ULW5-75R0JA1 ULW5-82R0JA1 ULW5-91R0JA1 ULW5-100R0JT075 ULW5-10R0JT075 ULW5-15R0JT075 ULW5-18R0JT075 ULW5-20R0JT075 ULW5-22R0JT075 ULW5-24R0JT075 ULW5-27R0JT075 ULW5-30R0JT075 ULW5-33R0JT075 ULW5-36R0JT075 ULW5-39R0JT075 ULW5-43R0JT075 ULW5-47R0JT075 ULW5-51R0JT075 ULW5-56R0JT075 ULW5-62R0JT075 ULW5-68R0JT075 ULW5-75R0JT075 ULW5-82R0JT075 ULW5-91R0JT075 ULW5-4R7JT075 ULW3-22RJA1 ULW3-33RJA1 ULW2-22RJA25 ULW5-33RJT075 ULW3-15RJA1 ULW2-100RJA25 ULW3-100RJA1 ULW2-33RJA25 ULW2-47RJA25 ULW5-68RJT075 ULW5-47RJT075 ULW5-27RJT075 ULW5-22RJT075 ULW3-68RJA1 ULW5-10RJT075 ULW2-68RJA25 ULW3-10RJA1 ULW3-27RJA1 ULW3-47RJA1 ULW5-100RJT075 ULW3-39RJA1