



MCP3004 ☆

10-Bit, 200kSPS, 4-Channel ADC

Status: In Production

 [View Datasheet](#)

Features:

- 10-bit resolution
- Four single-ended channels
- SPI interface
- ± 1 LSB DNL
- ± 1 LSB INL
- 200 kSPS sample rate at 5V

[View More](#)



Recommended for
Automotive Designs



Sampling
Options

 [Overview](#)

 [Documents](#)

Downloaded from [Arrow.com](https://www.arrow.com)

Device Overview

Summary

The MCP3004 10-bit Analog-to-Digital Converter (ADC) combines high performance and low power consumption in a small package, making it ideal for embedded control applications. The MCP3004 features a successive approximation register (SAR) architecture and an industry-standard SPI serial interface, allowing 10-bit ADC capability to be added to any PIC® microcontroller. The MCP3004 features 200k samples/second, 4 input channels, low power consumption (5nA typical standby, 425µA typical active), and is available in 14-pin PDIP, SOIC and TSSOP packages. Applications for the MCP3004 include data acquisition, instrumentation and measurement, multi-channel data loggers, industrial PCs, motor control, robotics, industrial automation, smart sensors, portable instrumentation and home medical appliances.

Additional Features

- 10-bit resolution
- Four single-ended channels
- SPI interface
- ± 1 LSB DNL
- ± 1 LSB INL
- 200 ksps sample rate at 5V
- -40 to +85°C temperature range
- AEC-Q100 Grade 3

Parametrics

| Name | Value |
|--------------------------------|--------------|
| Max Sample Rate (ksamples/sec) | 200 |
| Typ. INL \pm (LSB) | 0.5 |
| Max. Supply Current (μ A) | 500 |
| Input Type | Single-ended |
| # of Input Channels | 4 |
| Resolution (bits) | 10 |

Interface

SPI

Temp Range (°C)

-40 to +85°C

Input Voltage Range (V)

0 to 5.5



This website uses cookies for analytics, personalization, and other purposes. Click to learn more. By continuing to browse, you agree to our use of cookies as described in our [Cookies Statement](#).

©Copyright 1998-2020 Microchip Technology Inc. All rights reserved.

[Learn More](#)

[OK](#)