



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION SEPTEMBER , 2006.
 © COPYRIGHT 2006 By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
E	B	P	LTR	DESCRIPTION	DATE	DWN	APVD
		D		ECO-13-012122	13NOV2013	RZ	MY
		1.1		9-1478242-0	RG58C/U, 141A/U, 303/U, URM43, 76, BELDEN 9907, KX15		5-1814802-3
		1.1		9-1478242-0	RG58C/U, 141A/U, 303/U, URM43, 76, BELDEN 9907, KX15		5-1814802-2
		0.57		9-1478242-0	RG174A/U, 188A/U, 316/U, URM95, KX3B, KX22A		5-1814802-1
		0.57		9-1478242-0	RG174A/U, 188A/U, 316/U, URM95, KX3B, KX22A		5-1814802-0
		A		DIE SET	CABLE GROUPS		PART NO.

- NOTES**
- PACKAGE ONE COMPLETE CONNECTOR IN HEAT SEALED, LABELED BAG/ 50 BAGS PER INNER BOX/ 20 BOXES PER SHIPPING CARTON (TOTAL 1000 PCS PER SHIPPING CARTON)
 - 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
 - Au PLATING
 - Ni PLATING
 - HAND TOOL: 9-1478240-0
 - DIE SET: SEE TABLE
 - ELECTRICAL CHARACTERISTICS
 FREQUENCY RANGE: DC - 4 GHz
 NOMINAL IMPEDANCE: 50 Ohm
 INSULATION RESISTANCE: 5000 MOhm
 WORKING VOLTAGE: 500 Volts RMS at Sea Level
 DIELECTRIC WITHSTAND VOLTAGE: 1500 Volts RMS Max
 CONTACT RESISTANCE:
 CENTRE CONTACT: 1.50 mOhm Max
 OUTER CONTACT: 1.00 mOhm Max
 VSWR @ 4GHz: 1.30:1 Max
 INSERTION LOSS dB @ x 3 GHz: 0.20 Max
 - MECHANICAL CHARACTERISTICS
 CABLE RETENTION FORCE: RG58C/U: 170N Min
 CABLE RETENTION FORCE: RG174A/U: 85N Min
 MOUNT NUT RECOMMENDED TORQUE: 4N
 DURABILITY: 50 Cycles Min
 - ENVIRONMENTAL CHARACTERISTICS
 OPERATING TEMPERATURE: -65 to +85 DegC
 - FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
 - ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED










	OBSOLETE	OBSOLETE	OBSOLETE			
1	1	1	1	BRASS	HEXAGON NUT	9
1	1	1	1	PHOSPHOR BRONZE	WASHER	8
1	1	1	1	SILCON RUBBER	GASKET	7
-	-	1	1	BRASS	FERRULE	6
-	-	1	1	NYLON	PUSHER SLEEVE	5
1	1	-	-	BRASS	FERRULE	4
1	1	1	1	DELTRIN	INSULATOR	3
1	1	1	1	PHOSPHOR BRONZE	CONTACT	2
1	1	1	1	ZINC ALLOY	BODY	1
5	35	25	15	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SANDWELL 26SEP06	TE Connectivity	
DIMENSIONS: MM		CHK S.PARLOW 26SEP06	NAME TNC BULKHEAD CRIMP JACK - 50 OHM	
TOLERANCES UNLESS OTHERWISE SPECIFIED		APVD F.WHEELER-KING 26SEP06	DRAWING NO C=1814802	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-112000	SIZE A2	RESTRICTED TO
MATERIAL SEE TABLE		APPLICATION SPEC SEE SHEET 2	CAGE CODE 00779	SCALE NTS
FINISH SEE TABLE		WEIGHT -	DRAWING NO C=1814802	SHEET 1 of 2
		CUSTOMER DRAWING	SCALE NTS	REV D















THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION SEPTEMBER, 2004.
 © COPYRIGHT 2006 By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B	-	-	SEE SHEET 1	-	-	-

COMPONENTS

HEX NUT (ITEM 9)	LOCK WASHER (ITEM 8)	GASKET (ITEM 7)	MAIN BODY (ITEM 1,3,)	CENTRE CONTACT (ITEM 2)	PUSHER SLEEVE (ITEM 5)	CRIMP FERRULES (ITEM 4 & 6)
						

ASSEMBLY INSTRUCTION

CABLES: RG59B/U, 62A/U, 140/U, 210/U, URM90, KX 6A, KX 25, KX 52, KX 53, RG58C/U, 141A/U, URM43, 76, BELDEN 9907, KX 15	CABLES: RG179B/U, 187A/U, URM111
<p>STEP 1</p> <p>1. SLIDE METAL CRIMP FERRULE OVER CABLE</p> 	<p>STEP 1</p> <p>1. SLIDE METAL CRIMP FERRULE OVER CABLE</p> 
<p>STEP 2</p> <p>1. STRIP CABLE TO DIMENSIONS AS SHOWN</p> 	<p>STEP 2</p> <p>1. STRIP CABLE TO DIMENSIONS AS SHOWN</p> 
<p>STEP 3</p> <p>1. FIT CONTACT OVER CENTRE CONDUCTOR TO BUTT AGAINST DIELECTRIC. 2. CRIMP USING TOOL AS NOTES ON PAGE 1.</p>  <p>RECOMMENDED CENTRE CONTACT A/F HEX</p> 	<p>STEP 3</p> <p>1. SLIDE ITEM 10 PUSHER SLEEVE OVER DIELECTRIC BEFORE FITTING THE CONTACT. 2. FIT CONTACT OVER CENTRE CONDUCTOR TO BUTT AGAINST DIELECTRIC. 3. CRIMP USING TOOL AS NOTES ON PAGE 1.</p>  <p>RECOMMENDED CENTRE CONTACT A/F HEX</p> 
<p>STEP 4</p> <p>1. PRESS SUB-ASSEMBLY INTO BODY, UNTIL CONTACT IS FULLY LOCATED BY AN AUDIBLE CLICK. 2. ENSURE THAT KNURLED HOUSING INSERTS BETWEEN THE DIELECTRIC AND CABLE BRAID.</p>  <p>HOUSING END UNDER BRAID</p>	<p>STEP 4</p> <p>1. PRESS SUB-ASSEMBLY INTO BODY, UNTIL CONTACT IS FULLY LOCATED BY AN AUDIBLE CLICK. 2. ENSURE THAT KNURLED HOUSING INSERTS BETWEEN THE PUSHER SLEEVE AND CABLE BRAID.</p>  <p>HOUSING END UNDER BRAID</p>
<p>STEP 5</p> <p>1. SLIDE CRIMP FERRULE ALONG THE CABLE UNTIL IT BUTTS AGAINST THE HOUSING BODY. 2. CRIMP USING TOOL AS NOTED ON PAGE 1. 3. CRIMP DIMENSION X IS:- RG59B (SEE PAGE 1 FOR FULL CABLE LIST) = 6.50 RG58C/U (SEE PAGE 1 FOR FULL CABLE LIST) = 5.60</p>  <p>RECOMMENDED CRIMP SLEEVE A/F HEX</p> 	<p>STEP 5</p> <p>1. SLIDE CRIMP FERRULE ALONG THE CABLE UNTIL IT BUTTS AGAINST THE BODY HOUSING. 2. CRIMP USING TOOL AS NOTED ON PAGE 1. 3. CRIMP DIMENSION AS SHOWN.</p>  <p>RECOMMENDED CRIMP SLEEVE A/F HEX</p> 

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	RITA ZUO	11 Mar 09
CHK	ANSON MA	11 Mar 09
APVD	BOB ZHAO	11 Mar 09
PRODUCT SPEC	108-112000	
APPLICATION SPEC	SEE SHEET 2	
WEIGHT	-	
CUSTOMER DRAWING		

TE Connectivity

TNC BULKHEAD CRIMP JACK - 50 OHM

SIZE: A2 CAGE CODE: 00779 DRAWING NO: 1814802 RESTRICTED TO: -

SCALE: NTS SHEET: 2 OF 2 REV: D