




1887113-4 Product Details

[Share](#) | [Print](#) | [Email](#)


1887113-4
(XT374S15)

TE Internal Number: 1887113-4

[Active](#)

Industrial Relays (General Purpose)

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Relay Type = Interface Plug-In Relay
- Relay Style = Power
- XT Series
- Contact Arrangement = 1 Form C, SPDT, 1 C/O
- Contact - Rated Current = 16 A

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Series = XT
- [Termination Type](#) = Plug-in

Electrical Characteristics:

- [Contact - Rated Current \(A\)](#) = 16
- [Input Voltage \(VAC\)](#) = 115
- [Coil Resistance \(Ω\)](#) = 8100
- [Actuating System](#) = AC
- [Coil - Rated Power \(VA\)](#) = 0.76
- Insulation - Special Features = None
- Insulation - Initial Dielectric Between Contacts and Coil (V rms) = 4000
- Insulation - Tracking Index of Relay Base = PTI175
- Release/Reset Voltage (V) = 17.3

Body Features:

- Insulation - Clearance/Creepage = 8.0mm Clearance 8.0mm Creepage
- Polarized = No
- Enclosure Color = Clear

Contact Features:

- Relay Type = Interface Plug-In Relay
- [Mounting Options](#) = Socket
- [Enclosure Type](#) = Dust Cover
- [Contact Base Material](#) = Silver Nickel 90/10
- Approx. Dimensions (L x W x H) (mm [in]) = 29.0 x 13.7 x 26.7 [1.141 x .539 x 1.051]
- Test Button = With
- Contact Configuration = Single
- Pin Configuration = Industry Standard 5mm
- Terminal Assignment = 1 Form C
- Number of Poles = 1

Housing Features:

- Operate/Set Voltage (V) = 86.3 - 97.8

Configuration Features:

- Relay Style = Power
- [Contact Arrangement](#) = 1 Form C, SPDT, 1 C/O
- [Coil - Magnetic System](#) = Monostable
- [Coil Suppression Diode](#) = Without
- [Coil Selection Criteria](#) = Nominal Voltage
- Coil Latching = Without
- Status Indicator = LED
- Number of Coils = 1

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant
- Approved Standards = VDE Component Mark, CE Mark, UL Recognized for Canada and US

Packaging Features:

- Packaging Method = Carton Bar

Other:

- Brand = Schrack

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

