

PRODUCT DATA SHEET

3502 Double Sided PE Foam Tape

Last update: 27.07.2020r.

TECHNICAL CHARACTERISTICS	
Backing	PE Foam
Adhesive	Modified acrylic
Liner	PE/Paper
TECHNICAL PROPERTIES	
Total Thickness	1,0 ±0,02 [mm]
Colour	White
Density	67 kg/m ³
Temperature resistance	-20 do +100°C
Adhesion to steel	10 N/cm
Test method	ASTM D-1000
SIZE	
Length	66[m]
Width	On customer demand

Recommendations:

- Recommended application temperature is to be between +10°C and +30°C.
- Mounting elements should be dry, dust and oil free.
- To clean surfaces use dedicated CLEANER chemicals.
- Use PRIMER if increase adhesion is needed.
- Connected elements have to be evenly pressed with a force of 10N/cm with a pressure roller.
- Storage life – 24 months (Temperature about 20°C, R.H. – 50-60%)

The above technical information is presented based on the average laboratory tests and can not be used as binding technical data for design purposes, they should not be used as a basis for granting the guarantee. The user is fully responsible for the decision to use the product and for its installation. Before using it is recommended to analyse the product features considering the type of combined materials, the state of its surface and application conditions.