Surface Mount Red LED 3.5mm × 2.8mm

multicomp PRO

RoHS

Compliant



Features

- 3.5mm × 2.8mm SMT LED, 1.9mm Thickness
- Wide Viewing Angle
- Ideal for Backlight and Indicator

Applications

- · Automotive: backlighting in dashboard and switch
- · Telecommunication: indicator and backlighting in telephone and fax
- Flat backlight for LCD switch and symbol

Device Selection

С	Lens Colour		
Material	Emitted Colour	Lens Colour	
InGaAlP	Red	Water Clear	

Absolute Maximum Ratings at T_A = 25°C

Parameter	Symbol	Values	Unit
Power Dissipation	PD	62	mW
Forward Current	lf	25	mA
Peak Forward Current*	I FP	100	mA
Reverse Voltage	VR	5	V
Operating Temperature	Topr	-40 to +85	°C
Storage Temperature	Tstg	-40 to +85	°C

Note:

*Pulse width ≤0.1ms, Duty cycle ≤1/10

Electrical / Optical Characteristics at TA = 25°C

Parameter	Symbol	Min.	Тур.	Max.	Unit	Test Conditions
Forward Voltage	VF	1.8	-	2.6	V	I⊧ = 20mA
Reverse Current	Ir	-	-	10	μA	VR=5V
Dominate Wavelength	λd	617	-	629	nm	IF = 20mA
Luminous Intensity	lv	225	-	500	mcd	IF = 20mA
Viewing Angle	201/2	-	120	-	Deg.	IF = 20mA

Remarks:


If special sorting is required (e.g. binning based on forward voltage, luminous intensity, or chromaticity), the typical accuracy of the sorting process is as follows:

- 1. Wavelength: ±1nm
- 2. Luminous Intensity: ±15%
- 3. Forward Voltage: ±0.1V

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Typical Electrical / Optical Characteristics Curves




Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




multicomp PRO

Diagram



Dimensions : Millimetres (Inches) Tolerance is ±0.25mm

Soldering Profile



Notes

- 1. We recommend the reflow temperature 245°C. (±5°C) The maximum soldering temperature should be limited to 260°C.
- 2. Don't cause stress to epoxy resin while it is exposed to high temperature.
- 3. Number of reflow process shall be 2 times or less.



1,6

1,5

Recommended soldering pattern

Dimensions : Millimetres

1,5

Part Number Table

Description	Part Number	
Surface Mount LED, Red, 2.6V, 500 mcd, 629nm	MP001253	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility for such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

