





precision thin (metal) film flat chip resistors (high reliability)




applications

- Automotive electronics
- Industrial equipment
- Measurement equipment
- For higher precision, RN73H series is available


features





- High temperature exposure: ΔR of ±0.25%
- High precision type ±0.05% is also available
- Low current noise
- Improved moisture resistance by high humidity protective coating
- Suitable for control circuits in various industrial equipment
- Products meet EU RoHS requirements
- Rated ambient temperature: 85°C, rated up to +155°C
- Sulfur resistance verified according to ASTM B 809-95

dimensions and construction



					Sul	ostrat	е				
Derating Curve											
100								_			
% Rated Power 80 99 90 90 90 90 90 90 90 90 90 90 90 90	i							$ \cdot $			
	i										
	i										
	i										
20	Ή.							1			

40 60 80


20

Ambient Temperature (°C) For resistors operated at an ambient temperature of 85° C or above, a power rating shall be derated in accordance with the above derating curve.

85


100 120

Туре	Dimensions inches (mm)									
(Inch Size Code)	L	W	С	d	t					
1E (0402)	.039 +.004 002 (1.0 _{-0.05})	.020±.002 (0.5±0.05)	.010±.004 (0.25±0.1)	.010 +.002 004 (0.25 +0.05)	.014±.002 (0.35±0.05)					
1J (0603)	.063±.008 (1.6±0.2)	.031±.004 (0.8±0.1)	.012±.004 (0.3±0.1)	.012±.004 (0.3±0.1)	.018±.004 (0.45±0.1)					
2A (0805)	.079±.008 (2.0±0.2)	.049±.008 (1.25±0.2)	.016±.008 (0.4±0.2)	.012 +.008 004 (0.3 +0.2)	.02±.004 (0.5±0.1)					
2B (1206)	.126±.008 (3.2±0.2)	.063±.008 (1.6±0.2)	.02±.012 (0.5±0.3)	.016 +.008 004 (0.4 +0.2)	.024±.004 (0.6±0.1)					
2E (1210)	.126±.008 (3.2±0.2)	.098±.008 (2.5±0.2)	.02±.012 (0.5±0.3)	.016 +.008 004 (0.4 +0.2)	.024±.004 (0.6±0.1)					



For resistors operated at a terminal part temperature of described for each size or above, a power rating shall be derated in accordance with derating curve. Please refer to "Introduction of the derating curves based on the terminal part temperature" in the beginning of our catalog before use.

ordering information



Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.

Resistance Tolerance		T.C (ppm	
A: ±0.05%		0	5
B: ±0.1%		1	0
C: ±0.25%		2	5
D: ±0.5%		5	0
F: ±1.0%		10	00
or 1100	10/	20/20	





precision thin (metal) film flat chip resistors (high reliability)

applications and ratings

Part Designation	Power Rating	Rated Ambient	Rated Terminal Part	T.C.R. (x10 ⁻⁶ /K)	Resistance Range (Ω) E-24, E-96, E-192					Maximum Working	Maximum Overload
	@ 85°C	Temp.	Temp.	(2110 /11)	(A±0.05%)	(B±0.1%)	(C±0.25%)	(D±0.5%)	(F±1.0%)	Voltage	Voltage
	1/16W (.063W)	85°C	90°C	±10	_	47 - 10k	47 - 10k	47 - 10k	47 - 10k	50V	100V
RN73R1E				±25	_	47 - 300k	47 - 300k	10 - 300k	10 - 300k		
	(.00377)			±50	_	47 - 300k	47 - 300k	10 - 300k	10 - 300k		
				±5	100 - 59k	100 - 59k	_	_	_	75V 150V	
		85°C	95°C	±10	47 - 59k	47 - 59k	47 - 59k	47 - 59k	47 - 59k		150V
RN73R1J	1/10W			±25	47 - 59k	15 - 1M	15 - 1M	10 - 1M	10 - 1M		
	(.10W)			±50	_	15 - 1M	15 - 1M	10 - 1M	10 - 1M		
				±100	_	_	_	10 - 1M	10 - 1M		
	1/8W (.125W)	85°C	100°C	±5	100 - 100k	100 - 100k	_	_	_	150V	300V
				±10	47 - 100k	47 - 100k	47 - 100k	47 - 100k	47 - 100k		
RN73R2A				±25	47 - 100k	15 - 1.5M	15 - 1.5M	10 - 1.5M	10 - 1.5M		
				±50	_	15 - 1.5M	15 - 1.5M	10 - 1.5M	10 - 1.5M		
				±100	_		_	10 - 1.5M	10 - 1.5M		
	1/4W (.25W)	85°C	110°C	±5	100 - 300k	100 - 300k	_	_	_	200V	400V
				±10	47 - 300k	47 - 300k	47 - 300k	47 - 300k	47 - 300k		
RN73R2B				±25	47 - 300k	15 - 1M	15 - 1M	10 - 1M	10 - 1M		
				±50	_	15 - 1M	15 - 1M	10 - 1M	10 - 1M		
				±100	_	_	_	10 - 1M	10 - 1M		
	1/4W (.25W)		110°C	±10	100 - 510k	100 - 510k	100 - 510k	100 - 510k	100 - 510k	200V	400V
RN73R2E				±25	51 - 510k	15 - 1M	15 - 1M	10 - 1M	10 - 1M		
THIT SHEL				±50	_	15 - 1M	15 - 1M	10 - 1M	10 - 1M		
				±100	_	_	_	10 - 1M	10 - 1M		

Operating Temperature: -55°C to +155°C

Rated voltage = $\sqrt{\text{Power rating x resistance value}}$ or max. working voltage, whichever is lower

environmental applications

Performance Characteristics

	Requirement Δ R ±(%	-+0.05Ω)	
Parameter	Limit	Typical	Test Method
Resistance	Within specified tolerance	_	25°C
T.C.R.	Within specified T.C.R.	_	+25°C/+125°C: T.C.R. ±5 (x10°/K); +25°C/-55°C and +25°C/+155°C: other
Overload (Short time)	±0.05%	±0.01%	Rated Voltage x 2.5 or Max. overload voltage, whichever is less for 5 seconds
Resistance to Solder Heat	±0.05%*	±0.01%	260°C ± 5°C, 10 seconds ± 1 second
Rapid Change of Temperature	±0.1%*	±0.04%	1E, 1J, 2A: -55°C (30 minutes), +155°C (30 minutes), 1000 cycles 2B, 2E: -55°C (30 minutes), +155°C (30 minutes), 500 cycles
Moisture Resistance	±0.25%	±0.07%	85°C ± 2°C, 85%±5%RH, 1000 hours; 1.5 hr ON, 0.5 hr OFF cycle
Endurance at 85°C	±0.1%	±0.04%	85°C ± 2°C, 1000 hours, 1.5 hr ON, 0.5 hr OFF cycle
High Temperature Exposure	±0.25%	±0.10%	+155°C, 1000 hours

^{*} Depends on resistance value, please contact KOA Speer for details.

Precautions for Use

- The properly and electrostatically measured taping materials are used for the components, but attention should be paid to the fact that there is some danger the parts absorb on the top tapes to cause a failure in the mounting and the parts are destructed by static electricity (1J, 2A, 2B: 1kV and more, 1E: 0.5kV and more at Human Body Model 100pF, 1.5kΩ) to change the resistance in the conditions of an excessive dryness or after the parts are given vibration for a long time as they are packaged on the tapes. Similarly, care should be given not to apply the excessive static electricity when mounting on the boards.
- lonic impurities such as flux etc. that are attached to these products or those mounted onto a PCB, negatively affect their moisture resistance, corrosion
 resistance, etc. The flux may contain ionic substances like chlorine, acid, etc. while perspiration and saliva include ionic impurities like sodium (Na+), chlorine (Cl-)
 etc. Therefore these kinds of ionic substances may induce electrical corrosion when they invade into the products. Either thorough washing or using RMA solder
 and flux are necessary since lead free solder contains ionic substances. Washing process is needed, before putting on moisture proof material in order to prevent
 electrical corrosion.
- When heat-resistant masking tapes are attached to the chip resistors at the time of mounting and then detached, there is a possibility of exfoliation of the top
 electrodes. It is known that the heat applied in the mounting process will enhance the adhesion strength of the tape adhesive so please avoid the use. If the use of
 masking tapes are unavoidable, then please be sure not to attach the tape adhesives directly on the products.

When high-pressure shower cleaning is implemented, there is a possibility of exfoliation of the top electrodes caused by the water pressure stress so please avoid the implementation. If the implementation is unavoidable, then please evaluate the products beforehand.

For Surface Temperature Rise Graph see Environmental Applications. Additional environmental applications can also be found at www.koaspeer.com Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KOA Speer:

<u>RN73R2BTTD23R7C25</u> <u>RN73R2BTTD2400C25</u> <u>RN73R2BTTD2400C50</u> <u>RN73R2BTTD2401A10</u>
<u>RN73R2BTTD2402A25</u> <u>RN73R2BTTD2430A25</u> <u>RN73R2BTTD2430F10</u> <u>RN73R2BTTD2460F10</u>
<u>RN73R2BTTD2462A25</u> <u>RN73R2BTTD2490A25</u> <u>RN73R2BTTD2490F10</u> <u>RN73R2BTTD2492A25</u>
<u>RN73R2BTTD24R6C50</u> <u>RN73R2BTTD2520B25</u> <u>RN73R2BTTD2520C50</u> <u>RN73R2BTTD2521C25</u>
<u>RN73R2BTTD2522B50</u> <u>RN73R2BTTD2523B25</u> <u>RN73R2BTTD2523C50</u> <u>RN73R2BTTD2550C10</u>
<u>RN73R2BTTD2550C50</u> <u>RN73R2BTTD2551C10</u> <u>RN73R2BTTD2552B25</u> <u>RN73R2BTTD2552C10</u>
<u>RN73R2BTTD2580B25</u> <u>RN73R2BTTD2580B50</u> <u>RN73R2BTTD2580C25</u> <u>RN73R2BTTD2612B05</u>
<u>RN73R2BTTD2671B05</u> <u>RN73R2BTTD2672B05</u> <u>RN73R2BTTD2702A05</u> <u>RN73R2BTTD2702A10</u>
<u>RN73R2BTTD2710A05</u> <u>RN73R2BTTD2710A10</u> <u>RN73R2BTTD2711A05</u> <u>RN73R2BTTD2711A10</u>
<u>RN73R2BTTD2712A05</u> <u>RN73R2BTTD2712A10</u> <u>RN73R2BTTD2712C25</u> <u>RN73R2BTTD2713B50</u>
<u>RN73R2BTTD2713C50</u> <u>RN73R2BTTD2740A05</u> <u>RN73R2BTTD2740B25</u> <u>RN73R2BTTD2741A10</u>
<u>RN73R2BTTD2741B05</u> <u>RN73R2BTTD2741C50</u> <u>RN73R2BTTD2742B50</u> <u>RN73R2BTTD2742C25</u>
<u>RN73R2BTTD2742D25</u> <u>RN73R2BTTD2742F25</u> <u>RN73R2BTTD2743B25</u> <u>RN73R2BTTD2743B50</u>
<u>RN73R2BTTD2743D100</u> <u>RN73R2BTTD2743D50</u> <u>RN73R2BTTD2743F100</u> <u>RN73R2BTTD2743F25</u>
<u>RN73R2BTTD2743F50</u> <u>RN73R2BTTD2770C25</u> <u>RN73R2BTTD2770D25</u> <u>RN73R2BTTD2770D50</u>
<u>RN73R2BTTD2770F50</u> <u>RN73R2BTTD2771D100</u> <u>RN73R2BTTD2771D25</u> <u>RN73R2BTTD2771D50</u>
<u>RN73R2BTTD2771F100</u> <u>RN73R2BTTD2772A10</u> <u>RN73R2BTTD2772B05</u> <u>RN73R2BTTD2801A05</u>
<u>RN73R2BTTD2802A05</u> <u>RN73R2BTTD2802B05</u> <u>RN73R2BTTD2803F50</u> <u>RN73R2BTTD2840D25</u>
<u>RN73R2BTTD2840D50</u> <u>RN73R2BTTD2840F100</u> <u>RN73R2BTTD2841D25</u> <u>RN73R2BTTD2841F25</u>
<u>RN73R2BTTD2842A10</u> <u>RN73R2BTTD2842D50</u> <u>RN73R2BTTD2842F25</u> <u>RN73R2BTTD2843D25</u>
<u>RN73R2BTTD2843F25</u> <u>RN73R2BTTD2870D100</u> <u>RN73R2BTTD2870F100</u> <u>RN73R2BTTD2870F50</u>
<u>RN73R2BTTD2871A05</u> <u>RN73R2BTTD2871D100</u> <u>RN73R2BTTD2871D25</u> <u>RN73R2BTTD2871F50</u>
<u>RN73R2BTTD2872A10</u> <u>RN73R2BTTD2872D25</u> <u>RN73R2BTTD2872F50</u> <u>RN73R2BTTD2873F50</u>
<u>RN73R2BTTD28R0D25</u> <u>RN73R2BTTD28R0D50</u> <u>RN73R2BTTD28R0F100</u> <u>RN73R2BTTD28R0F25</u>
<u>RN73R2BTTD28R0F50</u> <u>RN73R2BTTD28R7D25</u> <u>RN73R2BTTD28R7D50</u> <u>RN73R2BTTD28R7F25</u>