

# Customer Information Sheet

DRAWING No.: M22-60230XX

SHEET 2 OF 2


IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



**SPECIFICATION:**

**MATERIALS:**

MOULDING = NYLON 6T UL94V-0 BLACK

CONTACTS = BRASS

**FINISH (OVER NICKEL):**

GOLD ON CONTACT AREA, 100% TIN ON TAILS

**ELECTRICAL:**

CONTACT RESISTANCE = 20 MILLIOHMS MAX.

INSULATION RESISTANCE = 5000 MEGOHMS MIN.

CURRENT RATING = 1A MAX.

VOLTAGE RATING = 250V AC



VOLTAGE PROOF = 800V AC FOR 1 MINUTE

**ENVIRONMENTAL:**

TEMPERATURE RANGE = -55° TO +105°C


**PACKING:**

TUBE



**NOTES:**

1. ALL TOLERANCES ARE  $\pm 0.20$  UNLESS OTHERWISE STATED.



**ORDER CODE:**

**M22-6023042**

No. OF WAYS PER ROW  
30

FINISH: \_\_\_\_\_  
42 = SELECTIVE GOLD + 100% TIN

CP	6	14.12.09	10582
NAME	ISS.	DATE	C/NOTE
APPROVED: C.PENROSE			
CHECKED: R.ADDE			
DRAWN: D.BECK			
CUSTOMER REF.:			
ASSEMBLY DRG:			

**HARWIN**

HARWIN USA  
TEL: 603 893 5376  
FAX: 603 893 5396  
mis@harwin.com

HARWIN Europe (UK)  
TEL: 023 9231 4545  
FAX: 023 9231 4590  
mis@harwin.co.uk

HARWIN Asia  
TEL: +65 6 779 4909  
FAX: +65 6 779 3868  
mis@harwin.com.sg

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

**TOLERANCES**  
X =  $\pm 1$ mm  
X.X =  $\pm 0.25$ mm  
X.XX =  $\pm 0.10$ mm  
X.XXX =  $\pm 0.01$ mm  
ANGLES =  $\pm 5^\circ$   
UNLESS STATED

**MATERIAL:**  
SEE ABOVE  
**FINISH:** SEE ABOVE  
**S/AREA:** mm<sup>2</sup>

**TITLE:**  
PCI04 PLUS  
POST HEADER  
**DRAWING NUMBER:**  
M22-60230XX  
SHT  
2 OF 2