


Number of contacts

max. 32



Female connectors

Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
Female connector for crimp contacts Order contacts separately	32	09 04 032 3213	<p>85, 84, 11,6, 14,8, 8,5, 2,9-0,5, 10, 90±0,1, 2,8-0,1, 5,08, 2c, 2a, 5,1, 5, 10,6±0,02, 15 x 5,08 = 76,20, 8,17, 95-0,4</p> <p>Contact arrangement View from termination side</p>	
Shell housing 09 03 096 0501 page 94				

Identification	Identification Wire gauge	Part No.	Performance levels according to DIN 41 612, explanations page 10	Special
		2	1	
Female crimp contacts				
Bandoliered contacts (approx. 2500 pieces)	1	09 06 000 6484	09 06 000 6474	09 06 000 6424
	2	09 06 000 6481	09 06 000 6471	09 06 000 6421
	3	09 06 000 6482	09 06 000 6472	09 06 000 6422
Bandoliered contacts (approx. 300 pieces)	1	09 06 000 9484	09 06 000 9474	09 06 000 9421
	2	09 06 000 9481	09 06 000 9471	09 06 000 9422
	3	09 06 000 9482	09 06 000 9472	
Individual contacts	1	09 06 000 8484	09 06 000 8474	09 06 000 6434
	2	09 06 000 8481	09 06 000 8471	09 06 000 6431
	3	09 06 000 8482	09 06 000 8472	09 06 000 6432
Female contacts with solder lugs (lockable)	—			09 06 000 6420

please check change-over to performance level 1 or 2

Wire gauge	mm <sup>2</sup>	AWG	Insulation Ø mm	Identification
1	0.09 – 0.25	28 – 24	0.7 – 1.5	
2	0.14 – 0.56	26 – 20	0.8 – 2.0	
3	0.5 – 1.5	20 – 16	1.6 – 2.8	

3.5 + 0.5 mm of insulation is stripped from the wires to be crimped  
Crimping tools page 91