

# Features

## Common Mode Chokes

- RoHS compliant

## CMC-08

### Choke for RECOM Power Supply





### Specifications

BASIC CHARACTERISTICS			
Parameter	Condition		Value
Inductance	100kHz/100mV		Pin 1-2 830 $\mu$ H $\pm$ 35%
	Measurement Instrument: HP4263B LCR Meter		Pin 3-4 830 $\mu$ H $\pm$ 35%
Impedance	Measurement Instrument: HIOKI 3540 m $\Omega$ HiTester		RDC 31m $\Omega$ max.

DIMENSION AND PHYSICAL CHARACTERISTICS			
Rated Current	Measurement Instrument: Aligent 34401A Meter	IDC	3.3A max.
Rated Voltage			500VDC
Recommended Through Hole		$\emptyset$	0.8mm
Operating Temperature Range	-40°C to +105°C		



The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.