







# 9007MS02S0084

**LIMIT SWITCH** 



Download your 9007MS02S0084 datasheet



#### Characteristics | Documents & Downloads

Main — Hic	de
------------	----

9007 Range of product

Series name Miniature potted Product or component type Limit switch Device short name 9007MS/ML Sensor design Miniature Fixed **Body type** 

Head type Plunger head Material Metal **Body material** Cast zinc Number of poles

#### Complementary

Hide

Fixing mode By the body Movement of operating head Linear

Type of operator Spring return parallel roller plunger steel (-)

Type of approach Lateral approach 2 directions

Switch actuation By 30° cam Contacts type and

composition

NC-NO

SPDT Switch function **Contact form** Form C **Contacts material** Silver contacts Snap action **Contacts operation** Positive opening Without

**Electrical connection** Male connector M12 micro AC type 1 keyway 4 pins bottom

Terminals description ISO

(1-2)NC (1-3)NO (4)gnd

Maximum force for tripping 80 ozf

5 A at 28 V DC [le] rated operational current

3 A at 120 V AC 3 A at 240 V AC

[Ithe] conventional enclosed

thermal current

3 A

[Ui] rated insulation voltage 300 V degree of pollution 3 conforming to UL 508

300 V degree of pollution 3 conforming to CSA C22.2 No 14

**Electrical durability** 100000 cycles 10000000 cycles Mechanical durability

Marking CE

CSA UL

Sale per indivisible quantity

Height 1.75 in Width 1.56 in 0.62 in Depth **Product weight** 1.2 lb(US)

### **Environment**

Hide

**Shock resistance** 35 gn (duration = 9 ms) conforming to IEC 60068-2-27 Vibration resistance 10 gn (f = 75...1200 Hz) conforming to IEC 60068-2-6

**NEMA** degree of protection NEMA 1 conforming to Nema type 250

NEMA 2 conforming to Nema type 250 NEMA 4 conforming to Nema type 250 NEMA 6 conforming to Nema type 250 NEMA 6P conforming to Nema type 250

IP degree of protection IP67 conforming to IEC 60529

Ambient air temperature for

operation

-40...220 °F

Ambient air temperature for

storage

-40...220 °F

**Protective treatment** Epoxy powder coat

**Product certifications** CE CSA

UL

**Standards** LR 25490 Class 32 11 03

E78403

## Offer Sustainability

Hide

Green Premium product Sustainable offer status

RoHS (date code: YYWW) Compliant - since 1150 - Schneider Electric declaration of

Reference not containing SVHC above the threshold **REACh** 

**Product environmental** 

profile

Available download Product environmental

Product end of life instructions

Need no specific recycling operations

# Contractual warranty



Period 18 months