

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0465565745**  
**Status:** **Active**  
**Overview:** SEARAY and SEARAY Slim Mezzanine Family  
**Description:** Searay Slim Plug, 200 Circuits, 7.00mm Unmated Height, 4 Rows, with Pegs, Solder Charge Lead-Free

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-45970-002-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Application Specification AS-45970-990-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-45970-002-001 (PDF)</a>
<a href="#">Product Specification PS-45970-001-001 (PDF)</a>	<a href="#">Test Summary TS-45970-002-001 (PDF)</a>
<a href="#">Product Specification TS-45970-001-001 (PDF)</a>	<a href="#">Symbol Footprint Data SYM-46556-5745-001 (PDF)</a>
<a href="#">Application Specification AS-45970-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**


CSA	LR19980
UL	E29179

**General**

Product Family	PCB Headers
Series	46556
Application	Board-to-Board, Signal
Electrical Model	Yes
Overview	<a href="#">SEARAY and SEARAY Slim Mezzanine Family</a>
Product Name	SEARAY
UPC	883906482855

**Physical**

Breakaway	No
Circuits (Loaded)	200
Circuits (maximum)	200
Color - Resin	Black
Durability (mating cycles max)	100
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	4.906/g
Number of Rows	4
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	Pick and Place Cap
Shrouded	No



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[46556 Series](#)

**Mates With**

[46557 SEARAY Slim Receptacles](#)

Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55° to +125°C
Termination Interface: Style	Surface Mount
Unmated Height	7.00mm

**Electrical**

Current - Maximum per Contact	2.7A
Voltage - Maximum	240V AC

**Solder Process Data**

Duration at Max. Process Temperature (seconds)	020
Lead-free Process Capability	REFLOW
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

**Material Info****Reference - Drawing Numbers**

Application Specification	AS-45970-001-001, AS-45970-002-001, AS-45970-990-001
Electrical Model Document	EE-45970-010-010
Packaging Specification	PK-45970-002-001
Product Specification	PS-45970-001-001, TS-45970-001-001
S-Parameter Model	SP-45970-010-010
Sales Drawing	SD-46556-001-001
Symbol/Footprint Data	SYM-46556-5745-001
Test Summary	TS-45970-002-001

This document was generated on 12/27/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[46556-5745](#)