

STGFW40H65FB, STGW40H65FB, life.augmented STGWA40H65FB, STGWT40H65FB

Trench gate field-stop IGBT, HB series 650 V, 40 A high speed

Datasheet - production data





Figure 1: Internal schematic diagram



This is information on a product in full production.

Features

- Maximum junction temperature: T_J = 175 °C
- High speed switching series
- Minimized tail current
- Very low saturation voltage: V_{CE(sat)} = 1.6 V (typ) @ I_C = 40 A
- Safe paralleling
- Tight parameter distribution
- Low thermal resistance

Applications

- Photovoltaic inverters
- High frequency converters

Description

These devices are IGBTs developed using an advanced proprietary trench gate field-stop structure. These devices are part of the new HB series of IGBTs, which represent an optimum compromise between conduction and switching loss to maximize the efficiency of any frequency converter. Furthermore, the slightly positive V_{CE(sat)} temperature coefficient and very tight parameter distribution result in safer paralleling operation.

Table 1: Device summary

Order code	Marking	Package	Packing
STGFW40H65FB	GFW40H65FB	TO-3PF	Tube
STGW40H65FB	GW40H65FB	TO-247	Tube
STGWA40H65FB	GWA40H65FB	TO-247 long leads	Tube
STGWT40H65FB	GWT40H65FB	TO-3P	Tube

www.st.com

Contents

Contents 1 2 Electrical characteristics4 2.1 3 4 Package information12 4.1 4.2 TO-247 package information......14 TO-247 long leads package information16 4.3 4.4 5 Revision history20



1 Electrical ratings

		Value		
Symbol	Parameter	TO-247, TO-247 long leads, TO-3P	247 long leads, TO-3PF	
Vces	Collector-emitter voltage (V _{GE} = 0 V)	650		V
L.	Continuous collector current at $T_c = 25 \ ^{\circ}C$ 80			А
Continuous collector current at Tc = 100 °		40		~
Icp ⁽¹⁾	Pulsed collector current	160		А
Vge	Gate-emitter voltage	±20		V
Ртот	Total dissipation at T_C = 25 °C	283	62.5	W
Viso	Insulation withstand voltage (RMS) from all three leads to external heat sink $(t = 1 s; T_c = 25 \text{ °C})$ 3.5		kV	
Tstg	Storage temperature range -55 to 150		0	°C
TJ	Operating junction temperature range -55 to 175		5	°C

Table 2: Absolute maximum ratings

Notes:

 $^{(1)}\mbox{Pulse}$ width is limited by maximum junction temperature.

		Val	ue		
Symbol	Parameter	TO-247, TO-247 long leads, TO-3P	TO-3PF	Unit	
RthJC	Thermal resistance junction-case0.532.4		°C/W		
R _{thJA}	Thermal resistance junction-ambient	50		°C/W	

Table 3: Thermal data



2 Electrical characteristics

 T_C = 25 °C unless otherwise specified

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
Symbol	Falalletei	Test conditions		тур.		Unit
V _{(BR)CES}	Collector-emitter breakdown voltage	$V_{GE} = 0 V$, Ic = 2 mA	650			V
		$V_{GE} = 15 \text{ V}, \text{ Ic} = 40 \text{ A}$		1.6	2	
V _{CE(sat)}	V _{CE(sat)} Collector-emitter saturation voltage	$V_{GE} = 15 \text{ V}, I_C = 40 \text{ A},$ $T_J = 125 ^{\circ}\text{C}$		1.7		V
		V _{GE} = 15 V, I _C = 40 A, T _J = 175 °C		1.8		
V _{GE(th)}	Gate threshold voltage	$V_{CE} = V_{GE}$, $I_C = 1 \text{ mA}$	5	6	7	V
ICES	Collector cut-off current	$V_{GE} = 0 V, V_{CE} = 650 V$			25	μA
IGES	Gate-emitter leakage current	$V_{CE} = 0 \text{ V}, V_{GE} = \pm 20 \text{ V}$			±250	nA

Table 4: Static characteristics

Table 5: Dynamic characteristics

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
Cies	Input capacitance		-	5412	-	
Coes	Output capacitance	V _{CE} = 25 V, f = 1 MHz,	-	198	-	рF
Cres	Reverse transfer capacitance	V _{GE} = 0 V	-	107	-	P1
Qg	Total gate charge	Vcc = 520 V, Ic = 40 A,	-	210	-	
Q _{ge}	Gate-emitter charge	V _{GE} = 0 to 15 V (see <i>Figure 28: "Gate charge</i>	-	39	-	nC
Q _{gc}	Gate-collector charge	test circuit")	-	82	-	



Electrical characteristics

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
t _{d(on)}	Turn-on delay time		-	40	-	
tr	Current rise time		-	13	-	ns
(di/dt) _{on}	Turn-on current slope	V _{CE} = 400 V, I _C = 40 A,	-	2413	-	A/µs
t _{d(off)}	Turn-off delay time	$V_{GE} = 400 \text{ V}, \text{ IC} = 40 \text{ A},$ $V_{GE} = 15 \text{ V}, \text{ R}_{G} = 5 \Omega$	-	142	-	
t _f	Current fall time	(see Figure 27: "Test circuit	-	27	-	ns
Eon ⁽¹⁾	Turn-on switching energy	for inductive load switching")	-	498	-	
E _{off} ⁽²⁾	Turn-off switching energy		-	363	-	μJ
Ets	Total switching energy		-	861	-	
t _{d(on)}	Turn-on delay time		-	38	-	20
tr	Current rise time		-	14	-	ns
(di/dt) _{on}	Turn-on current slope	$V_{CE} = 400 \text{ V}, I_C = 40 \text{ A},$	-	2186	-	A/µs
t _{d(off)}	Turn-off delay time	$V_{GE} = 15 \text{ V}, \text{ R}_{G} = 5 \Omega,$	-	141	-	20
t _f	Current fall time	T _J = 175 °C (see <i>Figure 27: "Test circuit</i>	-	61	-	ns
Eon ⁽¹⁾	Turn-on switching energy	for inductive load switching")	-	1417	-	
E _{off} ⁽²⁾	Turn-off switching energy		-	764	-	μJ
Ets	Total switching energy		-	2181	-	


Table 6: Switching characteristics (inductive load)


Notes:


⁽¹⁾Including the reverse recovery of the external diode. The diode is the same of the co-packed STGW40H65DFB. ⁽²⁾Including the tail of the collector current.



2.1 Electrical characteristics (curves)










DocID025171 Rev 7

57


Electrical characteristics









57










8/21




Electrical characteristics








57











3 Test circuits








4 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: *www.st.com*. ECOPACK[®] is an ST trademark.

4.1 TO-3PF package information






Package information


Table 7: TO-3PF mechanical data				
Dim.		mm		
Dim.	Min.	Тур.	Max.	
А	5.30		5.70	
С	2.80		3.20	
D	3.10		3.50	
D1	1.80		2.20	
E	0.80		1.10	
F	0.65		0.95	
F2	1.80		2.20	
G	10.30		11.50	
G1		5.45		
Н	15.30		15.70	
L	9.80	10	10.20	
L2	22.80		23.20	
L3	26.30		26.70	
L4	43.20		44.40	
L5	4.30		4.70	
L6	24.30		24.70	
L7	14.60		15	
N	1.80		2.20	
R	3.80		4.20	
Dia	3.40		3.80	



4.2

TO-247 package information







STGFW40H65FB, STGW40H65FB, STGW40H05FB, STGW40H05FB, STGWA40H65FB, STGWT40H65FB Table 8: TO-247 package mechanical data

Package information

Table 8: TO-247 package mechanical data						
Dim.		mm				
Dini.	Min.	Тур.	Max.			
A	4.85		5.15			
A1	2.20		2.60			
b	1.0		1.40			
b1	2.0		2.40			
b2	3.0		3.40			
С	0.40		0.80			
D	19.85		20.15			
E	15.45		15.75			
е	5.30	5.45	5.60			
L	14.20		14.80			
L1	3.70		4.30			
L2		18.50				
ØP	3.55		3.65			
ØR	4.50		5.50			
S	5.30	5.50	5.70			



4.3

TO-247 long leads package information




Figure 32: TO-247 long leads package outline



STGFW40H65FB, STGW40H65FB, STGWA40H65FB, STGWT40H65FB Table 9: TO-247 long leads package mechanical data


Package information

Table 9: TO-247 long leads package mechanical data				
Dim.		mm		
Dim.	Min.	Тур.	Max.	
A	4.90	5.00	5.10	
A1	2.31	2.41	2.51	
A2	1.90	2.00	2.10	
b	1.16		1.26	
b2			3.25	
b3			2.25	
С	0.59		0.66	
D	20.90	21.00	21.10	
E	15.70	15.80	15.90	
E2	4.90	5.00	5.10	
E3	2.40	2.50	2.60	
е	5.34	5.44	5.54	
L	19.80	19.92	20.10	
L1			4.30	
Р	3.50	3.60	3.70	
Q	5.60		6.00	
S	6.05	6.15	6.25	



4.4 TO-3P package information

Figure 33: TO-3P package outline





Package information

Table 10: TO-3P package mechanical data				
Dim.		mm		
Dim.	Min.	Тур.	Max.	
A	4.60	4.80	5.00	
A1	1.45	1.50	1.65	
A2	1.20	1.40	1.60	
b	0.80	1.00	1.20	
b1	1.80	2.00	2.20	
b2	2.80	3.00	3.20	
С	0.55	0.60	0.75	
D	19.70	19.90	20.10	
D1	13.70	13.90	14.10	
E	15.40	15.60	15.80	
E1	13.40	13.60	13.80	
E2	9.40	9.60	9.90	
е	5.15	5.45	5.75	
L	19.80	20.00	20.20	
L1	3.30	3.50	3.70	
L2	18.20	18.40	18.60	
ØP	3.30	3.40	3.50	
ØP1	3.10	3.20	3.30	
Q	4.80	5.00	5.20	
Q1	3.60	3.80	4	



5 Revision history

Table 11: Document revision history

Date	Revision	Changes
30-Aug-2013	1	Initial release
11-Sep-2013	2	Document status changed from preliminary to production data. Inserted Section 2.1: Electrical characteristics (curves).
28-Feb-2014	3	Updated title and description in cover page.
05-Mar-2014	4	Updated units in Table 6: Switching characteristics (inductive load).
11-Apr-2014	5	Added part number and references for the device in a TO-3PF package.
		Added device in TO-247 long leads and updated the document accordingly.
03-Nov-2016	6	Updated Section 2.1: Electrical characteristics (curves) and Section 4.3: TO-247 long leads, package information.
		Minor text changes.
		Updated Table 1: "Device summary".
21-Mar-2017	7	Added Figure 26: "Thermal impedance for TO-3PF".
		Minor text changes



IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2017 STMicroelectronics - All rights reserved

