




PJM7002KNDC

N-Channel Enhancement Mode Power MOSFET

Features

- Fast switching
- Low gate charge and $R_{DS(ON)}$
- Low reverse transfer capacitances
- $V_{DS} = 60V, I_D = 0.3A$
 $R_{DS(on)} < 3\Omega @ V_{GS} = 10V$

DFN1x0.6-3L




Marking Code: K72

Applications

- Load switch
- PWM application

Schematic Diagram




Absolute Maximum Ratings

Ratings at 25°C ambient temperature unless otherwise specified.

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	60	V
Gate-Source Voltage	V_{GS}	± 20	V
Drain Current-Continuous	I_D	0.3	A
Drain Current-Pulsed ^{Note1}	I_{DM}	0.8	A
Maximum Power Dissipation	P_D	0.3	W
Junction Temperature	T_J	150	°C
Storage Temperature Range	T_{STG}	-55 to +150	°C

Thermal Characteristics

Thermal Resistance, Junction-to-Ambient ^{Note2}	$R_{\theta JA}$	357	°C/W
--	-----------------	-----	------



PJM7002KNDC

N-Channel Enhancement Mode Power MOSFET

Electrical Characteristics

(Ta=25°C unless otherwise specified)

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS}=0V, I_D=250\mu A$	60	--	--	V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=60V, V_{GS}=0V$	--	--	1	μA
Gate-Body Leakage Current	I_{GSS}	$V_{GS}=\pm 20V, V_{DS}=0V$	--	--	± 10	μA
Gate Threshold Voltage ^{Note3}	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=250\mu A$	1	1.4	2.5	V
Drain-Source On-Resistance ^{Note3}	$R_{DS(on)}$	$V_{GS}=10V, I_D=0.5A$	--	1.9	3	Ω
		$V_{GS}=4.5V, I_D=0.3A$	--	2.2	4	Ω
Forward Transconductance ^{Note3}	g_{FS}	$V_{DS}=10V, I_D=0.2A$	0.1	--	--	S
Dynamic Characteristics						
Input Capacitance	C_{iss}	$V_{DS}=25V, V_{GS}=0V, f=1MHz$	--	21	--	pF
Output Capacitance	C_{oss}		--	11	--	pF
Reverse Transfer Capacitance	C_{rss}		--	4.2	--	pF
Switching Characteristics						
Turn-on Delay Time	$t_{d(on)}$	$V_{DS}=30V, I_D=0.2A$ $V_{GEN}=10V, R_G=10\Omega$	--	10	--	nS
Turn-on Rise Time	t_r		--	50	--	nS
Turn-off Delay Time	$t_{d(off)}$		--	17	--	nS
Turn-off Fall Time	t_f		--	10	--	nS
Total Gate Charge	Q_g	$V_{DS}=10V, I_D=0.3A, V_{GS}=4.5V$	--	1.7	--	nC
Source-Drain Diode Characteristics						
Diode Forward Voltage ^{Note3}	V_{SD}	$V_{GS}=0V, I_S=0.2A$	--	--	1.2	V
Diode Forward Current ^{Note2}	I_S		--	--	0.3	A

Note: 1. Repetitive Rating: Pulse width limited by maximum junction temperature.

2. Surface Mounted on FR4 Board, $t \leq 10$ sec.







3. Pulse Test: Pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$.



PJM7002KNDC

N-Channel Enhancement Mode Power MOSFET




Typical Characteristic Curves





PJM7002KNDC

N-Channel Enhancement Mode Power MOSFET






PJM7002KNDC

N-Channel Enhancement Mode Power MOSFET

Package Outline

DFN1x0.6-3L-0009

Dimensions in mm



Ordering Information

Device	Package	Shipping
PJM7002KNDC	DFN1x0.6-3L	10,000PCS/Reel&7inches