



*DC COMPONENTS CO., LTD.*

RECTIFIER SPECIALISTS

**BZT52C2V4S  
THRU  
BZT52C51S**

**TECHNICAL SPECIFICATIONS OF SURFACE MOUNT ZENER DIODES**

**FEATURES**


- \* Planar Die construction
- \* Zener Voltages from 2.4V - 51V
- \* 200mW Power Dissipation
- \* Ideally Suited for Automated Assembly Processes

**MECHANICAL DATA**

- \* Case: Molded Plastic
- \* Terminals: Solder plated, solderable per MIL-STD-202, Method 208
- \* Polarity: See Diagram Below
- \* Mounting position: Any
- \* Weight: 0.008 gram Approx.



**SOD-323**



**MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS**

Ratings at 25°C ambient temperature unless otherwise specified.  
Single phase, half wave, 60 Hz, resistive or inductive load.  
For capacitive load, derate current by 20%.

Dimensions in inches(millimeters)

	SYMBOL	VALUE	UNITS
Zener Current see Table "Characteristics"			
Maximum Power Dissipation @TA=25°C	P <sub>tot</sub>	200	mW
Maximum Forward Voltage @IF=10mA	V <sub>F</sub>	0.9	Volts
Typical Thermal Resistance	R <sub>θJA</sub>	625	°C/W
Operating and Storage Temperature	T <sub>J</sub> ,T <sub>stg</sub>	-55 to +150	°C


NOTE: Normal Tolerance ±5%

# RATING AND CHARACTERISTIC CURVES (BZT52CXXS SERIES)


TYPE	Nominal Zener Voltage $V_Z @ I_{ZT}$		Zener Test Current $I_{ZT}$	Maximum Zener Impedance			Maximum Reverse Leakage Current	
				$Z_{ZT} @ I_{ZT}$	$Z_{ZK} @ I_{ZK}$	$I_{ZK}$	$I_R @ V_R$	
	Min	Max	mA	Ohms	Ohms	mA	$\mu A$	Volts
BZT52C2V4S	2.2	2.6	5	100	600	1	150	1.0
BZT52C2V7S	2.5	2.9	5	100	600	1	50	1.0
BZT52C3V0S	2.8	3.2	5	95	600	1	20	1.0
BZT52C3V3S	3.1	3.5	5	95	600	1	10	1.0
BZT52C3V6S	3.4	3.8	5	90	600	1	5.0	1.0
BZT52C3V9S	3.7	4.1	5	90	600	1	5.0	1.0
BZT52C4V3S	4.0	4.6	5	90	600	1	3.0	1.0
BZT52C4V7S	4.4	5.0	5	80	500	1	3.0	2.0
BZT52C5V1S	4.8	5.4	5	60	480	1	2.0	2.0
BZT52C5V6S	5.2	6.0	5	40	400	1	1.0	2.0
BZT52C6V2S	5.8	6.6	5	10	150	1	3.0	4.0
BZT52C6V8S	6.4	7.2	5	15	80	1	2.0	4.0
BZT52C7V5S	7.0	7.9	5	15	80	1	1.0	5.0
BZT52C8V2S	7.7	8.7	5	15	80	1	0.7	5.0
BZT52C9V1S	8.5	9.6	5	15	100	1	0.5	6.0
BZT52C10S	9.4	10.6	5	20	150	1	0.2	7.0
BZT52C11S	10.4	11.6	5	20	150	1	0.1	8.0
BZT52C12S	11.4	12.7	5	25	150	1	0.1	8.0
BZT52C13S	12.4	14.1	5	30	170	1	0.1	8.0
BZT52C15S	13.8	15.6	5	30	200	1	0.1	10.5
BZT52C16S	15.3	17.1	5	40	200	1	0.1	11.2
BZT52C18S	16.8	19.1	5	45	225	1	0.1	12.6
BZT52C20S	18.8	21.2	5	55	225	1	0.1	14.0
BZT52C22S	20.8	23.3	5	55	250	1	0.1	15.4
BZT52C24S	22.8	25.6	5	70	250	1	0.1	16.8
BZT52C27S	25.1	28.9	5	80	300	0.5	0.1	18.9
BZT52C30S	28.0	32.0	5	80	300	0.5	0.1	21.0
BZT52C33S	31.0	35.0	5	80	325	0.5	0.1	23.1
BZT52C36S	34.0	38.0	5	90	350	0.5	0.1	25.2
BZT52C39S	37.0	41.0	5	130	350	0.5	0.1	27.3
BZT52C43S	40.0	46.0	5	100	700	1	0.1	32.0
BZT52C47S	44.0	50.0	5	100	750	1	0.1	35.0
BZT52C51S	48.0	54.0	5	100	750	1	0.1	38.0

NOTE: Standard Zener Voltage Tolerance  $\pm 5\%$

changes in the power dissipation due to the ambient temperature.



## Breakdown characteristics BZT52-SERIES



## Disclaimer

Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold *DC COMPONENTS* harmless against all damages.

*DC COMPONENTS* disclaims any and all liability arising out of the application or use of any product, including consequential or incidental damages. Statement regarding the suitability of products for certain types of applications are based on *DC COMPONENTS*'s knowledge of typical requirements that are often placed on *DC COMPONENTS* products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application.

*DC COMPONENTS* reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein, and disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product. Parameters provided in datasheets and specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify *DC COMPONENTS*'s terms and conditions of purchase, including but not limited to the warranty expressed therein.

Unless otherwise in writing, *DC COMPONENTS* products are intended for use as general electronic components in standard applications ( eg: Consumer electronic, Computer equipment, Office equipment, etc.), and not recommended for use in a high specific application where a failure or malfunction of the device could result in human injury or death ( eg: Aerospace equipment, Submarine cables, Combustion equipment, Safety devices, Life support systems, etc.)

Customers using or selling *DC COMPONENTS* products not expressly indicated for use in such applications do so at their own risk. If customer intended to use *DC COMPONENTS* standard quality grade devices for applications not envisioned by *DC COMPONENTS*, please contact our sales representatives in advance.



*DC COMPONENTS CO., LTD.*