

Messrs. Specification No.: JEMCP0-010869A

Product Specification for Reference

Issued Date: 20 FEB. 2014

Part Description: Chip EMIFIL®Chip 3-terminal Capacitor for Large Current for General

Customer Part No.:

MURATA Part No.: NFM31PC Series

Technical Dept.

Product Engineering Department Capacitor Division I Fukui Murata MFG. Co., Ltd.

Prepared by

Yoshinori Sugihara

Representative

Yoshihiro Nakayama

[CONTENTS]

- 1.Scope
- 2.Part No. List
- 3.MURATA Part No. System
- 4.Type · Structure & Dimensions
- **5.Rated Value**
- 6.Packaging
- 7. Specifications
- 8.Package
- 9. A Caution & Notice



CHIP EMIFIL®CHIP 3-TERMINAL CAPACITOR FOR LARGE CURRENT FOR GENERAL

1.Scope

This product specification is applied to Chip EMIFIL®Chip 3-terminal Capacitor for Large Current NFM31PC Series used for General Electronic equipment.


2.Reference PART No. List

		Customer PART NO.	MURATA PART NO.
I	1		NFM31PC276B0J3L

3.MURATA Part NO. System

(Ex.)	NFM	31	PC	276	В	0J	3	L
		(1)L/W Dimensions	(2)Features	(3)Nominal Capacitance	(4)Characteristics	(5)DC Rated Voltage	(6)Electrode	(7)Packaging Code


4. Type & Dimensions



 MURATA PART NO.
 (1)-1 L
 (1)-2 W
 T
 e
 g
 i
 j

 1 NFM31PC276B0J3L
 3.2±0.2
 1.6±0.2
 1.3±0.2
 0.4±0.3
 0.3 min.
 1.1±0.3
 0.3±0.2

a)Equivalent Circuit



5.Rated value

	MURATA PART NO.	(3) Nominal Capacitance	•	(5) DC Rated Voltage	Rated Current (mA)	DC Resistance	Insulation Resistance	Operating Temp. Range/ Storage Temp. Range
1	NFM31PC276B0J3L	27 uF	±20 %	DC 6.3 V	6A(DC)	5mΩmax.	20MΩmin.	-40 to 85 °C / -40 to 85 °C

6.Package

	•			
_		MURATA PART NO.	(7) Packaging	Packaging Unit
	1 NI	FM31PC276B0J3L	□180mm Reel EMBOSSED	3000 pcs./Reel



SPECIFICATIONS AND TEST METHODS

Electrical Performance

No	Item	Specification	Test Method
1	Capacitance	Meet item 5.	Frequency: 120Hz
	(Cap.)		Voltage : 0.5± 0.1V(rms)
2	Insulation		Voltage : Rated Voltage
	Resistance(I.R.)		Time : 2 minutes max.
3	DC Resistance		Measured with 100mA max.
4	Withstanding Voltage	Products shall not be damaged.	Test Voltage : Rated Voltage x 300%
			Time: 1 to 5 s
			Charge Current : 50 mA max.
5	Operating Temperature	Shown in item 5.	Includes self-heating
6	Storage Temperature		

Standard Testing Condition

< Unless otherwise specified > $\,$ < In case of doubt > $\,$ Temperature : Ordinary Temp. / 15 °C to 35 °C $\,$ Temperature: 20 °C \pm 2 °C $\,$ Humidity: Ordinary Humidity / 25 %(RH) to 85 %(RH) $\,$ Humidity: 60 %(RH) to 70 %(RH)

Atmospheric pressure: 86 kPa to 106 kPa



SPECIFICATIONS AND TEST METHODS

Mechanical Performance

No	Item	Specification	Test Method	
1	Appearance and Dimensions	Meet item 4.	Visual Inspection and measured with Slide Calipers or Micrometer.	
2	Solderability	Electrodes shall be at least 90% covered with new solder coating.	Flux: Ethanol solution of rosin, 25(wt)% Pre-heat: 150 ± 10°C, 60 to 90s Solder: Sn-3.0Ag-0.5Cu Solder Temperature: 240 ± 3°C Immersion Time: 3 ± 1 s Immersion and emersion rates: 25mm / s	
3	Resistance to soldering heat	Meet Table 1. Table 1 Appearance No damaged Cap. Change Within ±7.5% I.R. Meet the initial rated value. DC Resistance 0.05 Ωmax.	Flux: Ethanol solution of rosin, 25(wt)% Pre-heat: 150±10°C, 60 to 90s Solder: Sn-3.0Ag-0.5Cu Solder Temperature: 270 ± 5°C Immersion Time: 10 ± 1 s Immersion and emersion rates: 25mm / s Initial values: measured after heat treatment (150+0 / -10 °C,1hour) and exposure in the room condition for 48±4 hours. Then measured after exposure in the room condition for 48±4 hours.	
4	Bending Strength	Meet Table 2. Table 2 Appearance No damaged Cap. Change Within ±7.5% DC Resistance 0.05 Ωmax.	It shall be soldered on the glass-epoxy substrate(100 x 40 x 1.0 mm). Deflection : 2 mm Keeping Time : 30 s Pressure jig R230 F Deflection (in mm)	
5	Drop	Products shall be no failure after tested.	It shall be dropped on concrete or steel board. Method: Free fall Height: 1m Attitude from which the product is dropped: 3 directions The Number of Time: 3 times for each direction (Total 9 times)	
6	Bonding Strength	The electrodes shall be no failure after tested.	It shall be soldered on the glass-epoxy substrate. Applying Force (F): 9.8 N Applying Time: 30 s 1.0 1.6 (in mm)	
7	Vibration	Meet Table 3. Table 3 Appearance No damaged Capacitance Meet the initial rated value. DC Resistance 0.05 Ωmax.	It shall be soldered on the glass-epoxy substrate. Oscillation Frequency: 10 to 55 to 10Hz for 1 minute Double Amplitude: 1.5 mm Time: A period of 2 hours in each of 3 mutually perpendicular directions. (Total 6 hours) Preconditioning: Heat treatment (150+0 / -10 °C, 1hour)	




SPECIFICATIONS AND TEST METHODS

Environment Performance

It shall be soldered on the glass-epoxy substrate.

No	Item	Specification	Test Method		
1	Temperature Cycling	Meet Table 1.	1 Cycle 1 step: Minimum Operating Temperature +0 / -3 °C / 30 +3 / -0 min 2 step: Room Temperature / within 3 min 3 step: Maximum Operating Temperature +3 /-0 °C / 30 +3 / -0 min 4 step: Room Temperature / within 3 min Total of 10 cycles Then measured after exposure in the room confition for 48±4hours. Initial values: measured after heat treatment (150+0 / -10 °C,1hour) and exposure in the room condition for 48±4 hours. If it's doubt, the measuring has to be done after 1 hours curing at 150+0 / -10°C and 48±4 hours storage.		
2	Humidity	Meet Table 4. Table 4 Appearance No damaged Cap. Change Within ±12.5% I.R. 50Ω F min. DC Resistance 0.05 Ωmax.	Temperature: 40 ± 2 °C Humidity: 90 to 95%(RH) Time: 500+24 / -0 hours Then measured after exposure in the room condition for 48±4 hours Initial values: measured after heat treatment (150+0 / -10 °C,1hour) and exposure in the room condition for 48±4 hours. If it's doubt, the measuring has to be done after 1 hours curing at 150+0 / -10°C and 48±4 hours storage.		
5	Heat Life		Temperature: Maximum Operating Temperature±2°C Test Voltage:Rated Voltage×150% Charge Current: 50 mA max. Time: 1000+48 / -0 hours Then measured after exposure in the room condition for 48±4 hours. Initial values: measured after voltage treatment (Maximum Operating Temperature±3°C, Rated Voltage×150%, 1hour) and exposure in the room condition 48±4 hours. If it's doubt, the mesuring has to be done after 1 hours curing at 150+0 / -10°C and 48±4 hours storage.		

1. Appearance and Dimensions (8mm-wide plastic tape)



2. Specification of Taping

- (1) Packing quantity (standard quantity)
 - 3000 pcs. / reel
- (2) Packing Method

Products shall be packaged in the cavity of plastic tape and sealed cover tape.

- (3) Sprocket Hole
 - The sprocket holes are to the right as the tape is pulled toward the user.
- (4)Cover tape

Cover tape has no spliced point.

(5) Missing components number


Missing components number within 0.1% of the number per reel or 1 pc., whichever is greater, and are not continuous. The specified quantity per reel is kept.

3. Pull Strength of Plastic Tape and Cover Tape

Plastic Tape	5N min.
Cover Tape	10N min.


4. Peeling off force of cover tape

0.2N to 0.7N (minimum value is typical) Speed of Peeling off : 300 mm / min



5. Dimensions of Leader-tape, Trailer and Reel

There shall be leader-tape (cover tape only and empty tape) and trailer-tape (empty tape) as follows.





∧Caution

1. Mounting density

Add special attention to radiating heat of products when mounting this product near the products with heating. The excessive heat by other products may cause deterioration of insulation resistance and excessive heat at this product, resulting in a fire.

2. Limitation of Applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property.

- (1)Aircraft equipment (2)Aerospace equipment (3)Undersea equipment (4)Power plant control equipment
- (5)Medical equipment (6)Transportation equipment(automobiles, trains, ships, etc.) (7)Traffic signal equipment
- (8)Disaster prevention / crime prevention equipment (9)Data-processing equipment
- (10)Applications of similar complexity or with reliability requirements comparable to the applications listed in the above

Notice

This product is designed for solder mounting.

Please consult us in advance for applying other mounting method such as conductive adhesive.

1. Flux and Solder

~.				
	Flux	Use rosin-based flux, Do not use highly acidic flux (with chlorine content exceeding 0.2(wt)%)		
		Do not use water-soluble flux.		
		Other flux (except above) Please contact us for details, then use.		
	Solder	Use Sn-3.0Ag-0.5Cu solder		
		Use of Sn-Zn based solder will deteriorate performance of products.		
		In case of using Sn-Zn based solder, please contact Murata in advance.		

2. Note for Assembling


< Thermal Shock >

Pre-heating should be in such a way that the temperature difference between solder and products surface is limited to 100°C max. Also cooling into solvent after soldering should be in such a way that the temperature difference is limited to 100°C max.

3. Attention Regarding P.C.B. Bending


The following shall be considered when designing P.C.B.'s and laying out products.

(1) P.C.B. shall be designed so that products are not subject to the mechanical stress for board warpage.



Products shall be located in the sideways direction (Length:a
b) to the mechanical stress.

(2) Products location on P.C.B. near seam for separation.



Products (A,B,C,D) shall be located carefully so that products are not subject to the mechanical stress due to warping the board. Because they may be subjected the mechanical stress in order of A>C>B \rightleftharpoons D.

4. Standard Soldering Conditions


4.1. Pre-heating Temperature

Soldering shall be handled so that the difference between pre-heating temperature and solder temperature shall be limited to 100°C max. to avoid the heat stress for the products.

4.2. Reflow Soldering

- 1) Soldering paste printing for reflow
- Standard thickness of solder paste: 100µm to 150µm.
- Use the solder paste printing pattern of the right pattern.
- For the resist and copper foil pattern, use standard land dimensions.

• Standard printing pattern of solder paste.




(in mm)

2) Soldering Conditions

Standard soldering profile and the limit soldering profile is as follows.

The excessive limit soldering conditions may cause leaching of the electrode and/or resulting in the deterioration of product quality. _____1



	Standard Profile	Limit Profile	
Pre-heating	150°C ~ 180°C , 90s ± 30s		
Heating	above 220°C , 30s ~ 60s	above 230°C , 60s max.	
Peak temperature	245°C ± 3°C	260°C , 10s	
Cycle of reflow	2 times	2 times	


Notice

5. Flow Soldering

Printing of Adhesive

Adhesive amount shall be about 0.06mg per chip to obtain enough adhesive strength.

The adhesive position is as follows.




6. Soldering Conditions

Standard soldering profile and the limit soldering profile is as follows.

The excessive limit soldering conditions may cause leaching of the electrode and/or resulting in the deterioration of product





	Standard Profile	Limit Profile	
Pre-heating	150°C, 60s min.		
Heating	250°C, 4s ~ 6s	265°C ± 3°C, 5s max.	
Cycle of reflow	2 times	2 times	

7. Reworking with Soldering iron

The following conditions shall be strictly followed when using a soldering iron.


• Pre-heating : 150°C, 1 minute • Soldering iron output : 30W max.

•Tip temperature : 350° C max. •Soldering time : 3(+1,-0) s •Tip diameter : ϕ 3mm max. •Tip diameter : ϕ 3mm max.

Note: Do not directly touch the products with the tip of the soldering iron in order to prevent the crack on the ceramic material due to the thermal shock.

8. Solder Volume

Solder shall be used not to be exceeded as shown below.



Accordingly increasing the solder volume, the mechanical stress to product is also increased.

Excessive solder volume may cause the failure of mechanical or electrical performance.

9. Cleaning Conditions

Products shall be cleaned on the following conditions.

- (1) Cleaning temperature shall be limited to 60°C max. (40°C max. for Isopropyl alcohol (IPA))
- (2) Ultrasonic cleaning shall comply with the following conditions, with avoiding the resonance phenomenon at the mounted products and P.C.B.

Power : 20W / I max.
Frequency : 28kHz to 40kHz
Time : 5 minutes max.

(3) Cleaner 1. Cleaner

Isopropyl alcohol (IPA)

2. Aqueous agent

PINE ALPHA ST-100S

(4) There shall be no residual flux and residual cleaner after cleaning.

In the case of using aqueous agent, products shall be dried completely after rinse with de-ionized water in order to remove the cleaner.

(5) Other cleaning

Please contact us.

10. Operating Environment

Do not use this product under the following environmental conditions, on deterioration of the performance, such as insulation resistance may result from the use.

- (1) in the corrodible atmosphere (acidic gases, alkaline gases, chlorine, sulfur gases, organic gases and etc.)
- (2) in the atmosphere where liquid such as organic solvent, may splash on the products.

Notice


11. Resin coating

The capacitance value may change and/or it may affect on the product's performance due to high cure-stress of resin to be used for coating / molding products. So please pay your careful attention when you select resin. In prior to use, please make the reliability evaluation with the product mounted in your application set.


12. Handling of a substrate

After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting to the substrate when cropping the substrate, inserting and removing a connector from the substrate or tightening screw to the substrate. Excessive mechanical stress may cause cracking in the product.

Bending




Twisting



13. Standard Land Dimensions

The chip EMI filter suppresses noise by conducting the high-frequency noise element to ground. Therefore, to get enough noise reduction, feed through holes which is connected to ground-plane should be arranged according to the figure to reinforce the ground-pattern.

- < Standard land dimensions for reflow >
- ·Side on which chips are mounted
- < Standard land dimensions for flow >
 - ·Side on which chips are mounted



(in mm)

14. Storage condition

(1) Storage period

Use the products within 12 months after delivered.

Solderability should be checked if this period is exceeded.

- (2) Storage environment condition
- Products should be stored in the warehouse on the following conditions.

Temperature: -10 to +40°C

Humidity: 15 to 85% relative humidity

No rapid change on temperature and humidity

- •Don't keep products in corrosive gases such as sulfur, chlorine gas or acid, or it may cause oxidization of electrode, resulting in poor solderability.
- Products should be stored on the palette for the prevention of the influence from humidity, dust and so on.
- Products should be stored in the warehouse without heat shock, vibration, direct sunlight and so on.
- Products should be stored under the airtight packaged condition.
- (3) Delivery

Care should be taken when transporting or handling product to avoid excessive vibration or mechanical shock.



- (1) Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.
- (2) You are requested not to use our product deviating from the agreed specifications.(3) We consider it not appropriate to include any terms and conditions with regard to the business transaction in the product specifications, drawings or other technical documents. Therefore, if your technical documents as above include such terms and conditions such as warranty clause, product liability clause, or intellectual property infringement liability clause, they will be deemed to be invalid.