

Features

- Lead Free Finish/RoHS Compliant(Note 1) ("P" Suffix Designates RoHS Compliant. See Ordering Information)
- Epoxy Meets UL 94 V-0 Flammability Rating
- Moisture Sensitivity Level 1
- Halogen Free Available Upon Request By Adding Suffix "-HF"

1 Amp Super Fast Recovery Rectifier 50 to 600 Volts

Maximum Ratings

- Operating Junction Temperature Range: -65°C to +175°C
- Storage Temperature Range: -65°C to +175°C
- Maximum Thermal Resistance: 35°C/W Junction to Lead
- Maximum Thermal Resistance: 85°C/W Junction to Ambient


MCC Part Number	Device Marking	Maximum Recurrent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
ES1A-L	ES1A	50V	35V	50V
ES1B-L	ES1B	100V	70V	100V
ES1D-L	ES1D	200V	140V	200V
ES1G-L	ES1G	400V	280V	400V
ES1J-L	ES1J	600V	420V	600V

Electrical Characteristics @ 25°C Unless Otherwise Specified

Average Forward Current	I _{F(AV)}	1.0A	T _L =125°C
Peak Forward Surge Current	I _{FSM}	30A	8.3ms,Half Sine
Maximum Instantaneous Forward Voltage ES1A-L-ES1D-L ES1G-L ES1J-L	V _F	0.95V 1.25V 1.70V	I _{FM} =1.0A;
Maximum DC Reverse Current At Rated DC Blocking Voltage	I _R	1.0μA 80μA	T _A =25°C; T _A =100°C
Maximum Reverse Recovery Time	T _{RR}	35ns	I _F =0.5A; I _R =1.0A; Irr=0.25A
Typical Junction Capacitance	CJ	15pF	Measured at 1.0MHz V _R =4.0V


Note: 1. High Temperature Solder Exemption Applied, see EU Directive Annex Notes 7a.

SMA (DO-214AC)



DIMENSIONS						
DIM	INCHES		MM		NOTE	
	MIN	MAX	MIN	MAX	NOTE	
Α	0.079	0.096	2.00	2.44		
В	0.050	0.064	1.27	1.63		
С	0.002	0.008	0.051	0.203		
D		0.020		0.51		
Е	0.030	0.060	0.76	1.52		
F	0.065	0.091	1.65	2.32		
G	0.189	0.220	4.80	5.59		
Н	0.157	0.181	4.00	4.60		
J	0.090	0.115	2.25	2.92		

SUGGESTED SOLDER PAD LAYOUT





Curve Characteristics




Fig. 3 - Typical Instantaneous Forward Characteristics 50 20 Instantaneous Forward Current (A) 10 ES1A-L-ES1D-I 2 ES1G-L 0.2 0.05 T_J=25°C 0.02 0.01 0.5 1.5 2.0 2.5 3.0

Instantaneous Forward Voltage (V)





Fig. 4 - Typical Reverse Leakage Characteristics





Ordering Information

Device	Packing	
ES1A-LTP~ES1J-LTP	Tape&Reel: 5Kpcs/Reel	

Note: Adding "-HF" Suffix For Halogen Free, eg. ES1A-LTP- HF~ES1J-LTP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp**. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp**, and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.