

5326 B




Models Versions

5326 B	black w/foam
5326 BE	black empty
5326 G	mil. green w/foam
5326 GE	mil. green empty
5326 O	orange w/foam
5326 OE	orange empty

- Made of Copolymer Polypropylene compound
- Waterproof, resistant to chemicals, humidity, dust
- Resistant to harsh temperatures (-33°C / +90°C)
- Jam-free purge valve and latches
- Recommended for professional applications

- 100% made in Italy: Italian design and proven functionality
- First to achieve the new military standard qualifications
- Recognized as the most versatile case to customize
- Widest choice of accessories to customize your experience
- Incorporate a number of patented innovations

Technical Features		L	W	D		
		Length	Width	Depth	Lid	Base
Internal dim.	mm	538	405	250	60	190
External dim.	mm	627	475	292		
Weight empty		Kg 10,00				
Weight w/foam		Kg 11,25				
Weight w/multi		Kg ---				
Volume		lt 53				
Buoyancy		Kg/max 37,20				
Temp. rating		°C min -33 max +90				
Certifications						
2002/95/EC Conformity with the Directive 2002/95/EC						
DEF STAN 81-41 (level J)						
IP67 Dustproof - Waterproof						
STANAG 4280 (edition 2)						



Accessories 5326 B



KIT.EXPL.PLUGS



LIDFOAM.53



KIN.0481 - SILICA BOX



FOAM.5325



PANEXPL53



KIT SUPP.EXPL.



BAG-V



DIV-V



EXPL COMBILOCK



EXPL PADLOCK



KIT SUPP.PLAST.



EXPL TSA.DIGILOCK