




## Steatite Ceramic Terminal Blocks

Approved industrial high temperature terminal blocks in 1, 2, 3 and 4 pole options.



Specifications:-					Features:-							
<b>Inserts</b>	Nickel-plated brass (galvanised)				Steatite is an alternative to Porcelain Ceramic and has many advantages such as:- Higher density, better bending/compression strength and elasticity, higher dielectric strength, non-flammable and temperature-resistant with dimensional stability up to 1000 °C							
<b>Screw</b>	Zinc-plated steel (galvanised), blue passivated											
<b>Housing</b>	Steatite C 220, IEC 672-1, unglazed											
<b>Temp C</b>	Continuous use temperature max. 350 °C											
					Dimensions (mm)					$\phi_1$		$\phi_2$
Part No.	Rated Cross Section	A (max)	V (Max)	Poles	W	L	H	d	D	Conductor size mm <sup>2</sup> Nominal/Max		Fixing hole
DESTB-0251	4.0 mm <sup>2</sup>	32	450	1	10	18	15	n/a	8	1.5-4.0	6.0	n/a
DESTB-0252	4.0 mm <sup>2</sup>	32	450	2	18	21	15	8	11	1.5-4.0	6.0	M3
DESTB-0253	4.0 mm <sup>2</sup>	32	450	3	18	32	15	8	11	1.5-4.0	6.0	M3
DESTB-0254	4.0 mm <sup>2</sup>	32	450	4	18	43	15	8	11	1.5-4.0	6.0	M3
DESTB-0401	6.0 mm <sup>2</sup>	41	750	1	11	22	21	n/a	11	1.5-6.0	10.0	n/a
DESTB-0402	6.0 mm <sup>2</sup>	41	750	2	22	24	21	10	14	1.5-6.0	10.0	M3.5
DESTB-0403	6.0 mm <sup>2</sup>	41	750	3	22	38	21	10	14	1.5-6.0	10.0	M3.5
DESTB-0404	6.0 mm <sup>2</sup>	41	750	4	22	52	21	10	14	1.5-6.0	10.0	M3.5
DESTB-0102	10.0 mm <sup>2</sup>	57	750	2	30	34	23	13	19	2.5-10.0	16.0	M4
DESTB-0103	10.0 mm <sup>2</sup>	57	750	3	30	52	23	13	19	2.5-10.0	16.0	M4

### MAKING THE RIGHT CONNECTIONS

T: +44 (0)1933 234400 ■ F: +44 (0)1933 234411  
E: sales@hylec-apl.com ■ W: www.hylec-apl.com