


2N7002KL

60V N-Channel Mosfet

FEATURES

- $R_{DS(ON)} \leq 1.6 \Omega @ V_{GS}=10V$
- $R_{DS(ON)} \leq 2.5 \Omega @ V_{GS}=4.5V$


SOT-23




APPLICATIONS

- Portable appliances

MARKING



N-CHANNEL MOSFET



72K : Device Code

MAXIMUM RATINGS (Ta=25°C unless otherwise noted)

Symbol	Parameter	Max.	Units
V _{DSS}	Drain-Source Voltage	60	V
V _{GSS}	Gate-Source Voltage	±20	V
I _D	Continuous Drain Current	0.5	A
I _{DM}	Pulsed Drain Current ^{note1}	2.0	A
P _D	Power Dissipation	0.83	W
R _{θJA}	Thermal Resistance, Junction to Ambient	150	°C/W
T _J	Junction Temperature	150	°C
T _{TSG}	Storage Temperature Range	-55 to +150	°C







**2N7002KL****MOSFET ELECTRICAL CHARACTERISTICS Ta=25 °C unless otherwise specified**

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Units
Off Characteristics						
V _{(BR)DSS}	Drain-Source Breakdown Voltage	V _{GS} = 0V, I _D = 250μA	60	-	-	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 48V, V _{GS} = 0V, T _J = 25°C	-	-	1	μA
I _{GSS}	Gate to Body Leakage Current	V _{GS} = ±20V, V _{DS} = 0V	-	-	±10	uA
On Characteristics						
V _{G(th)}	Gate Threshold Voltage	V _{DS} = V _{GS} , I _D = 250μA	0.5	-	1.5	V
R _{D(on)}	Static Drain-Source On-Resistance ^{note2}	V _{GS} = 10V, I _D = 0.5A	-	-	1.6	Ω
		V _{GS} = 4.5V, I _D = 0.1A	-	-	2.5	Ω
Dynamic Characteristics ^{note3}						
R _G	Gate Resistance	V _{GS} = V _{DS} = 0 V f = 1 MHz	-	100	-	Ω
C _{iss}	Input Capacitance	V _{DS} = 25V, V _{GS} = 0V, f = 1.0MHz	-	22.8	-	pF
C _{oss}	Output Capacitance		-	3.5	-	pF
C _{rss}	Reverse Transfer Capacitance		-	2.9	-	pF
Q _g	Total Gate Charge	V _{DS} = 10V, I _D = 0.5A, V _{GS} = 4.5V	-	280	-	pC
Q _{gs}	Gate-Source Charge		-	82	-	pC
Q _{gd}	Gate-Drain("Miller") Charge		-	201	-	pC
Switching Characteristics ^{note3}						
t _{d(on)}	Turn-On Delay Time	V _{GS} = 10V, V _{DS} = 30V, R _G = 25Ω, I _D = 0.5A R _L = 60Ω	-	3.8	-	ns
t _r	Turn-On Rise Time		-	3.4	-	ns
t _{d(off)}	Turn-Off Delay Time		-	19	-	ns
t _f	Turn-Off Fall Time		-	12	-	ns
Drain-Source Diode Characteristics and Maximum Ratings						
I _S	Maximum Continuous Drain to Source Diode Forward Current		-	-	0.5	A
V _{SD}	Drain to Source Diode Forward Voltage	V _{GS} = 0V, I _{SD} = 0.5A, T _J = 25°C	-	-	1.3	V
t _{rr}	Reverse Recovery Time	V _{GS} = 0V, I _S = 0.5A, di/dt = 100A/μs	-	42	-	ns
Q _{rr}	Reverse Recovery Charge		-	41	-	nC

Notes: 1. Repetitive Rating: Pulse width limited by maximum junction temperature







2. Pulse Test: Pulse width ≤ 300μs, Duty Cycle ≤ 2%

3. Guaranteed by design, not subject to production testing

TYPICAL PERFORMANCE CHARACTERISTICS






2N7002KL


TYPICAL PERFORMANCE CHARACTERISTICS (cont.)



2N7002KL

TYPICAL PERFORMANCE CHARACTERISTICS (cont.)



2N7002KL**SOT-23 PACKAGE OUTLINE DRAWING**

Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.950 TYP		0.037 TYP	
e1	1.800	2.000	0.071	0.079
L	0.550 REF		0.022 REF	
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	8°