

Drg No :- C 44599

SPECIFICATION

ACTUATING FORCE: -0.9N(3.2ozf)MAX

RELEASE FORCE : -0.07N(0.25ozf)MIN

FREE POSITION :- 13.2 (0.52) MAX

OPERATING POSITION :- ± 1.2
10.6 (0.42)

MOVEMENT DIFFERENTIAL :- 0.4(0.016)MAX

OVERTRAVEL (AVAILABLE) :- DEPRESS TO CASE

SPECIAL FEATURE :- TESTED AND STAMPED TO UL AND CSA REQUIREMENTS

APPROVAL RATING :- 3 AMP - 125 OR 250V.AC.

INSTALLATION DRAWING





DIAGRAM OF CONNECTIONS



1	FIRST ISSUE	15/08/02
ISSUE	REVISION	DATE

saia-burgess

Smart solutions for comfort and safety
 Saia-Burgess Gateshead Limited
 Dukesway, Team Valley Trading Estate
 Gateshead, Tyne & Wear NE11 0UB
 Tel: +44 (0) 191 401 6100
 Fax: +44 (0) 191 401 6322
 www.saia-burgess.co.uk



THIRD ANGLE PROJECTION
 DO NOT SCALE!
 THIS DRAWING MUST ONLY BE AMENDED ON A CAD SYSTEM
 ALL DIMENSIONS SPECIFIED IN MILLIMETRES

TOLERANCES UNLESS STATED:-
 NO DECIMAL PLACE ± 0.50
 1 DECIMAL PLACES ± 0.25
 2 DECIMAL PLACES ± 0.15
 ANGULAR $\pm 1^\circ$
 INCH - OUNCE UNITS [IN BRACKETS]

APPROVED

DRAWN	T.BELL.	CHECKED BY	<i>[Signature]</i>
DATE	15/08/02	ENGINEERING	<i>[Signature]</i>
SCALE	4/1	QUALITY ASSURANCE	<i>[Signature]</i>

TITLE / DESCRIPTION
V4NSY1 UL

Drg No :- C 44599

A3