

Inverter for motor control

# 600V IGBT Intelligent Power Module (IPM) for low speed switching drive

BM63564S-VA BM63564S-VC

## **General Description**

BM63564S-VA/-VC is an Intelligent Power Module composed of gate drivers, bootstrap diodes, IGBTs, fly wheel diodes. Low saturation voltage IGBTs optimized for low speed switching drive (to 6kHz) such as a compressor is adopted. Please examine high speed switching series for high speed switching drive.

#### Features

- 3phase DC/AC Inverter
- 600V/15A
- Low Side IGBT Open Emitter
- Built -in Bootstrap Diode
- High Side IGBT Gate Driver(HVIC): SOI (Silicon On Insulator) Process, Drive Circuit, High Voltage Level Shifting, Current Limit for Bootstrap Diode, Control Supply Under-Voltage Locked Out (UVLO)
- Low Side IGBT Gate Driver(LVIC): Drive Circuit, Short Circuit Current Protection (SCP), Control Supply Under Voltage Locked Out (UVLO), Temperature Output by Analog Signal (VOT)
- Fault Signal(LVIC) Corresponding to SCP (Low Side IGBT), UVLO Fault
- Input Interface 3.3V, 5V Line
- UL Recognized: File E468261

## Application

- Low Speed Switching Drive of AC100 to 240Vrms(DC Voltage: Less Than 400V) Class Motor
- Low Speed Switching Drive of Compressor Motor for Air Conditioner, Washing Machine, Refrigerator

## **Typical Application Circuit**


#### **Key Specifications**

- IGBT Collector-Emitter Voltage V<sub>CESAT</sub>: 1.5V(Typ)
  - FWD Forward Voltage V<sub>F</sub>: 1.5V(Typ)
- FWD Reverse Recovery Time trr: 100ns(Typ)
- Module Case Temperature T<sub>C</sub>: -25 to +100°C
- 150°C
- Junction Temperature T<sub>jmax</sub>:

## Package

HSDIP25 HSDIP25VC

W(Typ) x D(Typ) x H(Typ) 38.0mm x 24.0mm x 3.5mm 38.0mm x 24.0mm x 3.5mm






Figure 1. Example of Application Circuit

OProduct structure: Semiconductor IC OThis product is not designed for protection against radioactive rays

## **Pin Configuration**




Figure 2. Pin Configuration and Tc Detecting Point

Pin	Des	crip	tion

Pin No.	Pin Name	Function	Pin No.	Pin Name	Function
1	NC	No connection(GND potential)	14	FO	Alarm output
2	VBU	U phase floating control supply	15	CIN	Detecting of short circuit current trip voltage
3	VBV	V phase floating control supply	16	GND	Ground (Note 1)
4	VBW	W phase floating control supply	17	VOT	Temperature output
5	HINU	U phase high side IGBT control	18	NW	W phase low side IGBT emitter
6	HINV	V phase high side IGBT control	19	NV	V phase low side IGBT emitter
7	HINW	W phase high side IGBT control	20	NU	U phase low side IGBT emitter
8	HVCC	Control supply for HVIC	21	W	W phase output
9	GND	Ground (Note 1)	22	V	V phase output
10	LINU	U phase low side IGBT control	23	U	U phase output
11	LINV	V phase low side IGBT control	24	Р	Inverter supply
12	LINW	W phase low side IGBT control	25	NC	No connection (Note 2)
13	LVCC	Control supply for LVIC			

(Note 1) Two GND pins (9 & 16pin) are connected inside IPM, please connect one pin (16pin is recommended) to the 15V power supply GND outside and leave the other open.

(Note 2) NC pin (25pin) is not electrically connected to any other potential inside.

#### **Block Diagram**




Figure 3. Block Diagram

## **Description of Block**

- 1) High Side IGBT Drive (HVIC, Bootstrap Diode)
  - High voltage level shifting circuit drives high side IGBT.

Built-in bootstrap diode and current limit function for bootstrap diode enable HVIC to drive high side IGBT without external component (bootstrap diode, resistor). There is under-voltage-locked-out (UVLO) function for floating control power supply.

2) Low Side IGBT Drive (LVIC)

LVIC drives low side IGBT.

There is short circuit current protection (SCP), under-voltage locked out (UVLO) for control power supply LVCC function. Alarm signal (FO) will output when these protection circuits work. LVIC detects temperature of itself, transform temperature into analog voltage, and output voltage to VOT pin.

## Absolute Maximum Ratings (Unless otherwise specified, Tj=25°C)

In	ver	ter	Part	

Item		Symbol	Ratings	Unit	Conditions
Supply Voltage		VP	450	V	Applied between P-NU,NV,NW
Supply Voltage(Su	ırge)	VP(surge)	500	V	Applied between P-NU,NV,NW
Collector-Emitter \	/oltage	Vces	600	V	
Collector Current	DC	lc	±15 (Note 1)	А	Tc=25°C
Collector Current	PEAK	ICP	±45 (Note 1)	А	Tc=25°C, less than 1ms
Collector Power D	issipation	Pc	41	W	T <sub>C</sub> =25°C, per 1 chip
Junction Temperat	ure	T <sub>jmax</sub>	150	°C	
(Nata 4) Da wat haven	15.40	2			

(Note 1) Do not, however exceed  $P_C$ , ASO.

#### Control part

Item	Symbol	Ratings	Unit	Conditions	
Control Power Supply	Vcc	20	V	Applied between HVCC-GND, LVCC-GND	
Floating Control Power Supply	V <sub>BS</sub>	20	V	Applied between VBU-U, VBV-V, VBW-W	
Control Input Voltage	V <sub>IN</sub>	-0.5 to V <sub>CC</sub> +0.5	V	Applied between HINX, LINX-GND (X=U,V,W)	
Fault Output Supply Voltage	VFO	-0.5 to V <sub>cc</sub> +0.5	V	Applied between FO-GND	
Fault Output Current	I <sub>FO</sub>	1	mA	Sink current at FO pin	
Current Sensing Input Voltage	Vcin	-0.5 to +7.0	V	Applied between CIN-GND	
Temperature Output Voltage	Vот	-0.5 to +7.0	V	Applied between VOT-GND	

#### Bootstrap diode part

Item	Symbol	Ratings	Unit	Conditions
Reverse Voltage	Vrb	600	V	
Junction Temperature	T <sub>jmaxD</sub>	150	°C	

#### **Total system**

Item	Symbol	Ratings	Unit	Conditions
Self Protection Supply Voltage (SCP Capability)	VP(PROT)	400	V	V <sub>CC</sub> =13.5 to 16.5V, Inverter part T <sub>j</sub> =125°C, non-repetitive, less than 2µs
Module Case Temperature	Tc	-25 to +100	°C	Measurement point of T <sub>C</sub> is provided in Figure 2
Storage Temperature	T <sub>stg</sub>	-40 to +125	°C	
Isolation Voltage	V <sub>iso</sub>	1500	V <sub>rms</sub>	Sinusoidal, 60Hz, AC 1minute, between connected all pins and heat sink plate

#### Thermal resistance

Item	Symbol	Limit		Unit	Conditions	
	Symbol	Min	Тур	Max	Unit	Conditions
Junction to Case Thermal Resistance (Note 2)	Rth(j-c)_IGBT	-	-	3.0	°C /W	Inverter IGBT(1/6 module)
	Rth(j-c)_FWD	-	-	3.9	°C /W	Inverter FWD(1/6 module)

(Note 2) Grease with good conductivity and high reliability should be applied evenly with +100 to +200µm on the contacting surface of IPM and heat sink. Use a torque wrench to fasten up to the specified torque rating. The contacting thermal resistance between IPM case and heat sink is determined by the thickness and the thermal conductivity of the applied grease.

Caution: Operating the IPM over the absolute maximum ratings may damage the IPM. The damage can either be a short circuit between pins or an open circuit between pins and the internal circuitry. Therefore, it is important to consider circuit protection measures, such as adding a fuse, in case the IPM is operated over the absolute maximum ratings.

## **Recommended Operating Conditions**

ltem	Limit				Unit	Conditions
Item	Symbol	Min	Тур	Max	Unit	Conditions
Supply Voltage	VP	0	300	400	V	Applied between P-NU,NV,NW
Control Power Supply	V <sub>cc</sub>	13.5	15.0	16.5	V	Applied between HVCC-GND, LVCC-GND
Floating Control Power Supply	$V_{BS}$	13.0	15.0	18.5	V	Applied between VBU-U, VBV-V, VBW-W
Control Power Supply Variation	⊿Vcc ⊿Vвs	-1	-	+1	V/µs	
Control Input Voltage	Vin	0	-	5.5	V	
Current Sensing Input Voltage	V <sub>CIN</sub>	0	-	5.5	V	
Blanking Time for Preventing Arm-short	t <sub>dead</sub>	1.5	-	-	μs	For each input signal
PWM Input Frequency	fрwм	-	-	6	kHz	T <sub>C</sub> ≤ 100°C, T <sub>j</sub> ≤ 125°C
High Side IGBT	PWONH	0.8	-	-	μs	
Minimum Input Pulse Width <sup>(Note1)</sup>	PWoffh	0.8	-	-	μs	
Low Side IGBT	PWonl	2.5	-	-	μs	
Minimum Input Pulse Width <sup>(Note1)</sup>	PWOFFL	0.8	-	-	μs	
Voltage Variation Between GND- NU, NV, NW	VN	-5	-	+5	V	Between GND-NU, NV, NW (Including surge voltage)
Junction Temperature	Tj	-25	-	+125	°C	

(Note 1) IPM might not respond if the input signal pulse width is less than  $PW_{ON}$ ,  $PW_{OFF}$ .

#### Electrical Characteristics (Unless otherwise specified, Tj=25°C, V<sub>CC</sub>=V<sub>BS</sub>=15V, V<sub>P</sub>=300V) **Inverter Part**

ltem	Symbol		Limit		Unit	Conditions
item	Symbol	Min	Тур	Max	Unit	
Collector Emitter Seturation Voltage	Manada	-	1.50	1.90	V	Ic=15A
Collector-Emitter Saturation Voltage	Vcesat	-	0.85	1.15	V	Ic=1.5A
Collector-Emitter Cut-off Current	ICES	-	-	100	μA	V <sub>CE</sub> =V <sub>CES</sub>
FWD Forward Voltage	VF	-	1.50	2.00	V	I⊧=15A
FWD Reverse Recovery Time	t <sub>rr</sub>	-	100	-	ns	Inductive Load, Ic=15A
High Side IGBT Turn on Delay Time	t <sub>onH</sub>	0.50	0.90	1.40	μs	Inductive Load, Ic=15A
High Side IGBT Turn on Switching Time	t <sub>c(on)H</sub>	-	0.20	-	μs	Inductive Load, Ic=15A
High Side IGBT Turn off Delay Time	t <sub>offH</sub>	-	1.40	2.10	μs	Inductive Load, Ic=15A
High Side IGBT Turn off Switching Time	t <sub>c(off)</sub> H	-	0.45	-	μs	Inductive Load, Ic=15A
Low Side IGBT Turn on Delay Time	t <sub>onL</sub>	0.80	1.70	2.50	μs	Inductive Load, Ic=15A
Low Side IGBT Turn on Switching Time	t <sub>c(on)L</sub>	-	0.25	-	μs	Inductive Load, Ic=15A
Low Side IGBT Turn off Delay Time	t <sub>offL</sub>	-	1.00	1.50	μs	Inductive Load, I <sub>C</sub> =15A
Low Side IGBT Turn off Switching Time	t <sub>c(off)L</sub>	-	0.45	-	μs	Inductive Load, Ic=15A




Figure 4. Switching Time Definition

## **Control part**

ltere	Queshal		Limit		1.1	Conditions
Item	Symbol	Min	Тур	Max	Unit	
Whole	1 1					
VCC Circuit Current 1	Icc1	-	1.20	2.40	mA	VIN=0V
VCC Circuit Current 2	I <sub>CC2</sub>	-	1.40	2.80	mA	VIN=5V
VBS Circuit Current 1	I <sub>BS1</sub>	-	0.15	0.35	mA	VIN=0V
VBS Circuit Current 2	I <sub>BS2</sub>	-	0.15	0.35	mA	VIN=5V
Control Input(HINU,HINV,HINW	LINU,LINV,	,LINW)				
H Level Input Current	linh	0.7	1.0	1.5	mA	V <sub>IN</sub> =5V
L Level Input Current	linl	-10	-	-	μA	V <sub>IN</sub> =0V
H Level Input Threshold Voltage	VINH	-	-	2.6	V	
L Level Input Threshold Voltage	VINL	0.8	-	-	V	
Input Hysteresis Voltage	V <sub>HYS</sub>	-	0.25	-	V	
Short Circuit Current Protectio	n					
CIN Input Bias Current	ICIN	-2	-	-	μA	CIN=0V
Trip Voltage	Vsc	0.455	0.480	0.505	V	
Under Voltage Locked Out						
VCC Trip Voltage	Vccuvt	10.5	11.5	12.5	V	
VCC Release Voltage	V <sub>CCUVR</sub>	11	12	13	V	
VBS Trip Voltage	VBSUVT	10	11	12	V	
VBS Release Voltage	VBSUVR	10.5	11.5	12.5	V	
Temperature Output						
VOT Voltage <sup>(Note 1)</sup>	V	2.63	2.77	2.91	V	LVIC temperature = 90°C
vor vollage	V <sub>OT</sub>	0.88	1.13	1.39	V	LVIC temperature = 25°C
Fault Output(FO)	·					
Output low Voltage	V <sub>FO</sub>	-	-	0.95	V	I <sub>FO</sub> =1mA
Leak Current	IFOLEAK	-	-	10	μA	V <sub>FO</sub> =5V
Output Pulse Width	tFO	20	-	-	μs	

(Note 1) IPM does not shutdown IGBTs and output fault signal automatically when temperature rises excessively. When temperature exceeds the protective level that user defined, controller (MCU) should stop the IPM.

#### **Bootstrap Diode Part**


Item	Symbol		Limit		Unit	Conditions
item	Symbol	Min	Тур	Max	Offic	Conditions
Forward Voltage	V <sub>FB1</sub>	0.3	0.6	0.9	V	I <sub>FB</sub> =1mA Voltage drop between HVCC-VBX (X=U,V,W)
	Vfb2	1.1	2.0	2.9	V	I <sub>FB</sub> =100mA Voltage drop between HVCC-VBX (X=U,V,W)
Reverse Current	I <sub>RB</sub>	-	-	10	μA	V <sub>RB</sub> =600V
Reverse Recovery Time	t <sub>rrB</sub>	-	80	-	ns	І <sub>FB</sub> =0.1А

#### **Mechanical Characteristics And Ratings**

ltem	Limit			1.1	Following Otondord	Conditions
	Min	Тур	Max	Unit	Following Standard	Conditions
Mounting Torque	0.59	0.69	0.78	N∙m	-	Mounting Screw M3 (Note 1) Recommended 0.69N · m (Note 2)
Pin Pulling Strength	10	-	-	S	EIAJ-ED-4701/400	Load Control Pin:4.9N Power Pin:9.8N
Pin Bending Strength	2	-	-	times	EIAJ-ED-4701/400	Load Control Pin: 2.45N Power Pin:4.9N 90deg. Bend
Weight	-	10	-	g	-	
Heat Sink Flatness	0	-	+200	μm	-	Measurement point is provided in Figure 6-1.


(Note 1) Plain washers of 8mm outside diameter (ISO 7089 to 7094) are recommended.


(Note 2) When installing a module to a heat sink, excessive uneven fastening force might apply stress to inside chips or ceramic of heat sink plate, which will break or crack or degrade a module. An example of recommended fastening sequence is shown in Figure 5. The temporary fastening torque is set to 20 to 30% of the maximum torque rating. Evenly apply thermally-conductive grease with 100µm to 200µm thickness over the contact surface between the module and the heat sink. Also, pay attention not to have any dirt left on the contact surface between the module and the heat sink. It is recommended to install a module directly to a heat sink after applying grease. When installing a module to a heat sink, inserting a heat radiation sheet between a module and a heat sink might apply stress depending on thickness and elastic modulus of the sheet to inside chips or ceramic of heat sink plate, which will break or crack or degrade a module. When using a heat radiation sheet, it is needed to prevent IPM from bending into + side of Figure 6-2.



Temporary fastening :  $1 \rightarrow 2$ Permanent fastening :  $1 \rightarrow 2$ 

Figure 5. Example of Recommended Fastening Sequence








Figure 6-2. Flatness after Installing to a Heat Sink (When Using a Heat Radiation Sheet)

## **Typical Performance Curve**




Figure 10. Vot vs LVIC Tj (Characteristic of VOT pin Vot-Ti Curve)

(Characteristic of FO pin VFO-IFO Curve)

#### **Timing Chart**

- 1) Short Circuit Current Protection (protection with the external shunt resistor and RC filter)
  - a1. Normal operation: IGBT ON and outputs current  $I_{\text{C}.}$
  - a2. Short circuit current detection (SCP trigger)

It is recommended to set RC time constant of 1.0 to 2.0µs so that IGBT shuts down within 2.0µs when SCP is triggered. a3. All low side IGBT's gates are shut down (soft turn off).

- a4. All low side IGBTs turn off.
- a5. FO outputs for  $t_{FO}=20\mu s$  (Min).
- a6. LIN=L
- a7. LIN=H, but all IGBTs keep OFF during SCP=H.
- a8. FO finishes output , but IGBTs don't turn on until inputting the next ON signal(LIN=L $\rightarrow$ H) IGBT of each phase can return to normal state by inputting ON signal to each phase.
- a9. Normal operation: IGBT ON and outputs current Ic.




Figure 11. SCP Timing Chart

#### Notice

SCP works only for low side IGBT only.

In case of SCP trip and FO output, please stop controlling IPM quickly to avoid the abnormal state.

- 2) Control Supply (LVCC) Under Voltage Locked Out (UVLO)
  - b1. Control supply(LVCC) voltage exceeds UVLO release level (V<sub>CCUVR</sub>), but IGBT turns on by the next ON signal (LIN=L→ H).IGBT of each phase can return to normal state by inputting ON signal to each phase.
  - b2. Normal operation: IGBT ON and outputs current Ic.
  - b3. LVCC drops to UVLO trip level (V<sub>CCUVT</sub>).
  - b4. All low side IGBTs turn off in spite of control input condition.
  - b5. FO outputs for t<sub>FO</sub>=minimum 20µs, but output is extended while LVCC is below V<sub>CCUVR</sub>.
  - b6. LVCC reaches V<sub>CCUVR</sub>.
  - b7. Even if LVCC reaches V<sub>CCUVR</sub> during LIN=H, IGBTs don't turn on until inputting the next ON signal (LIN=L $\rightarrow$ H).
  - b8. Normal operation: IGBT ON and outputs current Ic.




Figure 12. LVCC UVLO Timing Chart

- 3) Control supply (VBS) Under Voltage Locked Out (UVLO)
  - c1. Control supply(VBS) voltage exceeds UVLO release level (V<sub>BSUVR</sub>), but IGBT turns on by the next ON signal (HIN=L $\rightarrow$  H).
  - c2. Normal operation: IGBT ON and outputs current Ic.
  - c3. VBS drops to UVLO trip level (VBSUVT).
  - c4. Only IGBT of the corresponding phase turns off in spite of control input signal, there is no FO signal output.
  - c5. VBS reaches  $V_{BSUVR}$ .
  - c6. Even if VBS reaches V<sub>BSUVR</sub> during HIN=H, IGBTs don't turn on until inputting the next ON signal (HIN=L $\rightarrow$ H).
  - c7. Normal operation: IGBT ON and outputs current Ic.






Figure 13. VBS UVLO Timing Chart

## Application Example (one shunt resistor drive)





#### Selection of Components Externally Connected (Refer to Figure 14)

1) VBU, VBV, VBW pin

- The bypass capacitor(good temperature, frequency characteristic electrolytic type C1: 22µF to 100µF) should be mounted as close as possible to the pin in order to prevent malfunction or destruction due to switching noise and power supply ripple. In addition, for the purpose of reducing of the power supply's impedance in wide frequency bandwidth, ceramic capacitor (good temperature, frequency and DC bias characteristic ceramic type C2: 0.1µF to 0.22µF) should also be mounted.
- · Zenner diode D1(1W) should be mounted between each pair of control supply pins to prevent surge destruction.
- Line ripple voltage should meet dV/dt ≤1V/µs, V<sub>ripple</sub> ≤ 2V<sub>p-p.</sub>
- The wiring from U, V, W pin should be as thick and as short as possible. They should be connected directly and separated from the main output wires.
- 2) HVCC, LVCC pin
  - The bypass capacitor(good temperature, frequency characteristic electrolytic type C3) should be mounted as close as
    possible to the pin in order to prevent malfunction or destruction due to switching noise and power supply ripple. In
    addition, for the purpose of reducing of the power supply's impedance in wide frequency bandwidth, ceramic capacitor
    (good temperature, frequency and DC bias characteristic ceramic type C2: 0.1µF to 0.22µF) should also be mounted.
  - Zenner diode D1(1W) should be mounted between each pair of control supply pins to prevent surge destruction.
  - Line ripple voltage should meet dV/dt  $\leq$  1V/µs, V<sub>ripple</sub>  $\leq$  2V<sub>p-p.</sub>
- 3) P pin
  - To prevent surge destruction, the wiring between the smoothing capacitor and P, N pins should be as short as possible.
  - Snubber capacitor(C4: 0.1µF to 0.22µF) should be mounted between the P-N pin.
- 4) Control Input pin (HINU, HINV, HINW, LINU, LINV, LINW)
  - The wiring should be as short as possible to prevent malfunction.
  - Input drive is active-high type. There is a  $3.3k\Omega(Min)$  pull-down resistor in the input circuit of IPM. When using RC coupling circuit, make sure the input signal level meet the input threshold voltage.
  - Dead time of input signal should be more than specified value.
  - The pull-down resistors in LINU and LINV pins become effective when voltage supplied into LVCC pin is in the range of recommended operating condition. LINU and LINV pins have high impedance when power supply to LVCC pin is off.
- 5) FO pin
  - FO output is open drain type. It should be pulled up to control power supply(e.g. 5V, 15V) by a resistor that makes  $I_{FO}$  up to 1mA. $I_{FO}$  is estimated roughly by the formula of control power supply voltage divided by pull-up resistance(R1). In the case of pulled up to 5V, R1=10k $\Omega$  is recommended.
- 6) CIN pin
  - RC filter(R2, C5) should be mounted as close as possible to the pin in order to prevent malfunction by recovery current or switching noise. It is recommended to select tight tolerance, temp-compensated type for RC filter (R2, C5). The time constant R2C5 (1.0µs to 2.0µs is recommended) should be set so that SCP current is shut down within 2µs. Please confirm operation on the actual application since SCP shutdown time changes depending on the PCB wiring pattern.
  - The point D at which the wiring to CIN filter is divided should be near the pin of shunt resistor. NU, NV, NW pin should be connected at near NU, NV, NW pin.
  - To prevent malfunction, the wiring of B should be as short as possible.

7) VOT pin (Refer to Fugure 15)

- It is recommended to insert 5.1kΩ pull down resistor for getting linear output characteristics at lower temperature than
  room temperature. When the pull down resistor is inserted between VOT and GND (control GND), the extra current
  calculated by VOT output voltage divided by pull down resistance flows as LVIC circuit current continuously. In the case
  of only using VOT for detecting higher temperature than room temperature, it isn't necessary to insert the pull down
  resistor.
- In the case of using VOT with low voltage controller (e.g. 3.3V MCU), VOT output might exceed control supply voltage 3.3V when temperature rises excessively. If system uses low voltage controller, it is recommended to insert a clamp diode between control supply of the controller and VOT for preventing over voltage.
- In the case of using low voltage controller like 3.3V MCU, if it is necessary to set the trip VOT level to control supply voltage (e.g. 3.3V) or more, there is the method of dividing the VOT output by resistance voltage divider circuit and then inputting to A/D converter on MCU. In that case, sum of the resistances of divider circuit should be as much as  $5k\Omega$ .
- When VOT pin is not used, please do not connect VOT pin to any other nodes.
- Please refer the application note for this product about the usage of VOT output.





Figure 15. Example of VOT External Circuit

- 8) GND pin
  - Two GND pins (9 & 16 pin) are connected inside IPM. Please connect one pin (16 pin is recommended.) to the 15V power supply GND outside and leave the other open.
  - · If control GND is connected with power GND by common broad pattern, it may cause malfunction by power GND
  - fluctuation. It is recommended to connect control GND and power GND at only a point N (near the pin of shunt resistor).
  - To prevent malfunction, the wiring of A should be as short as possible.
- 9) NU, NV, NW pin
  - When operating with one-shunt resistor, please short the three pins(NU, NV, NW). In addition, to prevent malfunction, the wiring of C should be as short as possible.
- 10) One-shunt Resistor Drive



Low inductance shunt resistor like surface mounted (SMD) type is recommended.

Figure 16. Wiring Pattern around the Shunt Resistor when Operating with One-shunt Resistor

## 11) Three-shunt Resistors Drive

- It is not recommended to input the voltage of each shunt resistor directly to the CIN pin when IPM is operated with three shunt resistor. In that case, it is necessary to use the external protection circuit as below.
- It is necessary to set the time constant R<sub>u</sub>f<sub>f</sub>(1.0µs to 2.0µs is recommended) of external comparator input so that IGBT stops within 2µs when short circuit occurs. Please confirm operation on the actual application since SCP shutdown time changes depending on the PCB wiring pattern.
- It is recommended for the threshold voltage VREF to be set to the same rating of short circuit trip level(Vsc=0.48V(Typ))
- To prevent malfunction, the wiring of A, B, C should be as short as possible.
- OR output high level when protection works should be 0.505V(maximum V<sub>SC</sub> rating) to 7V(CIN absolute maximum rating).





Figure 17. Wiring Pattern around the Shunt Resistor when operating with Three-shunt Resistors

## I/O Equivalence Circuit






Figure 18. Input / Output Equivalent Circuit (X=U, V, W)

#### **Operational Notes**

#### 1. Reverse Connection of Power Supply

Connecting the power supply in reverse polarity can damage the IPM. Take precautions against reverse polarity when connecting the power supply, such as mounting an external diode between the power supply and the IPM's power supply pins.

#### 2. Power Supply Lines

Design the PCB layout pattern to provide low impedance supply lines. Separate the ground and supply lines of the digital and analog blocks to prevent noise in the ground and supply lines of the digital block from affecting the analog block. Furthermore, connect a capacitor to ground at all power supply pins. Consider the effect of temperature and aging on the capacitance value when using electrolytic capacitors.

#### 3. Ground Voltage

Ensure that no pins are at a voltage below that of the ground pin at any time, even during transient condition. However, pins that drive inductive loads (e.g. motor driver outputs, DC-DC converter outputs) may inevitably go below ground due to back EMF or electromotive force. In such cases, the user should make sure that such voltages going below ground will not cause the IPM and the system to malfunction by examining carefully all relevant factors and conditions such as motor characteristics, supply voltage, operating frequency and PCB wiring to name a few.

#### 4. Ground Wiring Pattern

When using both small-signal and large-current ground traces, the two ground traces should be routed separately but connected to a single ground at the reference point of the application board to avoid fluctuations in the small-signal ground caused by large currents. Also ensure that the ground traces of external components do not cause variations on the ground voltage. The ground lines must be as short and thick as possible to reduce line impedance.

#### 5. Thermal Consideration

Should by any chance the maximum junction temperature rating be exceeded the rise in temperature of the chip may result in deterioration of the properties of the chip.

#### 6. Recommended Operating Conditions

These conditions represent a range within which the expected characteristics of the IPM can be approximately obtained. The electrical characteristics are guaranteed under the conditions of each parameter.

#### 7. Inrush Current

When power is first supplied to the IPM, it is possible that the internal logic may be unstable and inrush current may flow instantaneously due to the internal powering sequence and delays, especially if the IPM has more than one power supply. Therefore, give special consideration to power coupling capacitance, power wiring, width of ground wiring, and routing of connections.

#### 8. Operation Under Strong Electromagnetic Field

Operating the IPM in the presence of a strong electromagnetic field may cause the IPM to malfunction.

#### 9. Testing on Application Boards

When testing the IPM on an application board, connecting a capacitor directly to a low-impedance output pin may subject the IPM to stress. Always discharge capacitors completely after each process or step. The IPM's power supply should always be turned off completely before connecting or removing it from the test setup during the inspection process. To prevent damage from static discharge, ground the IPM during assembly and use similar precautions during transport and storage.

#### 10. Inter-pin Short and Mounting Errors

Ensure that the direction and position are correct when mounting the IPM on the PCB. Incorrect mounting may result in damaging the IPM. Avoid nearby pins being shorted to each other especially to ground, power supply and output pin. Inter-pin shorts could be due to many reasons such as metal particles, water droplets (in very humid environment) and unintentional solder bridge deposited in between pins during assembly to name a few.

#### 11. Unused Input Pins


Input pins of an IPM are often connected to the gate of a MOS transistor. The gate has extremely high impedance and extremely low capacitance. If left unconnected, the electric field from the outside can easily charge it. The small charge acquired in this way is enough to produce a significant effect on the conduction through the transistor and cause unexpected operation of the IPM. So unless otherwise specified, unused input pins should be connected to the power supply or ground line.

#### 12. Area of Safe Operation (ASO)


Operate the IPM such that the output voltage, output current, and power dissipation are all within the Area of Safe Operation (ASO).

## **Ordering Information**


QR Code



## Physical Dimension, Tape and Reel Information



## Datasheet



## Revision History

Date	Revision	Changes	
08.Dec.2016	001	New Release	
20.Jun.2017	002	Page 7: (Note 1), (Note 2) changed, Figure6-2 added	
30.Oct.2017	003	Page 17: Description modified	
16.Feb.2018	004	Page 8: Figure 10 Vo⊤ graph modified Page 12: Selection of Components Externally Connected 4) notice added Page 15: Figure 18 Equivalent Circuit of LINU, LINV, LINW modified	

## Notice

#### Precaution on using ROHM Products

1. Our Products are designed and manufactured for application in ordinary electronic equipments (such as AV equipment, OA equipment, telecommunication equipment, home electronic appliances, amusement equipment, etc.). If you intend to use our Products in devices requiring extremely high reliability (such as medical equipment <sup>(Note 1)</sup>, transport equipment, traffic equipment, aircraft/spacecraft, nuclear power controllers, fuel controllers, car equipment including car accessories, safety devices, etc.) and whose malfunction or failure may cause loss of human life, bodily injury or serious damage to property ("Specific Applications"), please consult with the ROHM sales representative in advance. Unless otherwise agreed in writing by ROHM in advance, ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of any ROHM's Products for Specific Applications.

(Note1) Medical Equipment Classification of the Specific Applications
---

JÁPAN	USA	EU	CHINA
CLASSⅢ	CLASSⅢ	CLASS II b	CLASSⅢ
CLASSⅣ	CLASSII	CLASSⅢ	CLASSI

- 2. ROHM designs and manufactures its Products subject to strict quality control system. However, semiconductor products can fail or malfunction at a certain rate. Please be sure to implement, at your own responsibilities, adequate safety measures including but not limited to fail-safe design against the physical injury, damage to any property, which a failure or malfunction of our Products may cause. The following are examples of safety measures:
  - [a] Installation of protection circuits or other protective devices to improve system safety
  - [b] Installation of redundant circuits to reduce the impact of single or multiple circuit failure
- 3. Our Products are designed and manufactured for use under standard conditions and not under any special or extraordinary environments or conditions, as exemplified below. Accordingly, ROHM shall not be in any way responsible or liable for any damages, expenses or losses arising from the use of any ROHM's Products under any special or extraordinary environments or conditions. If you intend to use our Products under any special or extraordinary environments or conditions (as exemplified below), your independent verification and confirmation of product performance, reliability, etc, prior to use, must be necessary:
  - [a] Use of our Products in any types of liquid, including water, oils, chemicals, and organic solvents
  - [b] Use of our Products outdoors or in places where the Products are exposed to direct sunlight or dust
  - [c] Use of our Products in places where the Products are exposed to sea wind or corrosive gases, including Cl<sub>2</sub>, H<sub>2</sub>S, NH<sub>3</sub>, SO<sub>2</sub>, and NO<sub>2</sub>
  - [d] Use of our Products in places where the Products are exposed to static electricity or electromagnetic waves
  - [e] Use of our Products in proximity to heat-producing components, plastic cords, or other flammable items
  - [f] Sealing or coating our Products with resin or other coating materials
  - [g] Use of our Products without cleaning residue of flux (even if you use no-clean type fluxes, cleaning residue of flux is recommended); or Washing our Products by using water or water-soluble cleaning agents for cleaning residue after soldering
  - [h] Use of the Products in places subject to dew condensation
- 4. The Products are not subject to radiation-proof design.
- 5. Please verify and confirm characteristics of the final or mounted products in using the Products.
- 6. In particular, if a transient load (a large amount of load applied in a short period of time, such as pulse. is applied, confirmation of performance characteristics after on-board mounting is strongly recommended. Avoid applying power exceeding normal rated power; exceeding the power rating under steady-state loading condition may negatively affect product performance and reliability.
- 7. De-rate Power Dissipation depending on ambient temperature. When used in sealed area, confirm that it is the use in the range that does not exceed the maximum junction temperature.
- 8. Confirm that operation temperature is within the specified range described in the product specification.
- 9. ROHM shall not be in any way responsible or liable for failure induced under deviant condition from what is defined in this document.

#### Precaution for Mounting / Circuit board design

- 1. When a highly active halogenous (chlorine, bromine, etc.) flux is used, the residue of flux may negatively affect product performance and reliability.
- 2. In principle, the reflow soldering method must be used on a surface-mount products, the flow soldering method must be used on a through hole mount products. If the flow soldering method is preferred on a surface-mount products, please consult with the ROHM representative in advance.

For details, please refer to ROHM Mounting specification

## Precautions Regarding Application Examples and External Circuits

- 1. If change is made to the constant of an external circuit, please allow a sufficient margin considering variations of the characteristics of the Products and external components, including transient characteristics, as well as static characteristics.
- 2. You agree that application notes, reference designs, and associated data and information contained in this document are presented only as guidance for Products use. Therefore, in case you use such information, you are solely responsible for it and you must exercise your own independent verification and judgment in the use of such information contained in this document. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of such information.

#### **Precaution for Electrostatic**

This Product is electrostatic sensitive product, which may be damaged due to electrostatic discharge. Please take proper caution in your manufacturing process and storage so that voltage exceeding the Products maximum rating will not be applied to Products. Please take special care under dry condition (e.g. Grounding of human body / equipment / solder iron, isolation from charged objects, setting of lonizer, friction prevention and temperature / humidity control).

#### Precaution for Storage / Transportation

- 1. Product performance and soldered connections may deteriorate if the Products are stored in the places where:
  - [a] the Products are exposed to sea winds or corrosive gases, including Cl2, H2S, NH3, SO2, and NO2
  - [b] the temperature or humidity exceeds those recommended by ROHM
  - [c] the Products are exposed to direct sunshine or condensation
  - [d] the Products are exposed to high Electrostatic
- 2. Even under ROHM recommended storage condition, solderability of products out of recommended storage time period may be degraded. It is strongly recommended to confirm solderability before using Products of which storage time is exceeding the recommended storage time period.
- 3. Store / transport cartons in the correct direction, which is indicated on a carton with a symbol. Otherwise bent leads may occur due to excessive stress applied when dropping of a carton.
- 4. Use Products within the specified time after opening a humidity barrier bag. Baking is required before using Products of which storage time is exceeding the recommended storage time period.

#### **Precaution for Product Label**

A two-dimensional barcode printed on ROHM Products label is for ROHM's internal use only.

#### Precaution for Disposition

When disposing Products please dispose them properly using an authorized industry waste company.

#### Precaution for Foreign Exchange and Foreign Trade act

Since concerned goods might be fallen under listed items of export control prescribed by Foreign exchange and Foreign trade act, please consult with ROHM in case of export.

#### **Precaution Regarding Intellectual Property Rights**

- 1. All information and data including but not limited to application example contained in this document is for reference only. ROHM does not warrant that foregoing information or data will not infringe any intellectual property rights or any other rights of any third party regarding such information or data.
- 2. ROHM shall not have any obligations where the claims, actions or demands arising from the combination of the Products with other articles such as components, circuits, systems or external equipment (including software).
- 3. No license, expressly or implied, is granted hereby under any intellectual property rights or other rights of ROHM or any third parties with respect to the Products or the information contained in this document. Provided, however, that ROHM will not assert its intellectual property rights or other rights against you or your customers to the extent necessary to manufacture or sell products containing the Products, subject to the terms and conditions herein.

#### **Other Precaution**

- 1. This document may not be reprinted or reproduced, in whole or in part, without prior written consent of ROHM.
- 2. The Products may not be disassembled, converted, modified, reproduced or otherwise changed without prior written consent of ROHM.
- 3. In no event shall you use in any way whatsoever the Products and the related technical information contained in the Products or this document for any military purposes, including but not limited to, the development of mass-destruction weapons.
- 4. The proper names of companies or products described in this document are trademarks or registered trademarks of ROHM, its affiliated companies or third parties.

## **General Precaution**

- 1. Before you use our Products, you are requested to care fully read this document and fully understand its contents. ROHM shall not be in an y way responsible or liable for failure, malfunction or accident arising from the use of a ny ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this docume nt is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sale s representative.
- 3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate an d/or error-free. ROHM shall not be in an y way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.



## BM63564S-VC - Web Page

Part Number	BM63564S-VC
Package	HSDIP25VC
Unit Quantity	60
Minimum Package Quantity	12
Packing Type	Tube
Constitution Materials List	inquiry
RoHS	Yes