



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOMINAL DUCT SIZE (W X H)	B	D	D TOL.	H REF	K	T	T TOL	R
.5 X .5	.69 (17.5)	.38 (9.7)	±.014 (.4)	.50 (12.7)	J	.050 (1.3)	±.008 (.2)	N/A
.5 X 1	.75 (19.1)	.75 (19.1)	±.020 (.5)	1.00 (25.4)	C	∅	±.010 (.3)	N/A
.75 X .75	.94 (23.8)	.56 (14.3)	∅	.75 (19.1)	Z	.055 (1.4)	±.008 (.2)	N/A
.75 X 1	∅	N/A	N/A	1.00 (25.4)	N/A	∅	∅	N/A
.75 X 1.5	∅	1.20 (30.5)	±.020 (.5)	1.50 (38.1)	ON C/L	.070 (1.8)	±.010 (.3)	N/A
.75 X 2	∅	N/A	N/A	2.00 (50.8)	N/A	.080 (2.0)	±.008 (.2)	N/A
1 X 1	1.25 (31.8)	.75 (19.1)	±.020 (.5)	1.00 (25.4)	∅	.055 (1.4)	±.010 (.3)	N/A
1 X 1.5	∅	1.20 (30.5)	∅	1.50 (38.1)	∅	.070 (1.8)	±.008 (.2)	N/A
1 X 2	∅	1.63 (41.4)	±.030 (.8)	2.00 (50.8)	∅	.080 (2.0)	±.015 (.4)	.712 (18.1)
1 X 3	∅	2.63 (66.8)	∅	3.00 (76.2)	∅	.095 (2.4)	±.012 (.3)	1.212 (30.8)
1 X 4	∅	3.63 (92.2)	∅	4.00 (101.6)	∅	.105 (2.7)	±.019 (.5)	1.700 (43.2)
1.5 X 1	1.75 (44.5)	.75 (19.1)	±.020 (.5)	1.00 (25.4)	∅	.060 (1.5)	±.010 (.3)	N/A
1.5 X 1.5	∅	1.20 (30.5)	∅	1.50 (38.1)	∅	.070 (1.8)	±.012 (.3)	N/A
1.5 X 2	∅	1.63 (41.4)	±.030 (.8)	2.00 (50.8)	∅	.080 (2.0)	∅	.712 (18.1)
1.5 X 3	∅	2.63 (66.8)	∅	3.00 (76.2)	∅	.095 (2.4)	±.010 (.3)	1.212 (30.8)
1.5 X 4	∅	3.63 (92.2)	∅	4.00 (101.6)	∅	.105 (2.7)	±.012 (.3)	1.700 (43.2)

N/A = NOT AVAILABLE



NOMINAL DUCT SIZE (W X H)	B	D	D TOL.	H REF	K	T	T TOL	R
2 X 1	2.25 (57.2)	.75 (19.1)	±.020 (.5)	1.00 (25.4)	.50 (12.7)	.060 (1.5)	±.010 (.3)	N/A
2 X 1.5	∅	1.20 (30.5)	∅	1.50 (38.1)	∅	.070 (1.8)	±.012 (.3)	N/A
2 X 2	∅	1.63 (41.4)	±.030 (.8)	2.00 (50.8)	∅	.080 (2.0)	∅	.712 (18.1)
2 X 3	∅	2.63 (66.8)	∅	3.00 (76.2)	∅	.095 (2.4)	±.010 (.3)	1.212 (30.8)
2 X 4	∅	3.63 (92.2)	∅	4.00 (101.6)	∅	.105 (2.7)	±.017 (.4)	1.700 (43.2)
2 X 5	∅	4.63 (117.6)	±.040 (1.0)	5.00 (127.0)	∅	.111 (2.8)	∅	2.233 (56.7)
2.5 X 3	2.75 (69.8)	N/A	N/A	3.00 (76.2)	N/A	.095 (2.4)	±.015 (.4)	N/A
3 X 1	3.25 (82.6)	.75 (19.1)	±.020 (.5)	1.00 (25.4)	1.00 (25.4)	.065 (1.7)	±.010 (.3)	N/A
3 X 2	∅	1.63 (41.4)	±.030 (.8)	2.00 (50.8)	∅	.080 (2.0)	∅	.712 (18.1)
3 X 3	∅	2.63 (66.8)	∅	3.00 (76.2)	∅	.100 (2.5)	±.015 (.4)	1.212 (30.8)
3 X 4	∅	3.63 (92.2)	∅	4.00 (101.6)	∅	.105 (2.7)	∅	1.700 (43.2)
3 X 5	∅	4.63 (117.6)	±.040 (1.0)	5.00 (127.0)	∅	.115 (2.9)	±.012 (.3)	2.233 (56.7)
4 X 1.5	4.25 (108.0)	N/A	N/A	1.50 (38.1)	N/A	.070 (1.8)	±.008 (.2)	N/A
4 X 2	∅	1.63 (41.4)	±.030 (.8)	2.00 (50.8)	1.50 (38.1)	.080 (2.0)	∅	.712 (18.1)
4 X 3	∅	2.63 (66.8)	∅	3.00 (76.2)	∅	.095 (2.4)	±.010 (.3)	1.212 (30.8)
4 X 4	∅	3.63 (92.2)	∅	4.00 (101.6)	∅	.105 (2.7)	±.012 (.3)	1.700 (43.2)
4 X 5	∅	4.63 (117.6)	±.040 (1.0)	5.00 (127.0)	∅	.110 (2.8)	±.018 (.5)	2.233 (56.7)
6 X 4	6.25 (158.8)	N/A	N/A	4.00 (101.6)	N/A	.110 (2.8)	±.010 (.3)	N/A

N/A = NOT AVAILABLE  
> = AVAILABLE AS "FS" ONLY.



WAS DPC\_PVC\_F\_US\_01

CAD FILENAME/LAYERS

D34301BA\_PVC\_F\_US\_02

DIMENSIONS IN PARENTHESIS ARE IN METRIC.

REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP
4	8-3-01	JCST	JKG	SEE SHEET 1 FOR REVISION NUMBERS	34301-03	JKG	JKG	
3	01-24-97	JBA	CEF	SEE SHEET 1 FOR REVISION NUMBERS	34301-03	CEF	CEF	
2	10-18-95	DW	CEF	SEE SHEET 1 FOR REVISION NUMBERS	34301-03	CEF	CEF	
1	10-27-93	DW	CEF	SEE SHEET 1 FOR REVISION NUMBERS	34301-03	CEF	CEF	
R	3/17/93	DW	BKR	SEE SHEET 1 FOR REVISION NUMBERS	34301-03	CEF	CEF	
REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP

  

SCALE	MATERIAL:	DRAWING NO.	DWG
NONE	POLYVINYL CHLORIDE	34301-03	A
		Sht 2 of 2	SIZE

  

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
(.X) ± .12(.3.1) ANGLES ±	
(.XX) ± .12(.3.1) ANGLES ±	
(.XXX) ±	

  

WIRING DUCT, TYPE "F" & "FS" CUSTOMER DRAWING
PANDUIT CORP. TINLEY PARK, ILLINOIS

PANDUIT

WIRING DUCT, TYPE "F" & "FS" CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

SCALE: NONE

DRAWING NO. 34301-03 Sht 2 of 2

DWG: A