



- Low Cost
- 5V to 48V Outputs
- Universal Input
- Compact Size
- NEC Class 2 Compliant
- UL508 Listed
- -10°C to +71°C Operation

DPP15-100 Series

15-100W, 5-48V Output

DIN Rail Mount Power Supplies

Key Market Segments & Applications

- Industrial Controls: Motor Control Systems
- Factory Automation: Process Control, Automotive, Chemical Processing
- Test & Measurement: Burn in & Test, Instrumentation Measurement

DPP15-100 Features and Benefits

Features

- PFC Compliant to EN61000-3-2
- UL508 Approvals
- TS35/7.5 or TS35/15 DIN Rail Mounting

Benefits

- Supports Global Use
- Easier System Configuration
- Easy System Integration

Specifications

ITEMS	MODELS		DPP15	DPP25/30	DPP50	DPP100
	(1)	VAC				
AC Input Voltage range	(1)	VAC	85 - 264VAC			85 - 132VAC 176 - 264VAC
Input Frequency		Hz	47 - 63Hz			
Inrush Current (115 / 230VAC)		A	<35A	35 / 45A	35 / 50A	35 / 55A
Power Factor		-	Meets EN61000-3-2 Class A			
Max Input Current (230VAC)		A	0.25	0.4	0.7	1.2
Output Voltage Accuracy		%	±1% (24V outputs preset at 24.5V)			
Line Regulation		%	< 0.5%			
Load Regulation		%	< 0.5%			
Ripple/Noise		mV	<50mV (20MHz Bandwidth)			
Overcurrent Protection (Typ)		-	>120%			
Overvoltage Protection		V	125 - 137.5%			
Hold Up Time (115VAC input)		ms	> 20ms			
Parallel switch		-	No			Yes
LED Indicator		-	Green LED = On			
Operating Temperature		-	-10°C to +71°C (Derate linearly 5%/°C from 61°C to 71°C)			
Storage Temperature		-	-25°C to +85°C			
Operating Humidity		-	20 - 90% RH (non condensing)			
Cooling	(2)	-	Convection			
Withstand Voltage		-	Input to Output 3kVAC for 1 min.			
Shock		-	Half sine wave, 4G, 22ms, 3 times per face, X, Y, Z			
Vibration		-	10-500Hz (20 min sweep) 0.002G ² /Hz, 1Grms acceleration X, Y, Z, 1 hour			
Isolation Resistance		Ω	>100MΩ at 25°C & 70%RH, Output to Ground 500VDC			
Safety Agency Approvals		-	IEC/UL/CSA/EN60950-1, 60950-1, UL508, UL1310(3) (Class 2), CE Mark			
Emissions		-	EN55011, EN55032 Class B Radiated & Conducted, EN61000-6-3			
Immunity		-	EN61000-6-2, EN61000-4-2 Level 4, EN61000-4-3, EN61000-4-6 Level 3			
		-	EN61000-4-4 Level 4 (I/P) Level 3 (O/P), EN61000-4-5 Level 3 L-N, Level 4 L/N-PE, EN61000-4-8, EN61000-4-11			
Weight (Typ)		g	130	260		390
Size (WxHxD)		mm	23 x 75 x 97	45 x 75 x 91		73 x 75 x 97
Case material		-	Plastic			
MTBF (MIL-HDBK-217F, GF25)		Hours	287,000	>288,000	273,000	239,000
Warranty		yrs	3			

(1) Auto Select - DPP100 only

(3) Does not include DPP25-5 & DPP100-24 models. Evaluated to NEC NFPA70 Class 2 output per UL1310.

(2) Recommend 25mm clearance on all sides.

Model Selector						
Model	Output Voltage (V)	Output Adjust (V)	Output Curr. (A)	Max. Output Power (W)	Efficiency at Full Load (%)	
DPP25-5	5	5-6	5	25	78	
DPP30-12	12	9.9-12.1	2.5	30	82	
DPP50-15	15	11.9-15.1	3.4	50	85	
DPP15-24	24	22.5-28.5	0.63	15	80	
DPP30-24	24	22.5-28.5	1.3	30	84	
DPP50-24	24	22.5-28.5	2.1	50	86	
DPP100-24	24	22.5-28.5	4.2	100	87	
DPP50-48	48	48-56	1.05	50	87	

Installation


Snap-on Mounting - snap onto DIN Rail TS35/7.5 or TS35/15 (no tools required)

Cooling - Normal Convection


Clearance - 25mm all sides

Connection - Use copper wire 0.5-2.5mm² (AWG24-12)


Outline Drawing DPP15 Series



Outline Drawing DPP25-DPP50 Series



Outline Drawing DPP100 Series





TDK-Lambda France SAS

Tel: +33 1 60 12 71 65
france@fr.tdk-lambda.com
www.emea.lambda.tdk.com/fr



Italy Sales Office

Tel: +39 02 61 29 38 63
info.italia@it.tdk-lambda.com
www.emea.lambda.tdk.com/it



Netherlands

info@nl.tdk-lambda.com
www.emea.lambda.tdk.com/nl



TDK-Lambda Germany GmbH

Tel: +49 7841 666 0
info@de.tdk-lambda.com
www.emea.lambda.tdk.com/de



Austria Sales Office

Tel: +43 2256 655 84
info@at.tdk-lambda.com
www.emea.lambda.tdk.com/at



Switzerland Sales Office

Tel: +41 44 850 53 53
info@ch.tdk-lambda.com
www.emea.lambda.tdk.com/ch



TDK-Lambda Nordic

Tel: +45 3222 8086
info@dk.tdk-lambda.com
www.emea.lambda.tdk.com/dk



TDK-Lambda UK Ltd.

Tel: +44 (0) 12 71 85 66 66
info@uk.tdk-lambda.com
www.emea.lambda.tdk.com/uk



TDK-Lambda Ltd.

Tel: +9 723 902 4333
info@tdk-lambda.co.il
www.emea.lambda.tdk.com/il



C.I.S.

Commercial Support:

Tel: +7 (495) 665 2627

Technical Support:

Tel: +7 (812) 658 0463

info@tdk-lambda.ru
www.emea.lambda.tdk.com/ru



TDK-Lambda Americas

Tel: +1 800-LAMBDA-4 or 1-800-526-2324
powersolutions@us.tdk-lambda.com
www.us.lambda.tdk.com



TDK Electronics do Brasil Ltda

Tel: +55 11 3289-9599
sales.br@tdk-electronics.tdk.com
www.tdk-electronics.tdk.com/en



TDK-Lambda Corporation

Tel: +81-3-6778-1113
www.jp.lambda.tdk.com



TDK-Lambda (China) Electronics Co. Ltd.

Tel: +86 21 6485-0777
powersolutions@cn.tdk-lambda.com
www.lambda.tdk.com.cn



TDK-Lambda Singapore Pte Ltd.

Tel: +65 6251 7211
tts.mkt@sg.tdk-lambda.com
www.sg.lambda.tdk.com



TDK India Private Limited, Power Supply Division

Tel: +91 80 4039-0660
mathew.philip@in.tdk-lambda.com
www.sg.lambda.tdk.com

