


Standard Open Toroidal Transformers

50VA Open Style, with Leads. Dual 115V Primaries, Dual Secondaries

High quality open style toroidal transformers with dual 115V/50-60Hz primary windings. Twin secondary windings may be connected in series or parallel, or used independently



Nuvotem Part Number	Alternate Reference	Full Load Vsec [V]	Rated Current per Sec [A]	No Load Vsec [V]	DC Resistance [Ohms] @ 25°C	DEKRA Certificate
0050P2-2-006	91946-P2S2	2 x 6	4.167	2 x 6.80	2 x 0.0914	2161054.01
0050P2-2-009	91947-P2S2	2 x 9	2.778	2 x 10.20	2 x 0.2139	2161054.01
0050P2-2-012	91948-P2S2	2 x 12	2.083	2 x 13.71	2 x 0.3977	2161054.01
0050P2-2-015	91949-P2S2	2 x 15	1.667	2 x 17.22	2 x 0.6411	2161054.01
0050P2-2-018	91950-P2S2	2 x 18	1.389	2 x 20.39	2 x 0.8519	2161054.01
0050P2-2-025	91951-P2S2	2 x 25	1.000	2 x 28.78	2 x 1.9135	2161054.02
0050P2-2-055	91952-P2S2	2 x 55	0.455	2 x 63.22	2 x 9.4110	2161054.02

Primary Winding	Input Voltage Range :	Series: 207V–253V (230V±10%) @ 50/60Hz Parallel: 103.5V–126.5V (115V±10%) @ 50/60Hz	
	DC Resistance @ 25°C =	Approx 24.5 Ohms each	
Losses	Iron Losses	0.41 Watts approx	
	Copper Losses	8.35 Watts approx	
Temperature Class	Winding Wire (Primary & Secondary)	Class H (180°C)	
	Insulation between input and output	Class B (130°C)	
	Connection lead insulation	Class A (105°C)	
Standards	Approved to UL506 & UL5085 : File E215495		
	Approved to EN61558 : DEKRA Certificates 2161054.01 or 2161054.02 (see table above)		
	Conforms to EN60065, VDE0550, BS415.		
Physical Data	Approximate Dimensions	Diameter	80mm*
		Height	33mm
	Approximate Weight	0.45 Kg	
		* Measured away from leadout bulge; Allow extra 4mm at leads.	
Terminations	Primary	Flexible equipment wire UL Style 1569 (105°C), CSA Type TR-64 (90°C) Double-insulated over entire length with 105°C PVC tubings. 150mm Long, 10mm tinned ends.	
	Secondary	Solid copper conductors (extension of winding wire), insulated over their entire length with 105°C PVC tubing. 150mm Long, 10mm tinned ends.	
Mounting Hardware	Each transformer is supplied with a mounting kit, comprising:		
	Neoprene Insulating disc	2 pieces	
	Dished Steel Washer	1 piece	

Regional Locations - Design, Manufacturing, Sales & Marketing
Talema Group Global Offices
North America
**United States
(Sales & Marketing)**

Talema Group, LLC
 PO Box 935
 900 Innovation Drive
 Suite 120, Rolla
 Missouri 65402
 Tel: +1 573-303-3675
 E-Mail:
 sales@talema.com
 Web: talema.com

Asia
**India
(Design, Manufacturing, Sales & Marketing)**
Administrative Office

Talema Electronic India Private Limited
 Door No. 221, 1st and 2nd Floor
 KJ Plaza, Opp.to Vidya Mandir School
 Meyanur Main Road
 Salem - 636 004 Tamil Nadu INDIA.
 Tel: +91 427 - 243 3100
 Fax: +91 427 - 243 3109
 E-Mail: talema@talemaindia.net
 Web: talema.com

Factory Premises

Talema Electronic India Private Limited
 No. 31 & 31, Electronic Industrial Estate
 Suramangalam Post
 Salem - 636 005 Tamil Nadu INDIA
 Tel: +91 427 - 243 3000
 E-Mail: talema@talemaindia.net
 Web: talema.com

Europe
**Germany
(Design, Sales & Marketing)**

Talema Elektronik GmbH
 Sembdnerstr. 5
 82110 Germering
 Tel: +49 89 - 841 00 - 0
 Fax: +49 89 - 841 00 25
 E-Mail: info@talema.de
 Web: talema.com

**Ireland
(Design, Sales & Marketing)**

Nuvotem TEO
 Units W & X, Gweedore Business Park
 Derrybeg, Letterkenny, Co. Donegal
 Tel: +353 (0) 74 95 48666
 Fax: +353 (0) 74 95 48139
 E-Mail: info@nuvotem.com
 Web: talema.com

**Czech Republic
(Design, Manufacturing, Sales & Marketing)**

NT Magnetics s.r.o.
 Chebská 27
 322 00 Plzeň
 Tel: +420 377 - 338 351
 Fax: +420 377 - 338 350
 E-Mail: talema@talema.cz
 Web: talema.com

Locations of Talema Group Global Offices
