


**KEMET Part Number: PMR209MC6100M100R30**  
(P409CE104M250AH101)



Capacitor, Film, Metallized Paper, 0.1 uF, +/-20% Tol, -40/+85C, Integrated Resistor (X2), 630 VDC@85C, Lead Spacing=20.3 mm, Not For New Design, Please Check Possible Alternative Parts (AltPart)



General Information	
Supplier:	KEMET
Dielectric:	Metallized Paper
Application:	Integrated Resistor (X2)
Style:	Radial Molded
Lead Form:	Wire Leads
Features:	Pulse
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	24	MAX
H	14	MAX
T	7.6	MAX
S	20.3	+/-0.4
LL	30	+5
F	0.8	+/-0.05

Specifications	
Capacitance:	0.1 uF
Voltage:	630 VDC
Tolerance:	+/-20%
Voltage AC:	250 VAC
Rated Temperature:	85C
Temperature Range:	-40/+85C
Insulation Resistance:	3 GOhm
Miscellaneous:	Not For New Design, Please Check Possible Alternative Parts (AltPart)
Miscellaneous:	Resistor= 100 Ohms

Packaging Specifications	
Package Kind:	Bulk
Package Quantity:	250

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006-2016 IntelliData.net