



SPECIFICATIONS			
GRIP CODE	S	M	L
REAL SECTION MM2	0.22 to 0.44	0.49 to 0.94	0.95 to 1.87
MOLEX PART NUMBER (P/N*)	0988971109	0988971119	0988971129
PLATING	Pre-plated 2µ Sn min.	Pre-plated 2µ Sn min.	Pre-plated 2µ Sn min.
MATERIAL	HIGH COPPER		
PART WEIGHT (g)	0.3582	0.3778	0.3955
THICKNESS	0.30		
A	2.40	2.70	3.10
B	1.90	2.60	3.50
Ø E	1.20	1.40	1.60
C	4.20	4.35	4.70
D	3.30	3.65	4.20
Ø F	2.40	2.50	2.70

NOTE:
 CRIMPING SPEC : AS-98897-001
 PACKAGING SPEC : PK-98897-001

MODIFY CRIMP AND PACKAGING NUMBER EC NO: G2012-0124 DRAWN BY: JOWAS CHKD.: DUCLOS APPR.: OPLESSIS	2012/02/08 2012/02/09 2012/02/17	QUALITY SYMBOLS ∇=0 ∇=0 ∇=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.10 ± --- 1 PLACE ± 0.1 ± --- ANGULAR ± 2°	DIMENSION STYLE MM ONLY	SCALE 10:1	DESIGN UNITS METRIC	FIRST ANGLE PROJECTION	
	DESCRIPTION NSCC 1.5 WIRE TERMINAL	DRAWN BY G. DESBRUERES	DATE 2009/11/03	CHECKED BY D. DOS SANTOS	DATE 2009/11/03	TITLE NSCC 1.5 WIRE TERMINAL		
	APPROVED BY OPLESSIS	DATE 2010/10/26	MATERIAL NO. SEE CHART			MOLEX INCORPORATED	DOCUMENT NO. SD-98897-050	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE A2	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					