

PRODUCT-DETAILS

# EH04-11N

## EH04-11N Auxiliary Contact



### General Information

Extended Product Type	EH04-11N
Product ID	1SAE901901R1011
EAN	4013614527616
Catalog Description	EH04-11N Auxiliary Contact
Long Description	The EH04 are auxiliary contact blocks which can be used in combination with all the new ESB..N and EN..N installation contactors. These devices are available in 2 different contact configurations and no tool is needed for their assembling.

### Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85369010

### Popular Downloads

Instructions and Manuals	2CDC1003008M1001
--------------------------	------------------

### Dimensions

Product Net Width	9 mm
Product Net Depth / Length	65 mm

Product Net Height	85 mm
Product Net Weight	0.04 kg

## Technical

Rated Operational Voltage	Auxiliary Circuit 500 V AC
Rated Frequency (f)	Auxiliary Circuit 50 Hz Auxiliary Circuit 60 Hz
Rated Impulse Withstand Voltage ( $U_{imp}$ )	Auxiliary Circuit 4 kV
Rated Insulation Voltage ( $U_i$ )	500 V
Degree of Protection	IP20
Tightening Torque	Auxiliary Circuit 0.9 N·m
Wire Stripping Length	Auxiliary Circuit, Top Terminals (1x 1.5) 7 mm Auxiliary Circuit, Top Terminals (1x 2.5 ... 4) 17 mm Auxiliary Circuit, Top Terminals (2x 1.5) 17 mm Auxiliary Circuit, Bottom Terminals (1x 1.5) 7 mm Auxiliary Circuit, Bottom Terminals (1x 2.5 ... 4) 9 mm Auxiliary Circuit, Bottom Terminals (2x 1.5) 9 mm
Standards	IEC/EN 60947-5-1
Number of Auxiliary Contacts NO	1
Product Name	Auxiliary Contact
Suitable For	ESB16..N ESB20..N ESB25..N ESB40..N ESB63..N EN20..N EN25..N EN40..N ESB100..N
Suitable for Product Class	Installation Contactors

## Technical UL/CSA

Maximum Operating Voltage UL/CSA	Auxiliary Circuit 600 V AC/DC
Connecting Capacity Auxiliary Circuit UL/CSA	Stranded 18-12 AWG
Tightening Torque UL/CSA	Auxiliary Circuit 8 in·lb

## Environmental

Ambient Air Temperature	Operation -25 ... +55 °C Storage -40 ... +80 °C
Conventional Free-air Thermal Current ( $I_{th}$ )	Auxiliary Circuit 6 A
Maximum Operating Altitude Permissible	2000 m
Resistance to Shock acc. to IEC 60068-2-27	11 ms Pulse 15g
Resistance to Vibrations acc. to IEC 60068-2-6	5g / 3 ... 150 Hz
RoHS Status	Following EU Directive 2011/65/EU

---

## Certificates and Declarations (Document Number)

---

ABS Certificate	1SAA920000-0101
CB Certificate	1SAA920006-2001
CCC Certificate	1SAA920004-3801
cULus Certificate	cUL_E191658
Declaration of Conformity - CE	1SAD938504-0302
DNV Certificate	1SAA920000-0306
EAC Certificate	1SAA920002-2701
Instructions and Manuals	2CDC1003008M1001
RINA Certificate	1SAA920000-0801
RoHS Information	1SAD938503-0302

---



---

## Container Information

---

Package Level 1 Width	87 mm
Package Level 1 Depth / Length	18 mm
Package Level 1 Height	69.5 mm
Package Level 1 Gross Weight	0.05 kg
Package Level 1 EAN	4013614527814
Package Level 1 Units	1 piece

---



---

## Classifications

---

Object Classification Code	K
ETIM 5	EC000041 - Auxiliary contact block
ETIM 6	EC000041 - Auxiliary contact block
ETIM 7	EC000041 - Auxiliary contact block
eClass	7.0 27371302
UNSPSC	39121522
E-Number (Sweden)	3210569

---



---

## Categories

---

Low Voltage Products and Systems → Control Products → Contactors → Installation Contactors Accessories

Low Voltage Products and Systems → Modular DIN Rail Products → Modular DIN Rail Components MDRCs → Installation  
Contactors Accessories

