



3-conductor through terminal block suitable for Ex i applications

281-651

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.08 - 4 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP®CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	32 A
Weight	10.401 g
Color	blue
Wiring type	Angled Type
No. of connection Points	3
No. of potentials	1
Height	37 mm
Height	1.46 in
Width	6 mm
Width	0.236 in
Depth	61.5 mm
Depth	2.42 in
Strip length from	9 mm
Strip length to	10 mm
Strip length	0.37 in
Mounting	TS 35