


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A	B	C	D	E	F	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT2H	.188 (4.8)	2.00 (51)	.075 (1.9)	.300 (7.6)	.338 (8.6)	.290 (7.4)	.480 (12.2)	8.1 (206)	120 (534)	HEAVY	STRAIGHT	.76 (346)
PLT2.5H	.188 (4.8)	2.50 (64)	.075 (1.9)	.300 (7.6)	.338 (8.6)	.290 (7.4)	.480 (12.2)	9.8 (251)	120 (534)	HEAVY	STRAIGHT	.90 (408)
PLT3H	.188 (4.8)	3.00 (76)	.075 (1.9)	.300 (7.6)	.338 (8.6)	.290 (7.4)	.480 (12.2)	11.4 (290)	120 (534)	HEAVY	STRAIGHT	1.04 (472)
PLT4H	.188 (4.8)	4.00 (102)	.075 (1.9)	.300 (7.6)	.338 (8.6)	.290 (7.4)	.480 (12.2)	14.5 (368)	120 (534)	HEAVY	STRAIGHT	1.28 (581)
PLT5H	.188 (4.8)	5.00 (127)	.078 (2.0)	.350 (8.9)	.406 (10.1)	.340 (8.6)	.560 (14.2)	17.7 (450)	175 (778)	HEAVY	STRAIGHT	2.06 (934)
PLT6H	.188 (4.8)	6.00 (152)	.078 (2.0)	.350 (8.9)	.406 (10.1)	.340 (8.6)	.560 (14.2)	20.9 (530)	175 (778)	HEAVY	STRAIGHT	2.46 (1116)
PLT8H	.188 (4.8)	9.00 (229)	.078 (2.0)	.350 (8.9)	.406 (10.3)	.340 (8.6)	.560 (14.2)	30.6 (779)	175 (778)	HEAVY	STRAIGHT	3.36 (1524)
PLT13H	.188 (4.8)	13.00 (330)	.078 (2.0)	.350 (8.9)	.406 (10.3)	.340 (8.6)	.560 (14.2)	43.3 (1100)	175 (778)	HEAVY	STRAIGHT	4.59 (2080)

NOTE:

*SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	MATERIAL:
							PAN-TY CABLE TIES - PLT SERIES	NYLON 6.6
							CUSTOMER DRAWING	
							ITEM REVISION NAME	
							W10001CD/10	
							DATASET FILE NAME	
							W10001CD/10-SS-5540 SH4 PLT SERIES CUSTOMER	
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	
							.x ± .02 [.5]	
							.xxx ± .020 [.51]	
							ANGLES ±	
							THIRD ANGLE PROJECTION	
							DRAWING NUMBER:	SS-5540 SHEET 4
							DRAWN BY	CEW
							DATE	12-27-84
							CHK	HVP
							SCALE	NONE
							SHT 1 OF 1	
							SIZE	A

D10100DA/16