

Low Cost 3.3 V Spread Aware Zero Delay Buffer

Features

- 10 MHz to 100 MHz and 133 MHz operating range, compatible with CPU and PCI bus frequencies
- Zero input-output propagation delay
- Multiple low skew outputs
 - □ Output-output skew less than 250 ps
 - □ Device-device skew less than 700 ps
 - One input drives five outputs (CY23S05)
 - □ One input drives nine outputs, grouped as 4 + 4 + 1 (CY23S09)
- Less than 200 ps Cycle-to-cycle jitter
- Test mode to bypass PLL (CY23S09 only, see Select Input Decoding for CY23S09 on page 4)
- Available in space saving 16-pin, 150-mil SOIC, 4.4 mm TSSOP (CY23S09) or 8-pin, 150-mil SOIC package (CY23S05)
- 3.3 V operation, advanced 0.65µ CMOS technology
- Spread Aware

Functional Description

The CY23S09 is a low cost 3.3 V zero delay buffer designed to distribute high speed clocks and is available in a 16-pin SOIC package. The CY23S05 is an 8-pin version of the CY23S09. It accepts one reference input, and drives out five low skew clocks. The -1H versions of each device operate at up to 100 and 133 MHz frequencies and have higher drive than the -1 devices.

All parts have on-chip PLLs that lock to an input clock on the REF pin. The PLL feedback is on-chip and is obtained from the CLKOUT pad.

The CY23S09 has two bans of four outputs each, which can be controlled by the select inputs as shown in the Select Input Decoding table on Select Input Decoding for CY23S09 on page 4. If all output clocks are not required, Bank B can be three-stated. The select inputs also allow the input clock to be directly applied to the outputs for chip and system testing purposes.


The CY23S09 and CY23S05 PLLs enter a power down mode when there are no rising edges on the REF input. In this state, the outputs are three-stated and the PLL is turned off, resulting in less than 12.0 μ A of current draw (for commercial temperature devices) and 25.0 μ A (for industrial temperature devices). The CY23S09 PLL shuts down in one additional case, as shown in the Select Input Decoding for CY23S09 on page 4.

Multiple CY23S09 and CY23S05 devices can accept the same input clock and distribute it. In this case, the skew between the outputs of two devices is guaranteed to be less than 700 ps.

All outputs have less than 200 ps of cycle-to-cycle jitter. The input to output propagation delay on both devices is guaranteed to be less than 350 ps; the output to output skew is guaranteed to be less than 250 ps.

The CY23S05 and CY23S09 is available in two different configurations, as shown in the Ordering Information on page 8. The CY23S05-1 and CY23S09-1 is the base part. The CY23S05-1H and CY23S09-1H is the high drive version of the -1, and its rise and fall times are much faster than -1.

For a complete list of related resources, click here.



Cypress Semiconductor Corporation
Document Number: 38-07296 Rev. *I

198 Champion Court

San Jose, CA 95134-1709 • 408-943-2600



Contents

Pinouts	. 3
Select Input Decoding for CY23S09	. 4
Functional Overview	. 4
Zero Delay and Skew Control	4
Spread Aware	4
Maximum Ratings	. 5
Operating Conditions for CY23S05SXX-XX and	
CY23S09SXX-XX (Industrial, Commercial Devices)	. 5
Electrical Characteristics for CY23S05SXX-XX and	
CY23S09SXX-XX (Industrial, Commercial Devices)	. 5
Switching Characteristics for CY23S05SXC-1 and	
CY23S09SXC-1 Commercial Temperature Devices	
Switching Characteristics for CY23S05SXI-1H Industria	
Temperature Devices	. 6
Switching Waveforms	. 6
Test Circuits	.7

I nermai Resistance	<i>(</i>
Ordering Information	8
Ordering Code Definitions	8
Package Diagrams	
Acronym	11
Document Conventions	
Units of Measure	11
Document History Page	12
Sales, Solutions, and Legal Information	
Worldwide Sales and Design Support	13
Products	13
PSoC® Solutions	13
Cypress Developer Community	13
Technical Support	



Pinouts

Figure 1. Pin Configuration - CY23S09




Figure 2. Pin Configuration - CY23S05




Table 1. Pin Description for CY23S09

Pin	Signal	Description	
1	REF ^[1]	Input reference frequency, 5 V tolerant input	
2	CLKA1 ^[2]	Buffered clock output, bank A	
3	CLKA2 ^[2]	Buffered clock output, bank A	
4	V_{DD}	3.3 V supply	
5	GND	Ground	
6	CLKB1 ^[2]	Buffered clock output, bank B	
7	CLKB2 ^[2]	Buffered clock output, bank B	
8	S2 ^[3]	Select input, bit 2	
9	S1 ^[3]	Select input, bit 1	
10	CLKB3 ^[2]	Buffered clock output, bank B	
11	CLKB4 ^[2]	Buffered clock output, bank B	
12	GND	Ground	
13	V_{DD}	3.3 V supply	
14	CLKA3 ^[2]	Buffered clock output, bank A	
15	CLKA4 ^[2]	Buffered clock output, bank A	
16	CLKOUT ^[2]	Buffered output, internal feedback on this pin	

Table 2. Pin Description for CY23S05

Pin	Signal	Description	
1	REF ^[1]	Input reference frequency, 5 V tolerant input	
2	CLK2 ^[2]	Buffered clock output	
3	CLK1 ^[2]	Buffered clock output	
4	GND	Ground	
5	CLK3 ^[2]	Buffered clock output	
6	V_{DD}	3.3 V supply	
7	CLK4 ^[2]	Buffered clock output	
8	CLKOUT ^[2]	Buffered clock output, internal feedback on this pin	

Notes

- Weak pull down.
 Weak pull down on all outputs.
 Weak pull up on these inputs.



Select Input Decoding for CY23S09

S2	S1	CLOCK A1-A4	CLOCK B1-B4	CLKOUT ^[4]	Output Source	PLL Shutdown
0	0	Three-state	Three-state	Driven	PLL	N
0	1	Driven	Three-state	Driven	PLL	N
1	0	Driven	Driven	Driven	Reference	Υ
1	1	Driven	Driven	Driven	PLL	N

Functional Overview

Zero Delay and Skew Control

All outputs must be uniformly loaded to achieve Zero Delay between the input and output. Because the CLKOUT pin is the internal feedback to the PLL, its relative loading can adjust the input-output delay. This is shown in the above graph.


For applications requiring zero input-output delay, all outputs, including CLKOUT, must be equally loaded. Even if CLKOUT is not used, it must have a capacitive load equal to that on other outputs, to obtain zero input-output delay. If input to output delay adjustments are required, use the above graph to calculate loading differences between the CLKOUT pin and other outputs.

For zero output-output skew, be sure to load all outputs equally. For further information refer to the application note titled AN1234

Spread Aware

Many systems being designed now use a technology called Spread Spectrum Frequency Timing Generation. Cypress is one of the pioneers of SSFTG development and designed this product so as not to filter off the Spread Spectrum feature of the Reference input, assuming it exists. When a zero delay buffer is not designed to pass the SS feature through, the result is a significant amount of tracking skew, which may cause problems in systems requiring synchronization.

For more details on Spread Spectrum timing technology, please see the Cypress Whitepaper EMI and Spread Spectrum Technology.



Note

Document Number: 38-07296 Rev. *I Page 4 of 13

^{4.} This output is driven and has an internal feedback for the PLL. The load on this output can be adjusted to change the skew between the reference and output.



Maximum Ratings

Supply voltage to ground potential0.5 V to +7.0 V	Maximum soldering temperature (10 seconds) 260 °C
DC input voltage (Except REF)0.5 V to V _{DD} + 0.5 V	Junction temperature
DC input voltage REF0.5 V to 7 V	Static discharge voltage
Storage temperature65 °C to +150 °C	(per MIL-STD-883, Method 3015)> 2,000 V

Operating Conditions for CY23S05SXX-XX and CY23S09SXX-XX (Industrial, Commercial Devices)^[5]

Parameter	Description	Min	Max	Unit
V_{DD}	Supply voltage	3.0	3.6	V
T _A	Operating temperature - Ambient (Commercial)	0	70	°C
	Operating temperature - Ambient (Industrial)	-40	85	°C
C _L	Load capacitance, below 100 MHz		30	pF
C _L	Load capacitance, from 100 MHz to 133 MHz		10	pF
C _{IN}	Input capacitance		7	pF

Electrical Characteristics for CY23S05SXX-XX and CY23S09SXX-XX (Industrial, Commercial Devices)

Parameter	Description	Test Conditions	Min	Max	Unit
V _{IL}	Input LOW voltage ^[6]			0.8	V
V _{IH}	Input HIGH voltage ^[6]		2.0		V
I _{IL}	Input LOW current	V _{IN} = 0 V		50.0	μΑ
I _{IH}	Input HIGH current	$V_{IN} = V_{DD}$		100.0	μΑ
V _{OL}	Output LOW voltage ^[7]	I _{OL} = 8 mA (-1) I _{OH =} 12 mA (-1H)		0.4	V
V _{OH}	Output HIGH voltage ^[7]	$I_{OH} = -8 \text{ mA } (-1)$ $I_{OL} = -12 \text{ mA } (-1\text{H})$	2.4		V
I _{DD} (PD mode)	Power-down supply current	REF = 0 MHz		12.0	μΑ
I _{DD}	Supply current	Unloaded outputs at 66.67 MHz, SEL inputs at V _{DD}		32.0	mA

Switching Characteristics for CY23S05SXC-1 and CY23S09SXC-1 Commercial Temperature Devices [8]

•					=	
Parameter	Description	Test Conditions	Min	Тур	Max	Unit
t1	Output frequency	30 pF load 10 pF load	10 10		100 133.33	MHz MHz
	Duty cycle ^[7] = $t_2 \div t_1$	Measured at 1.4 V, F _{out} = 66.67 MHz	40.0	50.0	60.0	%
t3	Rise time ^[7]	Measured between 0.8 V and 2.0 V			2.50	ns
t ₄	Fall time ^[7]	Measured between 0.8 V and 2.0 V			2.50	ns
t ₅	Output-to-output skew ^[7]	All outputs equally loaded			250	ps
t ₆	Delay, REF Rising Edge to CLKOUT Rising Edge ^[7]	Measured at V _{DD} /2		0	±350	ps
t ₇	Device-to-device skew ^[7]	Measured at V _{DD} /2 on the CLKOUT pins		0	700	ps
t _J	Cycle-to-cycle jitter[7]	Measured at 66.67 MHz, loaded outputs			200	ps
t _{LOCK}	PLL lock time ^[7]	Stable power supply, valid clock presented on REF pin			1.0	ms

Notes

- 5. Multiple Supplies: The voltage on any input or I/O pin cannot exceed the power pin during power up. Power supply sequencing is NOT required.
- 6. REF input has a threshold voltage of V_{DD}/2.
- 7. Parameter is guaranteed by design and characterization. Not 100% tested in production.
- 8. All parameters specified with loaded outputs.



Switching Characteristics for CY23S05SXI-1H Industrial Temperature Devices^[8]

Parameter	Description	Test Conditions	Min	Тур	Max	Unit
t1	Output frequency	30 pF load 10 pF load	10 10		100 133.33	MHz MHz
	Duty cycle ^[7] = $t_2 \div t_1$	Measured at 1.4 V, F _{out} = 66.67 MHz	40.0	50.0	60.0	%
	Duty cycle ^[7] = $t_2 \div t_1$	Measured at 1.4 V, F _{out} <50.0 MHz	45.0	50.0	55.0	%
t3	Rise time ^[7]	Measured between 0.8 V and 2.0 V			1.50	ns
t ₄	Fall time ^[7]	Measured between 0.8 V and 2.0 V			1.50	ns
t ₅	Output-to-output skew ^[7]	All outputs equally loaded			250	ps
t ₆	Delay, REF Rising Edge to CLKOUT Rising Edge ^[7]	Measured at V _{DD} /2		0	±350	ps
t ₇	Device-to-Device Skew ^[7]	Measured at V _{DD} /2 on the CLKOUT pins of devices		0	700	ps
t ₈	Output slew rate ^[7]	Measured between 0.8 V and 2.0 V using Test Circuit #2	1			V/ns
tJ	Cycle-to-cycle jitter ^[7]	Measured at 66.67 MHz, loaded outputs			200	ps
t _{LOCK}	PLL lock time ^[7]	Stable power supply, valid clock presented on REF pin			1.0	ms

Switching Waveforms

Figure 4. Duty Cycle Timing





Figure 5. All Outputs Rise/Fall Time








Figure 7. Input-Output Propagation Delay






Switching Waveforms continued

Figure 8. Device-Device Skew



Test Circuits



For parameter t8 (output slew rate) on -1H devices

Thermal Resistance

Parameter ^[9]	Description	Test Conditions	8-pin SOIC	16-pin SOIC	16-pin TSSOP	Unit
Theta J _A	Thermal resistance (junction to ambient)	Test conditions follow standard test methods and procedures for	132	108	108	°C/W
Theta J _C		measuring thermal impedance, in accordance with EIA/JESD51.	43	37	17	°C/W

Note


^{9.} These parameters are guaranteed by design and are not tested.



Ordering Information

Ordering Code	Package Name	Package Type	Operating Range
Pb-Free	-		<u> </u>
CY23S05SXC-1	SZ08	8-pin 150-mil SOIC	Commercial (0 ° to 70 °C)
CY23S05SXC-1T	SZ08	8-pin 150-mil SOIC - Tape and Reel	Commercial (0 ° to 70 °C)
CY23S05SXC-1H	SZ08	8-pin 150-mil SOIC	Commercial (0 ° to 70 °C)
CY23S05SXC-1HT	SZ08	8-pin 150-mil SOIC - Tape and Reel	Commercial (0 ° to 70 °C)
CY23S05SXI-1	SZ08	8-pin 150-mil SOIC	Industrial (-40 ° to 85 °C)
CY23S05SXI-1T	SZ08	8-pin 150-mil SOIC - Tape and Reel	Industrial (-40 ° to 85 °C)
CY23S09SXC-1	SZ16	16-pin 150-mil SOIC	Commercial (0 ° to 70 °C)
CY23S09SXC-1T	SZ16	16-pin 150-mil SOIC – Tape and Reel	Commercial (0 ° to 70 °C)
CY23S09SXC-1H	SZ16	16-pin 150-mil SOIC	Commercial (0 ° to 70 °C)
CY23S09SXC-HT	SZ16	16-pin 150-mil SOIC – Tape and Reel	Commercial (0 ° to 70 °C)
CY23S09ZXC-1H	ZZ16	16-pin 4.4 mm TSSOP	Commercial (0 ° to 70 °C)
CY23S09ZXC-1HT	ZZ16	16-pin 4.4 mm TSSOP – Tape and Reel	Commercial (0 ° to 70 °C)

Ordering Code Definitions







Package Diagrams

Figure 9. 8-Pin (150-Mil) SOIC S08 and SZ08

- 1. DIMENSIONS IN INCHES[MM] MIN.
- PIN 1 ID IS OPTIONAL,
 ROUND ON SINGLE LEADFRAME
 RECTANGULAR ON MATRIX LEADFRAI
- 3. REFERENCE JEDEC MS-012
- 4. PACKAGE WEIGHT 0.07gms









Package Diagrams continued

Figure 10. 16-Pin (150-Mil) SOIC S16 and SZ16





Figure 11. 16-Pin TSSOP 4.40 mm Body Z16 and ZZ16





Acronym

Acronym	Description		
CMOS	complementary metal oxide semiconductor		
EMI	electromagnetic interference		
PLL	phase-locked loop		
SOIC	small outline integrated circuit		
SS	spread spectrum		
SSFTG	TG spread spectrum frequency timing generator		
SSOP	P shrunk small outline package		
TSSOP	SSOP thin shrunk small outline package		

Document Conventions

Units of Measure

Symbol	Unit of Measure			
°C	degree Celsius			
MHZ	megahertz			
uA	microamperes			
mA	milliamperes			
ms	milliseconds			
ns	nanoseconds			
%	percent			
pF	picofarads			
ps	picoseconds			
V	volt			



Document History Page

Rev.	ECN No.	Submission	Orig. of	Description of Change
**		Date	Change	·
	111147	11/14/01	DSG	Changed from spec number 38-01094 to 38-07296
*A	111773	02/20/02	CTK	Added 150-mil SSOP option
*B	122885	12/22/02	RBI	Added power-up requirements to Operating Conditions
*C	267849	See ECN	RGL	Added Lead-Free devices
*D	2595524	10/23/08	CXQ/PYRS	5
*E	2761988	09/10/09	KVM	Removed obsolete parts from Ordering Information table: CY23S09ZC-CY23S09OC-1, CY23S09OC-1H, CY23S09ZXC-1, CY23S09OXC-1, CY23S09OXC-1H. Added CY23S05SXC-1T, CY23S05SXC-1HT, CY23S09SXC-1T, CY23S09SXC-1HT, CY23S09ZXC-1HT. Removed Status column from Ordering Information table; added footnot Updated package names and added numerical temperature range to Ordering Information table. Removed QSOP package drawing.
*F	2897373	03/22/10	CXQ	Removed part numbers CY23S05SC-1, CY23S05SC-1H, CY23S09SC-CY23S09SC-1H, and CY23S09ZC-1H from Ordering Information table. Added CY23S05SXI-1 and CY23S05SXI-1T to Ordering Information table. Updated package diagrams. Updated copyright section.
*G	3394655	10/04/11	PURU	Added Figure 3 Updated Hyper links Updated Package Diagrams Added Ordering Code Definitions, Acronym, and Units of Measure.
*H	4564025	11/07/2014	TAVA	Removed the SSOP package in Features. Updated Figure 1 (removed SSOP). Updated Figure 7. Replaced all occurrences of SC and SI with SXC and SXI in the followin tables: Operating Conditions for CY23S05SXX-XX and CY23S09SXX-XX (Industrial, Commercial Devices) ^[5] Electrical Characteristics for CY23S05SXX-XX and CY23S09SXX-XX (Industrial, Commercial Devices) Switching Characteristics for CY23S05SXC-1 and CY23S09SXC-1 Commercial Temperature Devices [8] Switching Characteristics for CY23S05SXI-1H Industrial Temperature Devices [8] Updated the table, Operating Conditions for CY23S05SXX-XX and CY23S09SXX-XX (Industrial, Commercial Devices) ^[5] . Removed CY23S09SI-1H in the table title, in Switching Characteristics for CY23S05SXI-1H Industrial Temperature Devices ^[8] . Updated Figure 9, Figure 10, and Figure 11 in Package Diagrams.
*	5738816	05/24/2017	PSR	Updated the link for AN1234. Added Thermal Resistance. Updated the Cypress logo, copyright information, Sales, Solutions, and Le Information based on the new template.



Sales, Solutions, and Legal Information

Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at Cypress Locations.

Products

ARM® Cortex® Microcontrollers cypress.com/arm Automotive cypress.com/automotive Clocks & Buffers cypress.com/clocks Interface cypress.com/interface Internet of Things cypress.com/iot Memory cypress.com/memory Microcontrollers cypress.com/mcu **PSoC** cypress.com/psoc

Power Management ICs cypress.com/pmic
Touch Sensing cypress.com/touch
USB Controllers cypress.com/usb
Wireless Connectivity cypress.com/wireless

PSoC® Solutions

PSoC 1 | PSoC 3 | PSoC 4 | PSoC 5LP | PSoC 6

Cypress Developer Community

Forums | WICED IOT Forums | Projects | Video | Blogs | Training | Components

Technical Support

cypress.com/support

© Cypress Semiconductor Corporation, 2001-2017. This document is the property of Cypress Semiconductor Corporation and its subsidiaries, including Spansion LLC ("Cypress"). This document, including any software or firmware included or referenced in this document ("Software"), is owned by Cypress under the intellectual property laws and treaties of the United States and other countries worldwide. Cypress reserves all rights under such laws and treaties and does not, except as specifically stated in this paragraph, grant any license under its patents, copyrights, trademarks, or other intellectual property rights. If the Software is not accompanied by a license agreement and you do not otherwise have a written agreement with Cypress governing the use of the Software, then Cypress hereby grants you a personal, non-exclusive, nontransferable license (without the right to sublicense) (1) under its copyright rights in the Software (a) for Software provided in source code form, to modify and reproduce the Software solely for use with Cypress hardware products, only internally within your organization, and (b) to distribute the Software in binary code form externally to end users (either directly or indirectly through resellers and distributors), solely for use on Cypress hardware product units, and (2) under those claims of Cypress's patents that are infringed by the Software (as provided by Cypress, unmodified) to make, use, distribute, and import the Software solely for use with Cypress hardware products. Any other use, reproduction, modification, translation, or compilation of the Software is prohibited.

TO THE EXTENT PERMITTED BY APPLICABLE LAW, CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS DOCUMENT OR ANY SOFTWARE OR ACCOMPANYING HARDWARE, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. To the extent permitted by applicable law, Cypress reserves the right to make changes to this document without further notice. Cypress does not assume any liability arising out of the application or use of any product or circuit described in this document. Any information provided in this document, including any sample design information or programming code, is provided only for reference purposes. It is the responsibility of the user of this document to properly design, program, and test the functionality and safety of any application made of this information and any resulting product. Cypress products are not designed, intended, or authorized for use as critical components in systems designed or intended for the operation of weapons, weapons systems, nuclear installations, life-support devices or systems, other medical devices or systems (including resuscitation equipment and surgical implants), pollution control or hazardous substances management, or other uses where the failure of the device or system could cause personal injury, death, or property damage ("Unintended Uses"). A critical component is any component of a device or system whose failure to perform can be reasonably expected to cause the failure of the device or system, or to affect its safety or effectiveness. Cypress is not liable, in whole or in part, and you shall and hereby do release Cypress from any claim, damage, or other liability arising from or related to all Unintended Uses of Cypress products. You shall indemnify and hold Cypress harmless from and against all claims, costs, damages, and other liabilities, including claims for personal injury or death, arising from or related to any Unintended Uses of Cypress products.

Cypress, the Cypress logo, Spansion, the Spansion logo, and combinations thereof, WICED, PSoC, CapSense, EZ-USB, F-RAM, and Traveo are trademarks or registered trademarks of Cypress in the United States and other countries. For a more complete list of Cypress trademarks, visit cypress.com. Other names and brands may be claimed as property of their respective owners

Document Number: 38-07296 Rev. *I Revised May 24, 2017 Page 13 of 13