Product datasheet Characteristics

ABL6TS02J

voltage transformer - 230..400 V - 1 x 12 V - 25 VA



Price* : 60.00 GBP



Main

		4
Range of product	Phaseo Optimum	
Product or component type	Safety and isolation transformer	
Rated power in VA	25 VA	
Input voltage	230 V AC single phase, terminal(s): N-L1 400 V AC phase to phase, terminal(s): L1-L2	o Vilindei
Output voltage	12 V AC	<u> </u>
Secondary winding	Single	
Protective cover	Without	- c
Ambient air temperature for operation	-2050 °C	

Complementary

Complementary	
Input voltage limits	360440 V 207253 V
Network frequency limits	4763 Hz
Input voltage tolerance	+/- 15 V
Efficiency	79 %
Power dissipation in W	6.6 W
Output sustained overvoltage	16 % (no load, hot state)
Maximum voltage drop at rated load	0.6 %
No load losses	3 W
Short-circuit voltage	0,1474
Output protection type	Against overload, protection technology: external Against overvoltage, protection technology: external Against short-circuits, protection technology: external
Connections - terminals	For input connection: screw type terminals, connection capacity: 5 x 4 mm² AWG 11 For input ground connection: screw type terminals, connection capacity: 1 x 4 mm² AWG 11 For output connection: screw type terminals, connection capacity: 2 x 4 mm² AWG 11
Marking	CE

Fixing mode	By 4 screws diameter: 4.8 mm on vertical panel, operating position: horizontal By 4 screws diameter: 4.8 mm on vertical panel, operating position: vertical By clips (with mounting plate) on 35 mm symmetrical DIN rail By 4 screws diameter: 4.8 mm on horizontal panel with derating to 90 %
Operating altitude	3000 m
Electrical insulation class	Class B
Width	66 mm
Height	90 mm
Depth	55 mm
Net weight	0.7 kg

Environment

Product certifications	EAC
	UR
Standards	UL 506
IP degree of protection	IP20
Environmental characteristic	EMC conforming to EN 62041 Safety conforming to EN 61558-1 Safety conforming to EN 61558-2-6
Protective treatment	TC
Ambient air temperature for storage	-4080 °C
Overvoltage category	Class I conforming to VDE 0106-1
Dielectric strength	2000 V between winding and ground 4000 V between primary and secondary

Offer Sustainability


Sustainable offer status	Green Premium product	
REACh Regulation	REACh Declaration	
EU RoHS Directive Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration		
Mercury free	Yes	
RoHS exemption information	Yes	
China RoHS Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	No need of specific recycling operations End of Life Information	

Contractual warranty

Contractad warranty		
Warranty	18 months	

ABL6TS02J

Dimensions



Dimensions in mm

а	b	С	G	J	Ø
66	81	64	50	42	4.8


Dimensions in in.

а	b	С	G	J	Ø
2.60	3.19	2.52	1.97	1.65	0.19

Product datasheet Connections and Schema

ABL6TS02J


Internal Scheme




Product datasheet Connections and Schema

ABL6TS02J

Primary Voltage Wiring





Product datasheet Connections and Schema

ABL6TS02J

Secondary Voltage Wiring

