Shock-Safe Fuseholder, 5 x 20 mm, Slotted Cap/Fingergrip, Snap-in, 0.75 - 3.0 mm





Slotted cap fingergrip

250 VAC · 3.2 W / 10 A (VDE) 10 A (UL/CSA)

See below:

Approvals and Compliances

Description

- Panel Thickness 0.75 - 3.0 mm, Snap-in

pdf data sheet, html datasheet, General Product Information, Distributor-Stock-Check, Detailed request for product, Microsite

PC2
5 x 20 mm
Panel mount, Front Side
Snap-in
Solder
250 VAC
10A (VDE), 10A (UL/CSA)
3.2W / 10A @ Ta 23°C
Admissible power acceptance at higher
ambient temperature see derating cur-
ves
IP40
-40 °C to 85 °C
40/085/21 acc. to IEC 60068-1
Thermoplastic, black, UL 94V-0
Thermoplastic, black, UL 94V-0
Copper alloy, tin-plated
6.45 g
0°C to 60°C, max. 70% r.h.
■, Type, Certification marks

Soldering Methods	Iron
	Soldering Profile
Solderability	350°C / 3 sec acc. to IEC 60068-2-20,
	Test Ta, method 2
Resistance to Soldering Heat	350°C / 10 sec acc. to IEC 60068-2-20,
	Test Tb, method 2
Contact Resistance	≤ 10 mΩ at 100 mA acc. to IEC
	60127-6
Dielectric Strength	> 3 kV between life parts
	(50 Hz: 1 min)
Impulse Withstand Voltage	> 4 kV between life parts
Insulation Resistance	≥ 10 MΩ between life parts
	(500 VDC: 1 min)
Overvoltage Category	III acc. to IEC 60664-1
Pollution Degree	2 acc. to IEC 60664-1
Panel Thickness	0.75 - 3.0 mm

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: FEF

Approval Logo	Certificates	Certification Body	Description
VDE	VDE Approvals	VDE	VDE Certificate Number: 40046093
c FL °us	UL Approvals	UL	UL File Number: E39328

Product standards

Product standards that are referenced

Organiz	zation	Design	Standard	Description
<u>IEC</u>		Designed according to	IEC 60127-6	Miniature fuses. Part 6. Fuse-holders for miniature fuse-links
(JL)		Designed according to	UL 4248-1	Fuseholder general requirements
(SE) CS	A	Designed according to	CSA C22.2 no. 4248.1	Fuseholder general requirements

Application standards

Application standards where the product can be used

	•		
Organization	Design	Standard	Description
<u>IEC</u>	Designed for applications acc.	IEC/UL 62368-1	IEC 62368-1 includes the basic requirements for safety of audio, video, information technology and office equipment.
<u>IEC</u>	Designed for applications acc.	IEC 60335-1	Safety of electrical appliances for household and similar purposes. Meets the requirements for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-11 or -12 & -13.


Compliances

The product complies with following Guide Lines


	O .		
Identification	Details	Initiator	Description
C€	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
RoHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
©	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.
00	White Paper Glow wire test	SCHURTER AG	Meets the requirements of IEC 60335-1 for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-11 or -12 &-13.


d 33 mm


Dimension [mm]




Variant 0031.1091 und 0031.1095







Variant Fingergrip 0031.1901 and 0031.1902




42.5

Variant Fingergrip 0031.1913 and 0031.1914








Mounting Holes. For 0031.1161 / 0031.1165 / 0031.1913 / 0031.1914

Mounting Holes. For 0031.1091 / 0031.1095 / 0031.1901 / 0031.1902

Derating Curves



Ambient Air Temperature Ta °C

All Variants

Holder	Сар	Panel Thickness s [mm]	Terminal	Cut shape	Degree of Protection	Order Number	
1	slotted	0.75 - 1.5mm	Solder	1)	IP40	0031.1091	
1	slotted	1.8 - 3.0mm	Solder	1)	IP40	0031.1095	
1	Fingergrip	0.75 - 1.5mm	Solder	1)	IP40	0031.1901	
1	Fingergrip	1.8 - 3.0mm	Solder	1)	IP40	0031.1902	
1	slotted	0.75 - 1.5mm	Solder	2)	IP40	0031.1161	
1	slotted	1.8 - 3.0mm	Solder	2)	IP40	0031.1165	
1	Fingergrip	0.75 - 1.5mm	Solder	2)	IP40	0031.1913	
1	Fingergrip	1.8 - 3.0mm	Solder	2)	IP40	0031.1914	

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

- 1) With Notch
- 2) With D-Form

Quick-Connect Terminals on Request

Packaging Unit

Bulk (100 pcs.)