

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	WIRE RANGE		COLOR (DIN)	WIRE STRIP LENGTH +1/32 -0 [+0.8 -0]	MAX. WIRE INSUL. DIA.	WIRE CLASS	DIMENSIONS in. [mm]					INSTALLATION TOOLS	PANDUIT PART #	WIRE RANGE		COLOR (DIN)	WIRE STRIP LENGTH +1/32 -0 [+0.8 -0]	MAX. WIRE INSUL. DIA.	WIRE CLASS	DIMENSIONS in. [mm]					INSTALLATION TOOLS/DIES	
	AWG	[mm ²]					L	P	ID	S1	S2			AWG	[mm ²]					L	P	ID	S1	S2		
* FSD72-6	26	[0,14]	GRAY	3/8 [9,5]	0.07 [2,0]	B, K, M	.41 [10,5]	.24 [6,0]	0.03 [0,8]	[0.15]	[0.25]	CT-1002 CT-1123	FSD79-8	14	[2,08]	YELLOW	15/32 [11,9]	0.14 [3,6]	G, K, M	0.57 [14,5]	0.31 [8,0]	0.08 [2,1]	[0.15]	[0,30]	CT-1002 CT-1003 CT-1123	
* FSD72-8				15/32 [11,9]	0.07 [2,0]		.49 [12,5]	.31 [8,0]	0.03 [0,8]	[0.15]	[0.25]		FSD80-8	14	[2,50]	BLUE	15/32 [11,9]	0.17 [4,2]	G, K, M	0.59 [15,0]	0.31 [8,0]	0.09 [2,3]	[0.15]	[0,30]		
* FSD73-6	24	[0,25]		3/8 [9,5]	0.07 [2,0]		.41 [10,5]	.24 [6,0]	0.03 [0,8]	[0.15]	[0.25]		FSD80-12				5/8 [15,9]	0.17 [4,2]		0.75 [19,0]	0.47 [12,0]	0.09 [2,3]	[0.15]	[0,30]		
* FSD73-8				15/32 [11,9]	0.07 [2,0]		.49 [12,5]	.31 [8,0]	0.03 [0,8]	[0.15]	[0.25]		FSD80-18				7/8 [22,2]	0.17 [4,2]		0.98 [25,0]	0.71 [18,0]	0.09 [2,3]	[0.15]	[0,30]		
* FSD74-6	24-22	[0,34]	TURQUOISE	3/8 [9,5]	0.07 [2,0]		.41 [10,5]	.24 [6,0]	0.03 [0,8]	[0.15]	[0.25]		FSD81-10	12	[4,00]	GRAY	17/32 [13,5]	0.19 [4,8]	G, K, M	0.69 [17,5]	0.39 [10,0]	0.11 [2,9]	[0.20]	[0,30]		
* FSD74-8				15/32 [11,9]	0.07 [2,0]		.49 [12,5]	.31 [8,0]	0.03 [0,8]	[0.15]	[0.25]		FSD81-12				5/8 [15,9]	0.19 [4,8]		0.79 [20,0]	0.47 [12,0]	0.11 [2,9]	[0.20]	[0,30]		
+ FSD75-6	22-20	[0,50]		3/8 [9,5]	0.09 [2,5]	B, K, M	.45 [11,5]	.24 [6,0]	0.04 [1,1]	[0.15]	[0.25]		FSD81-18				7/8 [22,2]	0.19 [4,8]		1.02 [26,0]	0.71 [18,0]	0.11 [2,9]	[0.20]	[0,30]		
+ FSD75-8				15/32 [11,9]	0.09 [2,5]		.53 [13,5]	.31 [8,0]	0.04 [1,1]	[0.15]	[0.25]		FSD82-12	10	[6,00]	YELLOW	5/8 [15,9]	0.24 [6,2]	G, I, K, M	0.79 [20,0]	0.47 [12,0]	0.14 [3,6]	[0.20]	[0,30]	CT-1002 ++CT-1003 CT-1123	
+ FSD75-10				17/32 [13,5]	0.09 [2,5]		.61 [15,5]	.39 [10,0]	0.04 [1,1]	[0.15]	[0.25]		FSD82-18				7/8 [22,2]	0.24 [6,2]		1.02 [26,0]	0.71 [18,0]	0.14 [3,6]	[0.20]	[0,30]		
FSD76-6	18	[0,75]	GRAY	3/8 [9,5]	0.11 [2,8]		.47 [12,0]	.24 [6,0]	0.05 [1,3]	[0.15]	[0.25]	CT-1002 CT-1003 CT-1123	FSD83-12	8	[10,0]	RED	5/8 [15,9]	0.30 [7,5]	G, H, I, K, M	0.83 [21,0]	0.47 [12,0]	0.18 [4,6]	[0.20]	[0,30]	++CT-1003 ++CT-1004 CT-1104 CT-1123	
FSD76-8				15/32 [11,9]	0.11 [2,8]		.55 [14,0]	.31 [8,0]	0.05 [1,3]	[0.15]	[0.25]		FSD83-18				7/8 [22,2]	0.30 [7,5]		1.06 [27,0]	0.71 [18,0]	0.18 [4,6]	[0.20]	[0,30]		
FSD76-10				17/32 [13,5]	0.11 [2,8]		.63 [16,0]	.39 [10,0]	0.05 [1,3]	[0.15]	[0.25]		FSD84-12	6	[16,0]	BLUE	5/8 [15,9]	0.35 [8,8]	G, H, I, K, M	0.91 [23,0]	0.47 [12,0]	0.24 [6,0]	[0.20]	[0,40]	++CT-1004 CT-1104	
FSD76-12				5/8 [15,9]	0.11 [2,8]		.71 [18,0]	.47 [12,0]	0.05 [1,3]	[0.15]	[0.25]		FSD84-18				7/8 [22,2]	0.35 [8,8]		1.14 [29,0]	0.71 [18,0]	0.24 [6,0]	[0.20]	[0,40]		
FSD77-6	-	[1,00]	RED	3/8 [9,5]	0.12 [3,0]	B, K, M	.49 [12,5]	.24 [6,0]	0.06 [1,5]	[0.15]	[0.30]	CT-1002 CT-1003 CT-1123	FSD85-16	4	[25,0]	YELLOW	3/4 [19,1]	0.43 [11,0]	G, H, I, K, M	1.14 [29,0]	0.63 [16,0]	0.30 [7,5]	[0.20]	[0,50]	CT-1005	
FSD77-8				15/32 [11,9]	0.12 [3,0]		.57 [14,5]	.31 [8,0]	0.06 [1,5]	[0.15]	[0.30]		FSD85-18				7/8 [22,2]	0.43 [11,0]		1.22 [31,0]	0.71 [18,0]	0.30 [7,5]	[0.20]	[0,50]		
FSD77-10				17/32 [13,5]	0.12 [3,0]		.65 [16,5]	.39 [10,0]	0.06 [1,5]	[0.15]	[0.30]		FSD85-22				1 [25,4]	0.43 [11,0]		1.38 [35,0]	0.87 [22,0]	0.30 [7,5]	[0.20]	[0,50]		
FSD77-12				5/8 [15,9]	0.12 [3,0]		.73 [18,5]	.47 [12,0]	0.06 [1,5]	[0.15]	[0.30]		FSD86-16	2	[35,0]	RED	3/4 [19,1]	0.49 [12,5]	G, H, I, K, M	1.18 [30,0]	0.63 [16,0]	0.33 [8,5]	[0.20]	[0,50]		
FSD78-6	16	[1,50]	BLACK	3/8 [9,5]	0.12 [3,0]		.49 [12,5]	.24 [6,0]	0.07 [1,8]	[0.15]	[0.30]		FSD86-18				7/8 [22,2]	0.49 [12,5]		1.26 [32,0]	0.71 [18,0]	0.33 [8,5]	[0.20]	[0,50]		
FSD78-8				15/32 [11,9]	0.12 [3,0]		.57 [14,5]	.31 [8,0]	0.07 [1,8]	[0.15]	[0.30]		FSD86-25	1-1/0	[50,0]	BLUE	1 1/8 [28,6]	0.49 [12,5]	G, H, DLO, I, K, M	1.26 [39,0]	0.98 [25,0]	0.33 [8,5]	[0.20]	[0,50]		
FSD78-10				17/32 [13,5]	0.12 [3,0]		.65 [16,5]	.39 [10,0]	0.07 [1,8]	[0.15]	[0.30]		FSD87-20				15/16 [23,8]	0.59 [15,0]		1.42 [36,0]	0.79 [20,0]	0.41 [10,5]	[0.30]	[0,60]	CT-1006 **CD-2001-F87	
FSD78-12				5/8 [15,9]	0.12 [3,0]		.73 [18,5]	.47 [12,0]	0.07 [1,8]	[0.15]	[0.30]		FSD87-25				1 1/8 [28,6]	0.59 [15,0]</								