



# Disconnect Terminals

DKT 4



Lever & Feed Through

DKT 4 V



Dual Level

## Terminal Block Selection Data

Available Options	Version	DKT 4		DKT 4 V	
With 2 StB test points KrS PA Beige PA					
		<b>0327860000</b>	<b>0327960000</b>	<b>1304860000</b>	<b>1304960000</b>
		<b>0687360000</b>	<b>0687460000</b>		

## Dimensions

Width / Length / Height mm (in.)	for TS 32	6/65/70 (.23/2.56/2.76)	6/65/56.5/70 (.23/2.56/2.76)
	for TS 35	6/65/70 (.23/2.56/2.76)	6/65/56.5/70 (.23/2.56/2.76)
Insulation stripping length	mm (in.)	9 (.35)	9 (.35)

## Technical Data

Rated voltage / rated current / wire size	UL	300 V / 10 A / #22...12 AWG	300 V / 10 A / #22...12 AWG
	CSA	300 V / 10 A / #26...12 AWG	300 V / 10 A / #26...12 AWG
	VDE	380 VAC / 10 A / 4 mm <sup>2</sup>	380 VAC / 10 A / 4 mm <sup>2</sup>
Torque	Nm (lb. in.)	0.6 / 0.5 StB (8.0 / 4.5 StB)	0.6 / 0.5 StB (8.0 / 4.5 StB)
Clamping screw	M	3	3

## Selected Accessory Data<sup>‡</sup>

End Plate (thickness mm)	Type	Part No.	Type	Part No.
Beige PA	AP (1.5)	<b>0687560000</b>	AP (1.5)	<b>0687560000</b>
Blue PA				
KrG				
KrS				

## Partition (thickness mm)

PA				
KrG				
KrS				
HP	TW (2.0)	<b>0607000000</b>	TW (2.0)	<b>0607000000</b>

## Jumpers



Final number indicates number of poles. See the Accessories Section for more information. When using QB, maximum conductor connection is 2.5 mm<sup>2</sup>.

Connection sleeve	QB 2	<b>0482700000</b>	QB 2	<b>0482700000</b>
Fixing screw	QB 3	<b>0482800000</b>	QB 3	<b>0482800000</b>
Lock washer	QB 4	<b>0482900000</b>	QB 4	<b>0482900000</b>
Insulation sleeve	QB 75 bare*	<b>0526400000</b>	QB 75 bare*	<b>0526400000</b>
	IP 75	<b>0526700000</b>	IP 75	<b>0526700000</b>

## Plugs

Lock-out device	WTR/SAKR	<b>9525900000</b>		
Test plug	PS 2.3	<b>0180400000</b>	PS 2.3	<b>0180400000</b>
Socket				
Diode plug without diode				
Diode plug with diode 1N4007				
Disconnecter plug (spare)				

## Marking Tags

	Print	DKT 4	DKT 4 V
Note: Part numbers are shown for a single card of pre-printed tags numbered 1-50.	Consecutive horizontal	DEK 5/6 <b>0468660001</b>	DEK 5/6 <b>0468660001</b>
	Consecutive vertical	DEK 5/6 <b>0468760001</b>	DEK 5/6 <b>0468760001</b>

<sup>‡</sup>See Accessories section for additional information.  
\*Without DLS