SDS1000 Series Oscilloscopes Technical Specifications

Unless otherwise specified, the technical specifications applied are for the oscilloscope only, and Probes attenuation set as 10X. Only if the oscilloscope fulfills the following two conditions at first, these specification standards can be reached.

- This instrument should run for at least 30 minutes continuously under the specified operating temperature.
- If change of the operating temperature is up to or exceeds 5° C, do a "Self-calibration" procedure.

All specification standards can be fulfilled, except one(s) marked with the word "Typical".

Performance Characteristics		Instruction		
5 1		SDS1022	20 MHz	
		SDS1052	50 MHz	
	Bandwidth	SDS1102	100 MHz	
		SDS1202	200 MHz	
	Channel	2 channels		
	Mode		Normal, Peak detect, Averaging	
		SDS1022	100 MS/s	
Acquisition	Sample rate	SDS1052	500 MS/s	
	(real time)	SDS1102	1.65/2	
		SDS1202	1 GS/s	
	Input coupling	DC, AC, Ground		
	Input impedance	1 MΩ±2%, in parallel with 20 pF±5 pF		
	Input coupling	1X, 10X, 100X, 1000X		
	Max. input voltage	400V (DC+AC, PK - PK)		
	Channel –channel	50Hz: 100:1		
Input	isolation	10MHz: 40	: 1	
IIIput	Time delay between	150ps		
	channel(typical)			
		SDS1022	Not support	
	Bandwidth limit	SDS1052	Not support	
	Danawiatii iiiiit	SDS1102	20 MHz, full bandwidth	
		SDS1202	20 Willz, full balluwidti	
		SDS1022	0.5 S/s∼100 MS/s	
	Sampling rate range	SDS1052	0.5 S/s∼500 MS/s	
Horizontal	Sampling rate range	SDS1102	0.5 S/s∼1 GS/s	
		SDS1202	0.5 3/3 1 03/3	
System	Interpolation	(Sinx)/x		
	Max Record length	10K		
	Scanning speed (S/div)	SDS1022	5 ns/div – 1000 s/div, step by 1 – 2 - 5	

Performance Characteristics		Instruction	
		SDS1052	
		SDS1102	2 ns/div – 1000 s/div, step by 1 – 2 - 5
		SDS1202	step by 1 – 2 - 3
	Sampling rate / relay time accuracy	±100 ppm	
		Single:	
	Interval(△T) accuracy	±(1 interval t	ime+100 ppm×reading+0.6 ns);
	(DC - 100MHz)	Average>16:	
		±(1 interval t	ime +100 ppm×reading+0.4 ns)
	Vertical Resolution (A/D)	8 bits (2 char	nnels simultaneously)
	Sensitivity	5 mV/div \sim 5	V/div
		SDS1022	±2 V (5 mV/div – 100 mV/div) ±50 V (200 mV/div – 5 V/div)
	Displacement	SDS1052 SDS1102 SDS1202	±2 V (5 mV/div – 200 mV/div) ±50 V (500 mV/div – 5 V/div)
		SDS1202	20 MHz
		SDS1022	50 MHz
	Analog bandwidth	SDS1032	100 MHz
		SDS1102	200 MHz
Vertical system	Single bandwidth	Full bandwid	
	Low Frequency		put, AC coupling, -3 dB)
	Low rrequericy	SDS1022	≤ 17.5 ns
	Rise time (at input, Typical)	SDS1052	≤ 7.0 ns
		SDS1102	≤ 3.5 ns
		SDS1202	≤ 1.75 ns
	DC gain accuracy	±3%	
	DC accuracy (average)	Delta Volts between any two averages or ≥16 waveforms acquired with the same scope setup and ambient conditions (△V): ±(3% reading + 0.05 div)	
	Waveform inverted ON		
	Cursor	$\triangle V, \triangle T, \triangle T $	&△V between cursors,
	- Cu1301	auto cursor	
Measurement	Automatic	Period, Frequency, Mean, PK-PK, RMS, Max, Min, Top, Base, Amplitude, Overshoot, Preshoot, Rise Time, Fall Time, +PulseWidth, -PulseWidth, +Duty Cycle, -Duty Cycle, Delay A→B +, Delay A→B +, Cycle RMS, Cursor RMS, Screen Duty, Phase, +PulseCount, -PulseCount, RiseEdgeCnt, FallEdgeCnt, Area, and Cycle Area.	
	Waveform Math	+, -,*,/,FFT	
		16 waveforms	

Performance Characteristics		eristics	Instruction
	Lissajous figure	Bandwidth	Full bandwidth
		Phase difference	±3 degrees
Communication port	USB 2.0 (USB storage)		
Counter	Support		

Trigger:

Performance Characteristics		Instruction	
Trigger level range	Internal	±5 div from the screen center	
Trigger level	T . 1	10.2 d:	
Accuracy (typical)	Internal	±0.3 div	
Trigger	According to Record length and time base		
displacement			
Trigger Holdoff	100 ns – 10 s		
range	100 115 - 10 5		
50% level setting	Input signal frequency ≥ 50 Hz		
(typical)			
Edge trigger	slope	Rising, Falling	
	Modulation	Support standard NTSC, PAL and SECAM	
Video Trigger		broadcast systems	
	Line number range	1-525 (NTSC) and 1-625 (PAL/SECAM)	

General Technical Specifications

Display

Display Type	7" Colored LCD (Liquid Crystal Display)
Display Resolution	800 (Horizontal) × 480 (Vertical) Pixels
Display Colors	65536 colors, TFT screen

Output of the Probe Compensator

Output Voltage (Typical)	About 5 V, with the Peak-to-Peak voltage \geqslant 1 M Ω .
Frequency (Typical)	Square wave of 1 KHz

Power

Mains Voltage	100 - 240 VACRMS, 50/60 Hz, CAT II
Power Consumption	< 15 W
Fuse	2 A, T class, 250 V

Environment

Tomporaturo	Working temperature: 0 °C - 40 °C
Temperature	Storage temperature: -20 $^{\circ}{\mathbb C}$ - 60 $^{\circ}{\mathbb C}$
Relative Humidity	≤ 90%
lla:abt	Operating: 3,000 m
Height	Non-operating: 15,000 m
Cooling Method	Natural cooling

Mechanical Specifications

Dimension	301 mm× 152 mm×70 mm (L*H*W)
Weight	About 1.1 kg

Interval Period of Adjustment:

One year is recommended for the calibration interval period.

7007020100069

V1.1.1