




RAYCHEM

TE Internal #: 806697-000

Straight, Size 202, 25, 25, Adhesive Purchased Separately Adhesive Requirement, -75 – 150 °C [-103 – 302 °F], Heat Shrink Boots

[View on TE.com >](#)

Wire Protection & Management > Heat Shrink Shapes > Heat Shrink Boots > Heat Shrink Boots: Non Lipped, Straight



Body Orientation: **Straight**

Molded Part Shape Code: **202**

Lipped: **No**

Material Code: **25**

Material Systems Code: **25**

[All Heat Shrink Boots: Non Lipped, Straight \(137\)](#)

Features

Housing Features

| | |
|------------------|----------|
| Body Orientation | Straight |
|------------------|----------|

Other

| | |
|------------------------|-----------|
| Molded Part Shape Code | 202 |
| EU RoHS Compliance | Compliant |
| EU ELV Compliance | Compliant |

Configuration Features

| | |
|----------------------|-------------------------------|
| Lipped | No |
| Adhesive Requirement | Adhesive Purchased Separately |

Body Features

| | |
|--------------------------|------------------------------------|
| Material Code | 25 |
| Material Systems Code | 25 |
| Primary Product Material | Fluid Resistant Modified Elastomer |

Usage Conditions

| | |
|-----------------------------|---|
| Operating Temperature Range | -75 – 150 °C[-103 – 302 °F] |
| Resistance Protection | Long-Term Fluid Exposure at High Temperatures |

Dimensions

| | |
|--|--|
| | |
|--|--|



| | |
|---------------------------------|---|
| Compatible Cable Diameter (Max) | 8 mm, 9 mm, 10 mm, 11 mm, 12 mm [.39 in][.314 in][.43 in][.47 in][.35 in] |
| Compatible Cable Diameter Range | 6.6 – 20.3 mm [.26 – .8 in] |

Industry Standards

| | |
|---|--|
| Compatible With Approved Standards Products | DEF Std 59-97 Issue 3 Type DE, IEC 62329-3-102, MIS-34867, BS-G-198-5-DE |
|---|--|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC |
| Halogen Content | Out of Scope - excluded from Halogen requirements |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 657863-000
[S1125-KIT-8](#)

Customers Also Bought



TE Part #806702-000
Heat Shrink Boots: Non Lipped, Right Angle



TE Part #806699-000
Heat Shrink Boots: Non Lipped, Straight



TE Part #D83327-000
204W511-25-0



TE Part #5677834001
RNF-3000 Heat Shrink Tubing

Documents

Datasheets & Catalog Pages

[1654025_Sec4_-25](#)

English

Raychem Molded Parts Visual Guide

English

Product Specifications

[Product Specification](#)

English