

PRODUCT-DETAILS

# KFS20/W/10M

## PVCU STAND.WEIGHT NC20 10MT WHT




---

### General Information

Extended Product Type	KFS20/W/10M
Product ID	7TCA296090R0028
EAN	5020963053115
Catalog Description	PVCU STAND.WEIGHT NC20 10MT WHT
Long Description	Standard Weight Conduit, Nominal Conduit Size 20mm, NW Conduit Size 17, Fine Conduit Pitch, Outside Diameter 19.8mm, Inside Diameter 14.3mm, Static Bend Radius 30mm, Reel Length 10 Meters, PVCu, White

---

### Additional Information

Application	Indoors / Outdoors, General Purpose Applications
Product Type	Standard Weight Conduit with Fine Pitch

---

### Ordering

EAN	5020963053115
UPC	786210248196
Customs Tariff Number	3926909985

---

### Dimensions

Product Net Depth / Length	10 m
----------------------------	------

---

## Technical

---

Number of Batteries	0
Color	White
Material	PVCu

---



---

## Environmental

---

WEEE Category	Product Not in WEEE Scope
---------------	---------------------------

---



---

## Container Information

---

Package Level 1 Units	1 piece
Package Level 1 Height	3.93 in 100 mm
Package Level 1 Depth / Length	12.99 in 330 mm
Package Level 1 Width	12.99 in 330 mm

---



---

## Certificates and Declarations (Document Number)

---

Data Sheet, Technical Information	KFS20/W/10M
Instructions and Manuals	KFS20/W/10M
Declaration of Conformity - CE	9AKK107492A9618
RoHS Information	9AKK107992A8994
RoHS Date	9AKK107992A8994
REACH Declaration	9AKK107992A8994

---



---

## Classifications

---

ETIM 8	EC001175 - Corrugated plastic hose
UNSPSC	39131706

---



---

## Categories

---

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

