SFH 4043

CHIPLED®

CHIPLED® with High Power Infrared Emitter (940









Applications

- Gesture Recognition

Features:

- Package: clear epoxy

- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)

- Very small package: (LxWxH) 1.0 mm x 0.5 mm x 0.45 mm

Ordering Information

Туре	Radiant intensity ¹⁾ $I_{F} = 70 \text{ mA; } t_{p} = 20 \text{ ms}$ I_{e}	Radiant intensity ¹⁾ typ. $I_F = 70 \text{ mA}$; $t_p = 20 \text{ ms}$ I_e	Ordering Code
SFH 4043	2.5 8.0 mW/sr	6 mW/sr	Q65111A3691



Maximur	n Ratings
Maxilliui	II Nauliya

Τ.	=	25	$^{\circ}C$
			\sim

Parameter	Symbol		Values
Operating temperature	T _{op}	min.	-40 °C
	σр	max.	85 °C
Storage temperature	T _{stg}	min.	-40 °C
	3.9	max.	85 °C
Reverse voltage ²⁾	V_R	max.	12 V
Forward current	I _F	max.	70 mA
Surge current $t_p \le 700 \mu s; D = 0$	I _{FSM}	max.	0.7 A
Power consumption	P _{tot}	max.	140 mW
ESD withstand voltage acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)	V_{ESD}	max.	2 kV



Characteristics

 I_F = 70 mA; t_p = 20 ms; T_A = 25 °C

Parameter	Symbol	Values	
Peak wavelength	$\lambda_{\sf peak}$	typ.	950 nm
Centroid wavelength	$\lambda_{ ext{centroid}}$	typ.	940 nm
Spectral bandwidth at 50% $I_{rel,max}$ $I_{F} = 70 \text{ mA}$; $t_{p} = 10 \text{ ms}$	Δλ	typ.	42 nm
Half angle	φ	typ.	70 °
Dimensions of active chip area	LxW	typ.	0.2 x 0.2 mm x mm
Rise time (10% / 90%) $I_F = 70 \text{ mA}; R_L = 50 \Omega$	t _r	typ.	12 ns
Fall time (10% / 90%) $I_F = 70 \text{ mA}; R_L = 50 \Omega$	t _f	typ.	12 ns
Forward voltage	V_{F}	typ. max.	1.6 V 2 V
Forward voltage $I_F = 500 \text{ mA}$; $t_p = 100 \mu\text{s}$	V_{F}	typ.	2.4 V
Reverse current ²⁾ V _R = 5 V	I _R	max. typ.	10 μA 0.01 μA
Total radiant flux 3)	Фе	typ.	35 mW
Temperature coefficient of brightness $I_F = 70 \text{ mA}$; $t_p = 10 \text{ ms}$	TC _I	typ.	-0.5 % / K
Temperature coefficient of voltage $I_F = 70 \text{ mA}$; $t_p = 10 \text{ ms}$	TC _v	typ.	-1.3 mV / K
Temperature coefficient of wavelength $I_F = 70 \text{ mA}$; $t_p = 10 \text{ ms}$	$TC_{_{\lambda}}$	typ.	0.3 nm / K
Thermal resistance junction ambient real 4)	R_{thJA}	max.	450 K / W
Thermal resistance junction solder point real 5)	R_{thJS}	max.	350 K / W



Brightness Groups


T_A = 25 °C

Group	Radiant intensity $I_F = 70 \text{ mA}$; $t_D = 20 \text{ ms}$	Radiant intensity $I_F = 70 \text{ mA}$; $t_o = 20 \text{ ms}$
	min.	max.
	l _e	l _e
N	2.5 mW/sr	5.0 mW/sr
P	4.0 mW/sr	8.0 mW/sr

Note: Only one group in one packing unit (variation lower 2:1)

Relative Spectral Emission 6), 7)


$$I_{rel} = f(\lambda); I_{F} = 70 \text{ mA}; t_{p} = 20 \text{ ms}$$






Radiation Characteristics 6), 7)






Forward current 6), 7)

 $I_F = f(V_F)$; single pulse; $t_p = 100 \mu s$




Relative Radiant Intensity 6), 7)

 I_e/I_e (70mA) = f (I_F); single pulse; t_p = 25 μs




Max. Permissible Forward Current

$$I_{F,max} = f(T_A); R_{thJA} = 450 K/W$$




Permissible Pulse Handling Capability

 $I_F = f(t_p)$; duty cycle D = parameter; $T_A = 25$ °C



Dimensional Drawing 8)




C63062-A4114-A1-03

Approximate Weight: 0.6 mg


Package marking: Anode

Pin	Description
1	anode
2	cathode

Recommended Solder Pad 8)




Component Location on Pad



E062.3010.122 -01

Reflow Soldering Profile

Product complies to MSL Level 3 acc. to JEDEC J-STD-020E






SFH 4043

Profile Feature	Symbol	Pb	-Free (SnAgCu) Ass	sembly	Unit
	,	Minimum	Recommendation	Maximum	
Ramp-up rate to preheat*) 25 °C to 150 °C			2	3	K/s
Time t_s T_{Smin} to T_{Smax}	t _s	60	100	120	S
Ramp-up rate to peak*) T_{Smax} to T_{P}			2	3	K/s
Liquidus temperature	T_L		217		°C
Time above liquidus temperature	t_		80	100	S
Peak temperature	T _P		245	260	°C
Time within 5 °C of the specified peak temperature T _P - 5 K	t _P	10	20	30	S
Ramp-down rate* T _p to 100 °C			3	6	K/s
Time 25 °C to T _P				480	S

All temperatures refer to the center of the package, measured on the top of the component

Taping 8)




C63062-A4114-B1-02



^{*} slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range

Tape and Reel 9)




Reel dimensions [mm]


Α	W	N_{min}	W_1	$W_{2 \text{ max}}$	Pieces per PU
180 mm	8 + 0.3 / - 0.1	60	8.4 + 2	14.4	3000



Barcode-Product-Label (BPL)




Dry Packing Process and Materials 8)



Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.



Transportation Packing and Materials 8)



Dimensions of transportation box in mm

Width	Length	Height
200 ± 5 mm	195 ± 5 mm	30 ± 5 mm



Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the LED specified in this data sheet fall into the class **exempt group (exposure time 10000 s)**. Under real circumstances (for exposure time, eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. As is also true when viewing other bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

For further application related informations please visit www.osram-os.com/appnotes



Disclaimer

Disclaimer

Language english will prevail in case of any discrepancies or deviations between the two language wordings.

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version in the OSRAM OS Webside.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office

By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product safety devices/applications or medical devices/applications

OSRAM OS components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

In case Buyer – or Customer supplied by Buyer– considers using OSRAM OS components in product safety devices/applications or medical devices/applications, Buyer and/or Customer has to inform the local sales partner of OSRAM OS immediately and OSRAM OS and Buyer and /or Customer will analyze and coordinate the customer-specific request between OSRAM OS and Buyer and/or Customer.



Glossary

- Radiant intensity: Measured at a solid angle of $\Omega = 0.01 \text{ sr}$
- ²⁾ **Reverse Operation**: Reverse Operation of 10 hours is permissible in total. Continuous reverse operation is not allowed.
- Total radiant flux: Measured with integrating sphere.
- Thermal resistance: junction ambient, mounted on PC-board (FR4), padsize 5 mm² each
- Thermal resistance: junction soldering point, of the device only, mounted on an ideal heatsink (e.g. metal block)
- Typical Values: Due to the special conditions of the manufacturing processes of LED, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- Testing temperature: $T_A = 25^{\circ}C$
- Tolerance of Measure: Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.
- ⁹⁾ **Tape and Reel**: All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.



Published by OSRAM Opto Semiconductors GmbH EU RoHS and China RoHS compliant product Leibnizstraße 4, D-93055 Regensburg www.osram-os.com © All Rights Reserved.

此产品符合欧盟 RoHS 指令的要求; 按照中国的相关法规和标准,不含有毒有害物质或元素。

