

SPECIFICATION

PRODUCT: AC BRUSHLESS FAN F1750BXAT-CE

TYPE	AC BRUSHLESS FAN		MODEL	F1750BXAT-CE
MECHANICAL				
1. EXTERNAL DIMENSION	171x150x51mm			
2. WEIGHT	1.1kg			
4. BEARING	BALL BEARING			
IN FREE AIR AT RATED VOLTAGE				
1. RATED VOLTAGE	220V			
2. RATED CURRENT	0.11A MAXIMUM			
3. RATED INPUT POWER	25W MAXIMUM			
EFFICIENCY				
1. RATED SPEED (RANGE)	2800 RPM			
2. MAXIMUM AIR FLOW	210 CFM (MIN AT ZERO STATIC PRESSURE ±5%)			
3. MAXIMUM STATIC PRESSURE	16 mm-H ₂ O / 156 Pa (AT ZERO AIR FLOW)			
CHARACTERISTICS				
1. OPERATING VOLTAGE	220-240VAC			
2. STARTING VOLTAGE	185VAC MINIMUM			
3. VIBRATION TEST1	OK			
4. SHOCK TEST2	OK			
5. OPERATING TEMPERATURE	BEARING TYPE	AMBIENT TEMP		
	SLEEVE BEARING	-10°C +70°C		
6. TENSILE STRENGTH OF LEAD WIRE	NOT BROKEN AT 1kg FOR 15sec PER PIECE			
7. SOUND LEVEL	54 dba			

