



# PML50 Series 0.688" (17.5mm) Waterproof LED FlexVolt<sup>™</sup> Panel Mount Indicator



PML50 Series with built-in LED FlexVolt<sup>™</sup> technology offers daytime visibility, easy installation in harsh environments



# Application

- Industrial
- Transportation
- People Movers
- Maritime, Oil and Gas Industry
- Automation and Control
- Slot, Gaming and Vending Machines
- Safety and Emergency
- Pilot Instrumentation
- Outdoor Applications


# **Key Features**

- For panel hole diameter: 0.688" (17.5mm)
- · Low profile flat and semi dome lens options for uniform illumination
- · Flat lens with a clear diffused lens for increased contrast visibility between on and off
- · Semi dome lens with a white diffused lens for optimal side distance viewing
- · Designed for extreme, harsh and outdoor environments
- · Available in five single colors: red, green, white, blue or yellow and in bi/color: red/green
- · Offered with two lens options: Low Profile Flat and Semi Dome
- · Resistant to shock and vibration
- Flex voltage (5 VDC to 28 VDC) designed for application flexibility: one solution for several required input voltages
- · Wide viewing angle
- · Mounting hardware provided: lock washer and hex nut
- Maximum installation torque: 15in/lb
- · "Double D" mounting hole prevents any rotation of the indicator while the nut is being installed
- · IP67 specification rating protects front panels against entry of dust, rain and moisture
- InGaN and AllnGaP Technology
- · Visible LED in direct sunlight with UV resistance lens
- · Long lifetime, up to 100k hours
- · For custom cable length, connectors or colors contact VCC
- RoHS and REACH Compliant



# **Ordering Data**

The PML50 Series is available in a range of standard features and options. To specify your Panel Mount Indicator, select one option from each column.



**Part Numbers** Color Lens Option PML50RFVW Red Flat PML50WFVW White Flat PML50GFVW Green Flat PML50BFVW Blue Flat PML50YFVW Yellow Flat PML50RGFVW Red/Green Flat PML50SRFVW Red Semi Dome PML50SWFVW White Semi Dome PML50SGFVW Green Semi Dome PML50SBFVW Blue Semi Dome PML50SYFVW Yellow Semi Dome PML50SRGFVW Red/Green Semi Dome

## **Example:**

#### PML50SGFVW

PML50 Semi Dome, Green, Flex Votage, Wire




PML50RFVW PML50 Flat, Red, Flex Votage, Wire




# **Product Dimensions**

## Semi Dome Lens

Flat Lens



## **Recommended Mounting Hole**




#### Notes:

- 1. All dimensions are in inches [millimeters]
- 2. Tolerance is  $\pm$ [0.25] 0.01 unless otherwise noted.
- 3. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.



## **Product Dimensions**

## Semi Dome Lens




#### Notes:


- 1. All dimensions are in inches [millimeters]
- 2. Tolerance is  $\pm$ [0.25] 0.01 unless otherwise noted.

3. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.




## Flat Lens





## Mounting Hardware (Included for flat and semi dome lenses)



#### Notes:

- 1. All dimensions are in inches [millimeters]
- 2. Tolerance is ±[0.25] 0.01 unless otherwise noted.
- 3. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.



Materials		
Housing	White Polycarbonate UL 94 V-0	
Lens	Transparent Polycarbonate UL 94 V-0	
	UV Material:Polycarbonate Resin (Semi dome lens only)	
Bezel	Plated, Black Color Finish	
Wire Leads	Tinned Copper Conductor PVC Insulation	
Washer (installed)	EPDM rubber	
Lock Washer	SPCC, Nickel Plated	
Hex Nut	Brass, Nickel Plated	

Installation Specifications		
Mounting Hole ("D" Shape)	11/16" or 0.688" (17.46 mm)	
Panel Thickness (max.)	0.156" (3.96 mm)	
Wire Leads	24 AWG - UL1430 rated, 5.5" (140 mm) long, stripped .5" Anode (+): Red lead (Single Color) and Green and Red leads (Bicolor)	
Mounting Torque	15 in-lbs (17.28 kg-cm)	

Temperature Specifications		
Operating	-25°C to +80°C	
Temperature	-13°F to +176°F	
Storage	-30°C to +100°C	
Temperature	-22°F to +212°F	

Electrical Specifications		
Operating Voltage	110-125VAC 120VAC	
Operating Current	2mA (max.)	

## **Optical Ratings\***

Part Number	Color	Luminance (mcd)
PML50RFVW	Red	950
PML50WFVW	White	2980
PML50GFVW	Green	3640
PML50BFVW	Blue	270
PML50YFVW	Yellow	2020
PML50RGFVW	Red/Green	1130/2380

Part Number	Color	Luminance (mcd)
PML50SRFVW	Red	780
PML50SWFVW	White	1090
PML50SGFVW	Green	1770
PML50SBFVW	Blue	200
PML50SYFVW	Yellow	970
PML50SRGFVW	Red/Green	520/1370

\*Test Parameters: Voltage at 24VDC and Temperature at 25°C or 77°F

# **Compliances and Approvals**



