




REV	ECO	DATE
001	???	11/22/2019

TABLE 1		
MODEL NUMBER	"L"	MARKER 
21-21-12	12	21-21-12 14949 #####
21-21-24	24	21-21-24 14949 #####
21-21-36	36	21-21-36 14949 #####
21-21-60	60	21-21-60 14949 #####
21-21-72	72	21-21-72 14949 #####
21-21-120	120	21-21-120 14949 #####
21-21-240	240	21-21-240 14949 #####



UNRELEASED DWG
DECEMBER 13, 2019
C.MONAHAN




NOTES: UNLESS OTHERWISE SPECIFIED.



1. WORKMANSHIP PER IPC/WHMA-A-620, CLASS 3, SECTION 13.

 TOLERANCE PER IPC/WHMA-A-620, SECTION 11.1

3. TESTING:
3.1 CONTINUITY
3.2 DWV: 1000 VRMS

4. BEND RADIUS (MIN): 1.25

 MARKERS:
5.1 MARKER PER TABLE 1.
5.2 ##### = LOT CODE

 <small>The PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not to be traced or copied without permission and is returnable upon demand.</small> <small>INTERPRET DRAWING ACCORDANCE WITH ASME Y14.5-2009.</small>	Model No.	21-21	Title: TROMPETER	
	RoHS2	14949	CABLE ASSEMBLY, TRB PLUG TO TRB PLUG	
	2011/65/EU	3RD ANGLE PROJECTION	Drawing No.	C_21-21
	UNLESS OTHERWISE SPECIFIED UNITS: INCH	Drawn By: M. Souriphong	Rev.	001
	Date: 11/25/2019	SIZE: B	DO NOT SCALE DRAWING	Workmanship Std: SEE NOTES
		SHEET 1 OF 1		